


FurseWELD

Cable to cable CC2

Cable to cable CC2 - FurseWELD

	Stranded/solid circular conductor size A (mm ²)	Stranded/solid circular conductor size B (mm ²)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	16*	16*	CC2-4-1616	7TCA083910R1253	45P10	HCPK4
	25	25	CC2-4-2525	7TCA083910R1298	45P10	HCPK4
	35	35	CC2-4-3535	7TCA083910R1315	45P10	HCPK4
	35	25	CC2-4-3525	7TCA083910R1313	45P10	HCPK4
	Ø 8	Ø 8	CC2-4-885C	7TCA083910R1348	65P10	HCPK4
	50	50	CC2-4-5050	7TCA083910R1326	90P10	HCPK4
	50	35	CC2-4-5035	7TCA083910R1325	65P10	HCPK4
	50	25	CC2-4-5025	7TCA083910R1324	65P10	HCPK4
	Ø 10	Ø 10	CC2-4-1010SC	7TCA083910R1219	90P10	HCPK4
	70	70	CC2-4-7070	7TCA083910R1345	90P10	HCPK4
	70	50	CC2-4-7050	7TCA083910R1343	90P10	HCPK4
	70	35	CC2-4-7035	7TCA014980R0082	65P10	HCPK4
	70	25	CC2-4-7025	7TCA083910R1340	65P10	HCPK4
	95	95	CC2-4-9595	7TCA014980R0083	115P10	HCPK4
	95	95	CC2-4-9595-IU	-	115P10	HCPK4
	95	70	CC2-4-9570	7TCA083910R1362	90P10	HCPK4
	95	50	CC2-4-9550	7TCA083910R1360	90P10	HCPK4
	95	35	CC2-4-9535	7TCA083910R1359	90P10	HCPK4
	120	120	CC2-4-120120	7TCA014980R0065	150P10	HCPK4
	120	50	CC2-4-120120-IU	-	90P10	HCPK4
	120	95	CC2-4-12095	7TCA014980R0067	150P10	HCPK4
	120	70	CC2-4-12070	7TCA083910R1232	90P10	HCPK4
	120	50	CC2-4-12050	7TCA014980R0066	90P10	HCPK4
	150	150	CC2-4-150150	7TCA083910R1239	200P10	HCPK4
	150	150	CC2-4-150150-IU	7TCA083910R1239	200P10	HCPK4
	150	120	CC2-4-150120	7TCA083910R1238	150P10	HCPK4
	150	95	CC2-4-15095	7TCA083910R1250	150P10	HCPK4
	150	70	CC2-4-15070	7TCA083910R1249	90P10	HCPK4
	185	185	CC2-4-185185	7TCA083910R1267	200P10	HCPK4
	185	150	CC2-4-185150	7TCA083910R1265	200P10	HCPK4
	185	120	CC2-4-185120	7TCA083910R1264	200P10	HCPK4
	185	95	CC2-4-18595	7TCA083910R1276	150P10	HCPK4
240	240	CC2-4-240240	7TCA083910R1289	2 x 150P10	HCPK4	
240	185	CC2-4-240185	7TCA083910R1288	200P10	HCPK4	
240	150	CC2-4-240150	7TCA083910R1286	200P10	HCPK4	
240	120	CC2-4-240120	7TCA083910R1285	200P10	HCPK4	
300	300	CC2-5-300300	7TCA083910R1370	2 x 200P10	HCPK5	
300	240	CC2-5-300240	7TCA083910R1369	2 x 200P10	HCPK5	
300	185	CC2-4-300185	7TCA083910R1304	250P10	HCPK4	

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

*3 x S103 Sleeve required when joining conductors 16 mm² or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection