



Test Report				Date of issue: 4.6.2014																															
Customer:				Serial No.: 075033774004001																															
Customer ref.:				Type: M3JP 280SMB 8 IMB3/IM1001 Product Code: 3GJP284220-ADG Protection type: Ex d IIB T4 Gb Cert. No.: LCIE 11 ATEX 3089X / IECEx LCI 04.0006X																															
Rating:				<table border="1"> <thead> <tr> <th>V</th> <th>Hz</th> <th>kW</th> <th>r/min</th> <th>A</th> <th>cos φ</th> <th>Duty</th> </tr> </thead> <tbody> <tr> <td>3~Motor</td> <td>400 D</td> <td>50</td> <td>45,0</td> <td>741</td> <td>89</td> <td>0,78 S1</td> </tr> <tr> <td>Insul.cl.F</td> <td>690 Y</td> <td>50</td> <td>45,0</td> <td>741</td> <td>52</td> <td>0,78 S1</td> </tr> <tr> <td>IP55</td> <td>415 D</td> <td>50</td> <td>45,0</td> <td>742</td> <td>90</td> <td>0,75 S1</td> </tr> </tbody> </table>				V	Hz	kW	r/min	A	cos φ	Duty	3~Motor	400 D	50	45,0	741	89	0,78 S1	Insul.cl.F	690 Y	50	45,0	741	52	0,78 S1	IP55	415 D	50	45,0	742	90	0,75 S1
V	Hz	kW	r/min	A	cos φ	Duty																													
3~Motor	400 D	50	45,0	741	89	0,78 S1																													
Insul.cl.F	690 Y	50	45,0	741	52	0,78 S1																													
IP55	415 D	50	45,0	742	90	0,75 S1																													
Eff class IE2				50Hz : IE2 - 93,2(100%) - 93,2(75%) - 92,2(50%)																															
Resistance Line				Ambient: 23,0 °C U ₁ - V ₁ 0,08225 Ω U ₁ - W ₁ 0,08260 Ω V ₁ - W ₁ 0,08235 Ω		Insulation resistance at 23 °C R > 2000 Mohm 1000 V		Overload Voltage 130 % 180s Torque 160 % 15s Speed 120 % 120s																											
				High-voltage test winding		2400 V		60 s																											
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]																										
No load test		400,6 D	50	40,5	1,15		750	0,04																											
Locked rotor test		90,9 D	50	90,2	3,82		0	0,27																											
Thermal test (100% load)	579,9	400 D	50	89,6	48,23	45,00	741	0,78	93,30																										
Partial load points:																																			
~75% load	433,5	400 D	50	72,1	36,12	33,75	744	0,72	93,40																										
~50% load	288,4	400 D	50	57,1	24,23	22,50	745	0,61	92,90																										
~25% load	143,6	400 D	50	45,6	12,56	11,25	748	0,40	89,60																										
Temperature rise at rated load.				[°C]		[K]		Method		Measurement method																									
Stator winding :				59,4		1				1 Resistance																									
Frame :				34,5		2				2 Thermometer																									
Bearing D-end :				36,3		2				3 Thermocouples																									
Ambient Temperature :				25		2																													
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.																																			
On behalf of customer																																			
On behalf of manufacturer				Date of test				3.12.2011																											
Tested by ABB Shanghai Motors , LV Motors, Shanghai,P.R.China						Telephone		+86 21 54723133		Telefax		+86 21 54725009																							

Computer print-out valid without signature.