



Test Report				Date of issue: 20.11.2015																																																																																												
				Type: M3JM 400LB 4																																																																																												
				Product Code: 3GJM402520-_DG																																																																																												
				Protection type: Ex d I Mb																																																																																												
				Cert. No.: LCIE 10 ATEX 3004 X /																																																																																												
				IECEx LCI 04.0032X																																																																																												
Rating:																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>V</th> <th>Hz</th> <th>kW</th> <th>r/min</th> <th>A</th> <th>cos φ</th> <th>Duty</th> </tr> </thead> <tbody> <tr> <td>3-Motor</td> <td>690</td> <td>Y 50</td> <td>630</td> <td>1491</td> <td>624</td> <td>0,87</td> <td>S1</td> </tr> <tr> <td>Insul.cl.F</td> <td>400</td> <td>D 50</td> <td>630</td> <td>1491</td> <td>1077</td> <td>0,87</td> <td>S1</td> </tr> <tr> <td>IP66</td> <td>415</td> <td>D 50</td> <td>630</td> <td>1492</td> <td>1076</td> <td>0,86</td> <td>S1</td> </tr> </tbody> </table>												V	Hz	kW	r/min	A	cos φ	Duty	3-Motor	690	Y 50	630	1491	624	0,87	S1	Insul.cl.F	400	D 50	630	1491	1077	0,87	S1	IP66	415	D 50	630	1492	1076	0,86	S1																																																						
	V	Hz	kW	r/min	A	cos φ	Duty																																																																																									
3-Motor	690	Y 50	630	1491	624	0,87	S1																																																																																									
Insul.cl.F	400	D 50	630	1491	1077	0,87	S1																																																																																									
IP66	415	D 50	630	1492	1076	0,86	S1																																																																																									
Cold resistance				Insulation resistance at 81 °C				Overload																																																																																								
Line Ambient: 23 °C				3000 MΩ 1000 V				Torque 160% 15s																																																																																								
U ₁ - V ₁ 0,00193 Ω																																																																																																
U ₁ - W ₁ 0,00194 Ω																																																																																																
V ₁ - W ₁ 0,00194 Ω																																																																																																
				High-voltage test winding 2400 V				60 s																																																																																								
<table border="1"> <thead> <tr> <th rowspan="2">Test</th> <th rowspan="2">Torque [Nm]</th> <th colspan="2">Line</th> <th colspan="2">Input</th> <th colspan="2">Output</th> <th rowspan="2">cos φ</th> <th rowspan="2">η [%]</th> </tr> <tr> <th>U[V]</th> <th>f[Hz]</th> <th>I[A]</th> <th>P1 [kW]</th> <th>P2 [kW]</th> <th>n[r/min]</th> </tr> </thead> <tbody> <tr> <td>No load test</td> <td></td> <td>399,9</td> <td>D 50</td> <td>331,0</td> <td>6,59</td> <td></td> <td>1500</td> <td>0,03</td> <td></td> </tr> <tr> <td>Locked rotor test</td> <td></td> <td>66,8</td> <td>D 50</td> <td>1086</td> <td>34,6</td> <td></td> <td>0</td> <td>0,28</td> <td></td> </tr> <tr> <td>Thermal test (100% load)</td> <td>4035</td> <td>400,4</td> <td>D 50</td> <td>1099</td> <td>651,7</td> <td>630,0</td> <td>1491</td> <td>0,86</td> <td>96,7</td> </tr> <tr> <td>Partial load points:</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>~75% load</td> <td>3036</td> <td>400,7</td> <td>D 50</td> <td>850,3</td> <td>487,4</td> <td>472,5</td> <td>1494</td> <td>0,83</td> <td>97,0</td> </tr> <tr> <td>~50% load</td> <td>2013</td> <td>401,0</td> <td>D 50</td> <td>623,3</td> <td>325,3</td> <td>315,0</td> <td>1496</td> <td>0,75</td> <td>96,8</td> </tr> <tr> <td>~25% load</td> <td>1012</td> <td>400,9</td> <td>D 50</td> <td>434,9</td> <td>165,0</td> <td>157,5</td> <td>1498</td> <td>0,55</td> <td>95,4</td> </tr> </tbody> </table>											Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]	U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]	No load test		399,9	D 50	331,0	6,59		1500	0,03		Locked rotor test		66,8	D 50	1086	34,6		0	0,28		Thermal test (100% load)	4035	400,4	D 50	1099	651,7	630,0	1491	0,86	96,7	Partial load points:										~75% load	3036	400,7	D 50	850,3	487,4	472,5	1494	0,83	97,0	~50% load	2013	401,0	D 50	623,3	325,3	315,0	1496	0,75	96,8	~25% load	1012	400,9	D 50	434,9	165,0	157,5	1498	0,55	95,4
Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]																																																																																							
		U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]																																																																																									
No load test		399,9	D 50	331,0	6,59		1500	0,03																																																																																								
Locked rotor test		66,8	D 50	1086	34,6		0	0,28																																																																																								
Thermal test (100% load)	4035	400,4	D 50	1099	651,7	630,0	1491	0,86	96,7																																																																																							
Partial load points:																																																																																																
~75% load	3036	400,7	D 50	850,3	487,4	472,5	1494	0,83	97,0																																																																																							
~50% load	2013	401,0	D 50	623,3	325,3	315,0	1496	0,75	96,8																																																																																							
~25% load	1012	400,9	D 50	434,9	165,0	157,5	1498	0,55	95,4																																																																																							
Temperature rise at rated load.																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>[°C]</th> <th>[K]</th> <th>Method</th> <th>Measurement method</th> </tr> </thead> <tbody> <tr> <td>Stator winding :</td> <td></td> <td>82</td> <td>1</td> <td>1 Resistance</td> </tr> <tr> <td>Frame :</td> <td></td> <td>46</td> <td>2</td> <td>2 Thermocouples</td> </tr> <tr> <td>Bearing D-end :</td> <td></td> <td>58</td> <td>2</td> <td>3 Thermometer</td> </tr> <tr> <td>Ambient Temperature :</td> <td>25</td> <td></td> <td>2</td> <td></td> </tr> </tbody> </table>												[°C]	[K]	Method	Measurement method	Stator winding :		82	1	1 Resistance	Frame :		46	2	2 Thermocouples	Bearing D-end :		58	2	3 Thermometer	Ambient Temperature :	25		2																																																														
	[°C]	[K]	Method	Measurement method																																																																																												
Stator winding :		82	1	1 Resistance																																																																																												
Frame :		46	2	2 Thermocouples																																																																																												
Bearing D-end :		58	2	3 Thermometer																																																																																												
Ambient Temperature :	25		2																																																																																													
<p>These tests have been carried out on motor no. 3GF10020866B, on date 2010-04-19, which is identical in electrical design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p> <p>On behalf of customer</p> <p>On behalf of manufacturer</p> <p>Tested by ABB Oy, Motors and Generators, Vaasa, Finland</p> <p>Telephone +358 10 2211 Telefax +358 10 22 47372</p>																																																																																																

Computer print-out valid without signature.