


NOTE: INTERNAL SCHEMATIC FOR PCMU STYLES R245D_V

1	2	ECO CSENG-3119	ECO CSENG-4083	INTERPRET GEOMETRIC TOLERANCE PER: ASME Y14.5- 2009	THIRD ANGLE PROJECTION	The information contained in this document has to be kept strictly confidential. Any unauthorized use, reproduction, distribution or disclosure to third parties is strictly forbidden. ABB reserves all rights regarding Intellectual Property Rights.	DFR/DATE: K. MARGIOTTA 11/08/13		
				UNLESS OTHERWISE SPECIFIED.	SOFTWARE TYPE : AUTOCAD 2014		CHRR/DATE: P. SHAH 11/11/13		
Dimensions are in inches. Tolerances: One Place Decimal: ±0.020 (.5) Two Place Decimal: ±0.010 (.25) Three Place Decimal: ±0.005 (.13) Four Place Decimal: ±0.003 (.07) Angular: ±1°				ABB Protective Relays and Switches, Coral Springs Fl, U.S.A.	APPR/DATE: B. TAUZER 11/13/13	TITLE: DPU245 TO REF615 PCMU 245+ SCHEMATIC	REV: 2		
Copyright 2017 ABB All rights reserved						SIZE A	DWG. NO: 95A1111	SCALE: NTS	SHEET 1 OF 1