


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
© ABB '19

On-load tap-changer type UCGL./III, VUCGL./III, UCLL./III, VUCLL./III, UC DL./III,
14 tap positions, linear switching.
Max. effective No. of turns in pos. 1.
The tap-changer is delivered set in pos. 8,
the preceding pos. was 7.

Lindningskopplare typ UCGL./III, VUCGL./III, UCLL./III, VUCLL./III, UC DL./III,
14 lägen, linjär koppling.
Max antal effektiva varv i läge 1.
Lindningskopplaren levereras inställd i läge 8,
föregående läge var 7.



Pos. Läge	Tap selector and diverter switch connect	30
1	1-V-x	
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	

The tap-changer is shown in pos. 8,
the preceding pos. was 7.
The tap selector is seen from above.
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 8,
föregående läge var 7.
Väljaren sedd uppifrån.
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
tap-changer. Dashed lines show leads belonging
to the cleats and leads.

Heldragna linjer visar ledare som ingår i
lindningskopplaren. Streckade linjer visar
ledare som tillhör anslutningsdonet.

Sheet	Cont
	Year Week
Form No.	Dept
	Design checked by

3	Tap selector figure changed	THLA	17	07
2	VUCL Added	CA	12	37
1	VUCG Added	CE	07	47
Rev Ind	Revision	Appd	Year	Week

Accepted by qual control R.Yngvesson	Accepted for prod by	Description (English) CONNECTION DIAGRAM	DATAORIGINAL
Design checked by B-O.Stenestam	Drawn by L.Bergman	Description (own language) KOPPLINGSSHEMA	File name 0367-6
Drawing checked by M.Hedlund	Issued by Dept Year Week COM/TKO 97 23	Lang 1	Sheet 1
Asea Brown Boveri		RevInd -	Cont -

5492 0367-6