


## FurseWELD

### Cable to cable CC1

#### Cable to cable CC1 - FurseWELD



Stranded/solid circular conductor size A (mm <sup>2</sup> )	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
16*	CC1-4-16	7TCA083910R1100	32P10	HCPK4
25	CC1-4-25	7TCA083910R1118	32P10	HCPK4
35	CC1-4-35	7TCA014980R0050	32P10	HCPK4
50	CC1-4-50	7TCA083910R1132	45P10	HCPK4
Ø 8	CC1-4-8SC	7TCA083910R1143	45P10	HCPK4
70	CC1-4-70	7TCA083910R1134	65P10	HCPK4
Ø 10	CC1-4-10SC	7TCA083910R1087	65P10	HCPK4
95	CC1-4-95	7TCA014980R0052	90P10	HCPK4
95	CC1-4-95-IU	–	90P10	HCPK4
120	CC1-4-120	7TCA014980R0049	115P10	HCPK4
120	CC1-4-120-IU	–	115P10	HCPK4
150	CC1-4-150	7TCA083910R1096	115P10	HCPK4
185	CC1-4-185	7TCA083910R1104	150P10	HCPK4
240	CC1-4-240	7TCA083910R1113	200P10	HCPK4
300	CC1-4-300	7TCA083910R1122	250P10	HCPK4
400	CC1-5-400	7TCA083910R1148	2 x 150P10	HCPK5

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

\*2 x S103 Sleeve required when joining conductors 16 mm<sup>2</sup> or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection