



Test Report				Date of issue: 30.6.2015					
				Serial No.: 3GF11076115					
				Type: M3JP 225SME4IMB35/IM2001					
				Product Code: 3GJP222250-BDH					
				Protection type: Ex d IIB T4 Gb					
				Cert. No.: LCIE 10 ATEX 3057X / IECEX LCI 04.0005X					
Rating:									
		V	Hz	kW	r/min	A	cos φ	Duty	
3-Motor		400	D	50	62	1477	113	0,84	S1
Insul.cl.F		415	D	50	62	1479	112	0,82	S1
IP56		690	Y	50	62	1477	66,1	0,84	S1
Eff class IE1		400 V 50Hz : IE1 - 93.6(100%) - 93.7(75%) - 92.9(50%)							
Resistance				Insulation resistance at 40,5 °C			Overload		
Line				5110 MΩ			1000 V		
Ambient: 23,5 °C							Torque 160 % 15s		
U ₁ - V ₁		0,05283 Ω							
U ₁ - W ₁		0,05291 Ω							
V ₁ - W ₁		0,05283 Ω							
				High-voltage test winding 1900 V			60 s		
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	η[r/min]	cos φ	η[%]
No load test		400,1 D	50	44,4	1,66		1500	0,05	
Locked rotor test		76,9 D	50	112,9	5,68		0	0,38	
Thermal test (100% load)	400,9	400,0 D	50	115,3	66,5	62,0	1480	0,83	93,3
Partial load points:									
~75% load	300,4	400,1 D	50	90,4	49,7	46,5	1484	0,79	93,5
~50% load	200,4	400,1 D	50	68,3	33,4	31,0	1489	0,71	92,9
~25% load	100,2	400,1 D	50	50,9	17,4	15,5	1495	0,49	89,3
Temperature rise at rated load.				°C	K	Method		Measurement method	
Stator winding :				67,2	1			1 Resistance	
Frame :				37,2	2			2 Thermometer	
Bearing D-end :				45,4	2			3 Thermocouples	
Ambient Temperature :				25,0	2				
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.									
On behalf of customer									
On behalf of manufacturer		Date of test		19.6.2011					
Tested by ABB Oy, Motors and Generators, Vaasa, Finland						Telephone +358 10 2211		Telefax +358 10 22 47372	

Computer print-out valid without signature.