



Test Report				Date of issue: 4.6.2014						
				Serial No.: 3GF11094416						
				Type: M3JP 160MLC 6 IMB3/IM1001						
				Product Code: 3GJP163430-ADH						
				Protection type: Ex d IIB T4 Gb						
				Cert. No.: LCIE 11 ATEX 3087X / IECEx LCI 09.0008X						
Rating:				V	Hz	kW	r/min	A	cos φ	Duty
3~Motor				690	Y 50	14	969	17,5	0,75	S1
Insul.cl.F				400	D 50	14	969	30,2	0,75	S1
IP55				415	D 50	14	971	29,9	0,73	S1
Eff class IE1				400V 50Hz: IE1 - 89.2(100%) - 89.4(75%) - 88.0(50%)						
Resistance				Ambient: 21,0 °C			Insulation resistance at 47,5 °C			
Line				3000 MΩ			1000 V			
U ₁ - V ₁				0,40000 Ω						
U ₁ - W ₁				0,40020 Ω						
V ₁ - W ₁				0,40020 Ω						
				High-voltage test winding			2900 V		1 s	
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]	
No load test		400,0 D	50	17,3	0,65		998	0,05		
Locked rotor test		84,5 D	50	30,2	1,65		0	0,37		
Thermal test (100% load)	138,0	400,0 D	50	30,1	15,7	14,0	973	0,75	89,1	
Partial load points:										
~75% load	103,3	400,0 D	50	25,2	11,7	10,5	981	0,67	89,4	
~50% load	68,5	400,0 D	50	20,9	7,92	7,00	987	0,55	88,4	
~25% load	34,4	400,0 D	50	17,9	4,23	3,50	993	0,34	82,8	
Temperature rise at rated load.				°C	K	Method		Measurement method		
Stator winding :				73,6	73,6	1		1 Resistance		
Frame :				35,8	35,8	2		2 Thermometer		
Bearing D-end :				39,7	39,7	2		3 Thermocouples		
Rotor :				92,0	92,0	3				
Ambient Temperature :				25,0	25,0	2				
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.										
On behalf of customer										
On behalf of manufacturer				Date of test		14.2.2012				
Tested by ABB Oy, Motors and Generators, Vaasa, Finland								Telephone +358 10 2211 Telefax +358 10 22 47372		

Computer print-out valid without signature.

ABB, Motors and Generators
www.abb.com/motors&generators