



Test Report				Date of issue: 28.8.2013							
				Serial No.: 0927-010205101							
				Type: M3GP 160MLB 8 B5							
				Product Code: 3GGP164420-ADD							
				Protection type: Ex nA II C T3 Gc							
				Cert. No.: LCIE 13 ATEX 1034 X IECEx LCIE 13.0047X							
Rating:				V	Hz	kW	r/min	A	cos φ	Duty	
3~Motor				400	D	50	5,5	723	12,8	0,71	S1
Insul.cl.F				415	D	50	5,5	725	12,7	0,69	S1
IP55				690	Y	50	5,5	723	7,5	0,71	S1
400 V 50Hz : 86.8(100%) - 87.6(75%) - 86.8(50%)											
Resistance				Ambient: 26,0 °C				Insulation resistance at 52,5 °C		Overload	
Line				15000 MΩ				1000 V		Torque 160% 15s	
U <sub>1</sub> - V <sub>1</sub>				1,34450 Ω							
U <sub>1</sub> - W <sub>1</sub>				1,34470 Ω							
V <sub>1</sub> - W <sub>1</sub>				1,34430 Ω							
				High-voltage test winding				1900 V		60 s	
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	η[r/min]	cos φ	η [%]		
No load test		400,0 D	50	7,91	0,37		750	0,07			
Locked rotor test		114,9 D	50	13,2	0,98		0	0,37			
Thermal test (100% load)	72,7	400,2 D	50	13,5	6,47	5,50	720	0,69	85,0		
Partial load points:											
~75% load	54,5	400,0 D	50	11,4	4,83	4,12	728	0,61	85,4		
~50% load	36,0	400,0 D	50	9,62	3,27	2,75	736	0,49	84,1		
~25% load	18,0	400,0 D	50	8,37	1,79	1,37	743	0,31	76,9		
Temperature rise at rated load.				[°C]	[K]	Method		Measurement method			
Stator winding :				46,4	1			1 Resistance			
Frame :				18,6	2			2 Thermometer			
Bearing D-end :				24,2	2			3 Thermocouples			
Rotor:				58,8	3						
Ambient Temperature :				25,0	2						
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.											
On behalf of customer											
On behalf of manufacturer			Date of test		11.8.2009						
Tested by ABB Oy, Motors and Generators, Vaasa, Finland								Telephone		+358 10 2211	
								Telefax		+358 10 22 47372	

Computer print-out valid without signature.