


MULTIPLES OF CURRENT RATING (In)



Time Current Curve

Available Ratings (Amperes)

Type	Model	Trip Unit	Frame Amps	Current Rating (In)
Power	E1.2	Touch/Hi-Touch	1200	250 800 400 1200

Voltage Rating: 635 Vac, 50 to 60 hz systems

electrification.us.abb.com

Power Circuit Breaker

Type Emax E1.2 with Ekip Touch/Hi-Touch LSI/LSIG Ground Fault Curve

Operating Conditions: Curves apply at 50 to 60 Hertz and ambient temperature from -25°C to +70°C up to an altitude of 2000 meters. Electronic trip units do not undergo any variations in performance as the temperature varies, but, in the case of temperatures exceeding +40°C, the maximum setting for protection L (protection against overloads) must be reduced, as indicated in the UL Catalog.

ABB

Interrupting Ratings: The pickup setting for each interrupting rating is listed below. Tolerance is in parentheses.
B-A: 50,000 (minus 16% or plus 0%)
N-A: 50,000 (minus 16% or plus 0%)
S-A: 50,000 (minus 16% or plus 0%)