

---

TECHNICAL DATA SHEET

# Terminals, fork

## Vinyl-insulated, single crimp

### Spec-Kon<sup>®</sup>



---

**Features:**

- Belled opening for wire termination
- Corrosive resistant plating
- Color coded to wire size range

---

**Maximum rating:**

- 75°C Max
- 600 volts
- Copper conductors only

---

**Applications:**

- ERG9002

Vinyl-insulated fork terminals for wire termination of copper conductors ranging from 0.5mm<sup>2</sup> to 6mm<sup>2</sup>

**Certifications / Standards:**



---

**Conforms to:**

- IEC 60352-2

---

**Materials / Finishes:**

- Copper terminal
- Brazed seam crimp barrel
- Electro-Tin plated
- Vinyl insulation

**Terminals, fork:**  
Vinyl-insulated, single crimp

Product selection										
Drawing	Part no:	Wire size range (mm <sup>2</sup> )	Color	Stud hole size		Dimensions (mm)				Crimping tool
				d2	L	F	W	D		
	F1.5-3VSC	0.5 - 1.5	Red	M3	21.0	6.5	5.7	4.3	ERG9002	
	F1.5-35VSC	0.5 - 1.5	Red	M3.5	21.0	6.5	6.4	4.3		
	F1.5-4VSC	0.5 - 1.5	Red	M4	21.0	6.5	8.1	4.3		
	F1.5-5VSC	0.5 - 1.5	Red	M5	21.0	6.5	9.5	4.3		
	F1.5-6VSC	0.5 - 1.5	Red	M6	27.0	11.0	12.0	4.3		
	F2.5-3VSC	1.5 - 2.5	Blue	M3	21.0	6.5	5.7	4.8		
	F2.5-35VSC	1.5 - 2.5	Blue	M3.5	21.0	6.5	6.4	4.8		
	F2.5-4VSC	1.5 - 2.5	Blue	M4	21.0	6.5	8.1	4.8		
	F2.5-5VSC	1.5 - 2.5	Blue	M5	21.0	6.5	9.3	4.8		
	F2.5-6VSC	1.5 - 2.5	Blue	M6	27.0	11.0	12.0	4.8		
	F6-35VSC	4 - 6	Yellow	M3.5	25.5	7.0	8.3	6.7		
	F6-4VSC	4 - 6	Yellow	M4	25.5	7.0	9.0	6.7		
	F6-5VSC	4 - 6	Yellow	M5	25.5	7.0	9.0	6.7		
	F6-6VSC	4 - 6	Yellow	M6	31.5	12.0	12.0	6.7		
	F6-8VSC	4 - 6	Yellow	M8	30.5	11.5	14.0	6.7		

Note: Products must be installed in accordance with applicable national and local electrical codes.