



MVI Fault Interrupter	Cooper 280ARX Relay	30-600 Ampere
MINIMUM TRIPPING AND TOTAL CLEARING TIME-CURRENT CHARACTERISTIC CURVES		
Notes: <div>1. Tested per C37.60</div> <div>2. Accuracy is equal to +/- 10% of the current or time which ever is greater.</div> <div>3. Minimum power up current: 15 Amperes</div> <div>4. Curves are applicable to the operating range of -40°C to +65°C.</div>	<div>5. CT current sensing capability range: 10 -10,000 amperes RMS</div> <div>6. Curves and trips are set using a personal computer or a control panel</div> <div>7. The total clearing time-current characteristics curves represent the total time required to detect and interrupt the fault current</div> <div>8. This curve in its entirety, including the title block, should be printed on a 11"x 17" sheet in order to conform with the C37.41 curve presentation standard (5.6 cm/decade).</div>	Cooper 280ARX Relay 30-600 Ampere
	<div>Thomas &amp; Betts</div> <div>Route 24, Hackettstown NJ, 07840</div> <div>(908) 852-1122 FAX (908) 813-2091</div>	Issue Date: August 30, 2007 Reference number: MVI-TCC-13