



Test Report				Date of issue: 28.5.2015						
Customer:				Serial No.:						
Customer ref.:				Order No.:						
				Type: M3JP 200MLA 6						
				Product Code: 3GJP203410-ADK						
				Protection type: Ex d IIB T4 Gb						
				Cert. No.: LCIE 10 ATEX 3061X/						
				IECEX LCI 04.0011X						
Rating:										
		V	Hz	kW	r/min	A	cos φ	Duty		
3-Motor		690	Y 50	18,5	990	21,6	0,77	S1		
Insul.cl.F		400	D 50	18,5	990	37,3	0,77	S1		
IP55		660	Y 50	18,5	989	21,8	0,80	S1		
		380	D 50	18,5	989	37,8	0,80	S1		
		415	D 50	18,5	991	37,4	0,74	S1		
		460	D 60	18,5	1191	32,3	0,77	S1		
Eff class IE3		50Hz : IE3-92,8(100%)-93,2(75%)-92,6(50%)								
		60Hz : IE3-93,3(100%)								
Resistance				Insulation resistance at 22 °C			Overload			
Line		Ambient: 22,1 °C		R > 2000 Mohm 1000 V			Current 150 % 120s			
U ₁ - V ₁		0,2704 Ω					Torque 160 % 15s			
U ₁ - W ₁		0,2693 Ω					Speed 120 % 120s			
V ₁ - W ₁		0,2695 Ω								
				High-voltage test winding 2400 V			60 s			
Test	Torque [Nm]	Line U[V]		f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	n[r/min]	cos φ	η [%]
No load test		401	D	50	17,4	0,6		1000	0,05	
Locked rotor test		76	D	50	36,2	1,52		0	0,32	
Thermal test (100% load)	178,5	400	D	50	36,9	20,03	18,50	990	0,78	92,38
Partial load points:										
~75% load	135,9	400	D	50	30,3	15,26	14,12	992	0,73	92,54
~50% load	90,8	400	D	50	24,2	10,31	9,46	995	0,61	91,80
~25% load	46,6	400	D	50	19,7	5,55	4,87	997	0,41	87,85
Temperature rise at rated load.				°C	[K]	Method		Measurement method		
Stator winding :				50,0	1			1 Resistance		
Frame :				39,7	2			2 Thermometer		
Bearing D-end :				31,3	2			3 Thermocouples		
Ambient Temperature :				22	2					
<p>These tests have been carried out on motor no. 3GV1110796909001, on date 2011-09-20 which is identical in electrical design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p>										
On behalf of customer										
On behalf of manufacturer				Date of test						
Tested by ABB AB, LV Motors, 721 70 Västerås, Sweden						Telephone +46 (0)21 32 90 00		Telefax +46 (0)21 32 90 22		

Computer print-out valid without signature.