



Test Report				Date of issue: 20.11.2015																																																																																												
				Type: M3JM 400LC 8																																																																																												
				Product Code: 3GJM404530-_DG																																																																																												
				Protection type: Ex d I Mb																																																																																												
				Cert. No.: LCIE 10 ATEX 3004 X /																																																																																												
				IECEx LCI 04.0032X																																																																																												
Rating:																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>V</th> <th>Hz</th> <th>kW</th> <th>r/min</th> <th>A</th> <th>cos φ</th> <th>Duty</th> </tr> </thead> <tbody> <tr> <td>3-Motor</td> <td>690</td> <td>Y 50</td> <td>400</td> <td>744</td> <td>428</td> <td>0,82</td> <td>S1</td> </tr> <tr> <td>Insul.cl.F</td> <td>400</td> <td>D 50</td> <td>400</td> <td>744</td> <td>735</td> <td>0,82</td> <td>S1</td> </tr> <tr> <td>IP66</td> <td>415</td> <td>D 50</td> <td>400</td> <td>744</td> <td>724</td> <td>0,80</td> <td>S1</td> </tr> </tbody> </table>												V	Hz	kW	r/min	A	cos φ	Duty	3-Motor	690	Y 50	400	744	428	0,82	S1	Insul.cl.F	400	D 50	400	744	735	0,82	S1	IP66	415	D 50	400	744	724	0,80	S1																																																						
	V	Hz	kW	r/min	A	cos φ	Duty																																																																																									
3-Motor	690	Y 50	400	744	428	0,82	S1																																																																																									
Insul.cl.F	400	D 50	400	744	735	0,82	S1																																																																																									
IP66	415	D 50	400	744	724	0,80	S1																																																																																									
Cold resistance				Insulation resistance at 83 °C				Overload																																																																																								
Line Ambient: 28 °C				7000 MΩ 1000 V				Torque 160% 15s																																																																																								
U <sub>1</sub> - V <sub>1</sub> 0,00430 Ω																																																																																																
U <sub>1</sub> - W <sub>1</sub> 0,00430 Ω																																																																																																
V <sub>1</sub> - W <sub>1</sub> 0,00430 Ω																																																																																																
				High-voltage test winding 1900 V				60 s																																																																																								
<table border="1"> <thead> <tr> <th rowspan="2">Test</th> <th rowspan="2">Torque [Nm]</th> <th colspan="2">Line</th> <th colspan="2">Input</th> <th colspan="2">Output</th> <th rowspan="2">cos φ</th> <th rowspan="2">η [%]</th> </tr> <tr> <th>U[V]</th> <th>f[Hz]</th> <th>I[A]</th> <th>P1 [kW]</th> <th>P2 [kW]</th> <th>n[r/min]</th> </tr> </thead> <tbody> <tr> <td>No load test</td> <td></td> <td>400,0</td> <td>D 50</td> <td>259,0</td> <td>5,07</td> <td></td> <td>750</td> <td>0,03</td> <td></td> </tr> <tr> <td>Locked rotor test</td> <td></td> <td>87,2</td> <td>D 50</td> <td>731,2</td> <td>21,5</td> <td></td> <td>0</td> <td>0,19</td> <td></td> </tr> <tr> <td>Thermal test (100% load)</td> <td>5134</td> <td>400,8</td> <td>D 50</td> <td>735,3</td> <td>416,4</td> <td>400,0</td> <td>744</td> <td>0,82</td> <td>96,1</td> </tr> <tr> <td>Partial load points:</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>~75% load</td> <td>3856</td> <td>401,1</td> <td>D 50</td> <td>573,9</td> <td>311,3</td> <td>300,0</td> <td>746</td> <td>0,78</td> <td>96,4</td> </tr> <tr> <td>~50% load</td> <td>2563</td> <td>401,4</td> <td>D 50</td> <td>436,3</td> <td>207,8</td> <td>200,0</td> <td>747</td> <td>0,70</td> <td>96,2</td> </tr> <tr> <td>~25% load</td> <td>1282</td> <td>401,6</td> <td>D 50</td> <td>318,3</td> <td>105,8</td> <td>100,0</td> <td>749</td> <td>0,48</td> <td>94,5</td> </tr> </tbody> </table>											Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]	U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]	No load test		400,0	D 50	259,0	5,07		750	0,03		Locked rotor test		87,2	D 50	731,2	21,5		0	0,19		Thermal test (100% load)	5134	400,8	D 50	735,3	416,4	400,0	744	0,82	96,1	Partial load points:										~75% load	3856	401,1	D 50	573,9	311,3	300,0	746	0,78	96,4	~50% load	2563	401,4	D 50	436,3	207,8	200,0	747	0,70	96,2	~25% load	1282	401,6	D 50	318,3	105,8	100,0	749	0,48	94,5
Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]																																																																																							
		U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]																																																																																									
No load test		400,0	D 50	259,0	5,07		750	0,03																																																																																								
Locked rotor test		87,2	D 50	731,2	21,5		0	0,19																																																																																								
Thermal test (100% load)	5134	400,8	D 50	735,3	416,4	400,0	744	0,82	96,1																																																																																							
Partial load points:																																																																																																
~75% load	3856	401,1	D 50	573,9	311,3	300,0	746	0,78	96,4																																																																																							
~50% load	2563	401,4	D 50	436,3	207,8	200,0	747	0,70	96,2																																																																																							
~25% load	1282	401,6	D 50	318,3	105,8	100,0	749	0,48	94,5																																																																																							
Temperature rise at rated load.																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>[°C]</th> <th>[K]</th> <th>Method</th> <th>Measurement method</th> </tr> </thead> <tbody> <tr> <td>Stator winding :</td> <td></td> <td>69</td> <td>1</td> <td>1 Resistance</td> </tr> <tr> <td>Frame :</td> <td></td> <td>45</td> <td>2</td> <td>2 Thermocouples</td> </tr> <tr> <td>Bearing D-end :</td> <td></td> <td>49</td> <td>2</td> <td>3 Thermometer</td> </tr> <tr> <td>Rotor :</td> <td></td> <td>121</td> <td>3</td> <td></td> </tr> <tr> <td>Ambient Temperature :</td> <td>25</td> <td></td> <td>2</td> <td></td> </tr> </tbody> </table>												[°C]	[K]	Method	Measurement method	Stator winding :		69	1	1 Resistance	Frame :		45	2	2 Thermocouples	Bearing D-end :		49	2	3 Thermometer	Rotor :		121	3		Ambient Temperature :	25		2																																																									
	[°C]	[K]	Method	Measurement method																																																																																												
Stator winding :		69	1	1 Resistance																																																																																												
Frame :		45	2	2 Thermocouples																																																																																												
Bearing D-end :		49	2	3 Thermometer																																																																																												
Rotor :		121	3																																																																																													
Ambient Temperature :	25		2																																																																																													
<p>These tests have been carried out on motor no. 3GF11069476C, on date 2011-06-10, which is identical in electrical design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p> <p>On behalf of customer</p> <p>On behalf of manufacturer</p> <p>Tested by ABB Oy, Motors and Generators, Vaasa, Finland</p> <p>Telephone +358 10 2211 Telefax +358 10 22 47372</p>																																																																																																

Computer print-out valid without signature.