


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
© ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F
13 positions, linear switching.
Min. effective No. of turns in pos. 1.
The tap-changer is delivered set in pos. 7,
the preceding pos. was 6.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F
13 lägen, linjär koppling.
Min antal effektiva varv i läge 1.
Lindningskopplaren levereras inställd i läge 7,
föregående läge var 6.



Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	

The tap-changer is shown in pos. 7,
the preceding pos. was 6.
The tap selector is seen from above.
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 7,
föregående läge var 6.
Väljaren sedd uppifrån.
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
tap-changer. Dashed lines show leads belonging
to the cleats and leads.

Heldragna linjer visar ledare som ingår i
lindningskopplaren. Streckade linjer visar
ledare som tillhör anslutningsdonet.

Sheet	Cont									
	Year	Week	Dept		Appd		Year		Week	
Form No.	RevInd	Accepted by qual control L.Oberg		Accepted for prod by M.Haggmar		Description (English) CONNECTION DIAGRAM				DATAORIGINAL
	Design checked by	H.Sundberg		Drawn by A.Wang		Description (own language) KOPPLINGSSHEMA				File name
Design checked by	Drawing checked by	N.Gustavsson		Issued by Dept	Year	Week	1ZSC004308-AAJ			
	CO/TK		14	02	Lang	Sheet				
								Lang	Sheet	
								RevInd	Cont	