

TECHNICAL DATA SHEET

DS0104 rev 43

Cylon® CBT-3T6-5R



DESCRIPTION

The CBT-3T6-5R is a freely programmable BACnet® Unitary Controller with native MS/TP communications support. The controller is BTL listed as a BACnet Advanced Application Controller (B-AAC) and is ideally suited for Rooftop HVAC units, Fan Coil Units, Heat Pumps, Unit Ventilators, and custom unitary equipment control.

Part of the ABB Cylon® CB Line of BACnet field controllers, the CBT-3T6-5R provides 3 UniPuts™ with Triac (configurable as inputs or outputs), 6 Universal Inputs, 5 Digital (Relay) Outputs and a dedicated input for ABB Cylon® room sensors.

APPLICATION

The CBT-3T6-5R is suitable for controlling a variety of small to medium-sized HVAC equipment such as:

- Rooftop Units
- Fan Coil Units
- Heat Pumps
- Unit Ventilators
- Custom Unitary Equipment

This controller accommodates available pre-engineered strategies or can be tailored to custom applications using CXpro^{HD} programming software.

BACnet MS/TP Fieldbus

Supports the following configurable BACnet objects: AI/AO/BI/BO/AV/BV, Trend Logs, and Schedules

3 UniPuts with Triac

Configured as analog or digital outputs, or voltage inputs along with Triac functionality that can switch a 24 V AC load

6 Universal Inputs

Can be configured as analog or digital inputs with pulse counting on the 6th input

5 Digital (Relay) Outputs

3 Outputs can switch up to 240 V AC

2 Outputs can switch up to 24 V AC

Cylon Intelligent Room Sensor support

Up to 500 Strategy Blocks

Up to 6 Trendlogs

1024 entries per Trendlog

Data Security

Strategy and setpoints backed up in Flash

No Hardware I/O Jumpers

Hardware points are automatically configured by the downloaded strategy

SPECIFICATIONS

MECHANICAL

Size	5.12 x 5.17 x 1.78"
(excluding terminal plugs)	(130 x 131.2 x 45 mm)
Enclosure	Injection molded, flame retardant ABS plastic
Mounting	DIN rail - The housing base is designed for snap-mounting on DIN rails - The controller should not be freely accessible after mounting - Unit must be oriented such that powered relay terminals are at the bottom of unit

CONNECTION

Note: Use Copper or Copper Clad Aluminum 70 °C (158 °F) conductors only.

Terminals	I/O & RS485 Comm Network: Grey Pluggable PCB mounted screw terminal connections. 24 V AC Power: Green Pluggable PCB mounted screw terminal connections. 240 V AC Relay: Green PCB mounted screw terminal connections. These may not be pluggable.
Conductor Area	Max: AWG 12 (3.09 mm ²) Min: AWG 22 (0.355 mm ²)

ENVIRONMENT

Note: This equipment is intended for field installation within an enclosure.

Ambient Temperature	0 °C ... 50 °C [32 °F ... 122 °F] ambient.
Ambient Humidity	0% ... 90% RH non-condensing
Storage Temperature	-30 °C ... +70 °C (-22 °F ... 158 °F)
EMC Immunity	EN 61326-1
EMC Emission	EN 61326-1
Approvals	BTL Listed – BACnet Advanced Application Controller (B-AAC) UL Listed (CDN & US) UL916 Energy Management Equipment - File No. E176435
Safety	EN 60730-1:2011 Automatic Action type i.e. Type 1.B.Y CE Approved
Pollution Degree	Class 2 (EN 60730-1)

ELECTRICAL

Supply Requirements	24 V AC/DC +15 % / -20 % 50/60 Hz (SELV Power Source)
Transformer Rating	10 VA typical, 31 VA max with all external loads
Rated Impulse Level	2,500 V
BACnet Loading	¼ unit load device

PROCESSOR

Type	STM32 F103ZGT6 32bit processor
Clock Speed	8 MHz crystal, 72 MHz internal processor clock rate
System Memory (soldered to PCB not removable)	Internal Flash 1 Mbyte Internal SRAM 64 Kbyte External SRAM 1 Mbyte

COMMUNICATIONS

Local serial port	Right angle entry RJ-45 @ 9600 Baud Max cable length 4 m
BACnet MS/TP port	RS485 @ 9K6, 19K2, 38K4 or 76K8 Baud (defaults to 38K4) Max cable length 1.2 km
Local Sensor Port	RS485 with a maximum cable length 500 m Supports ABB Cylon® room sensors

INPUTS / OUTPUTS

Note: Shielded cable is recommended for all input connections.

UniPuts™ with Triac



When configured as Input:

Analog Input
Range: 0 ... 10 V @ 40 kΩ
Resolution: 12 bit
Digital Volt-Free contact, @ 25 mA not continuous

When configured as Output:

Analog Output 0 ... 10 V, 10 mA, 12-bit resolution
Active Output 1 ... 10 V for sinking 1 mA max load with 12 bit resolution.
Digital Output 0 ... 10 V, 10 mA
24 V AC Triac @ 500 mA maximum. Switch neutral only.

Universal Inputs



Analog Input

Range: 0 ... 10 V @ 130 kΩ
Resolution: 12 bit

Temperature measurement

Range: 0 °C ... +50 °C (32 °F ... 122 °F)
Resolution: 12 bit

Passive Input for a large range of temperature sensors. 10K3A1 sensors are recommended.

Note: It is not recommended using Sensors with a heating dissipation constant (K factor) < 2 as this will lead to an offset error.

Current input

Range: 0 ... 20 mA @ 390 Ω
Accuracy: ±0.5% full scale [100µA]

Digital Volt-Free contact, Dry Contact

Note: Only Universal Input 6 supports pulse counting at below 20 Hz and a minimum pulse width of 25 milliseconds.

Relay Digital Outputs



Points 9, 10 & 11 are relay contacts with ability to switch 240 V AC (USA: Pilot Duty 120V AC, 72 VA).
Points 12 & 13 are relay contacts with ability to switch up to 24 V AC.
Maximum Load: 250 V AC, 2 (1) A resistive (inductive) for all relay contacts.
Relay contacts switch single-phase only.

24 V AC output terminals

Total current drawn from 24 V AC terminals is limited to 0.9 A.

SOFTWARE FEATURES

Maximum number of Strategy Blocks	500
Maximum number of Trend log Modules	6
Maximum internal Trend log capacity (standard)	1024
Data Security	Strategy and Set points backed up in Flash


INTERFACE

Engineering Software


CXpro^{HD}




DIMENSIONS



WIRING



SYSTEM ARCHITECTURE



FBXi / CBXi-8R8 / CBX-8R8	FLX-8R8 -H	FBVi-2U4-4T	INTEGRA Series	FusionAir Smart Sensor
CBXi-8R8-H / CBX-8R8-H	FLX-4R4-H	NEXUS Series	eXplore	CBT-STAT
CBV-2U4-3T	FLX-PS24	MATRIX-2 Series		UCU Room Display
FLX-8R8 / FLX-4R4 / FLX-16DI	CBT-4T4-2U1R			