


# Serenga 2

Project covering & stylish



### Escape route - Surface mount 4-12m

- Injection moulded - high grade polycarbonate body
- Specially designed lens for optimised light distribution - ideal for high ceiling areas, up to 12 metres
- Modular, First-Fix installation
- Ease of installation - unique moulded construction to retain IP rating without additional protection



—  
Luminaire

Order code	Description	Input voltage	Lamp type	Lamp output (lm)	Power consumption (VA/W)	Operation / duration (hrs)	Environment temp. (°C)	Weight (kg)
CTSR2-SEM3-BC1	SFC M3 CT-NAVEO ESC-MH12M WH	220-240 AC 50Hz	1 x LED 2W	203	3.5 / 3	3	5-40	1.0
SR2-SE230-BC1	SFC 230V ESC-MH12M WH	220-240 AC/DC 0-60Hz			5.5 / 5	230V	0-40	0.7
SR2-SE230LT-BC1	SFC 230V EMEX ESC-MH12M WH	220-240 AC 50/60Hz			5.5 / 5	230V	0-40	0.7
SR2-SEM3-BC1	SFC M3 AUTOTST ESC-MH12M WH	220-240 AC 50Hz			3.5 / 3	3	5-40	1.0

Includes lens B & C  
Black version available on request

Code	Lens	Type	Application
SR2-LENS1	A	Escape route	2-4m corridor use, ceiling mount
SR2-LENS2*	B	Escape route, or object	4-8m corridor use, ceiling mount. Or spot light at 2-4m (ceiling mount)
SR2-LENS3*	C	Escape route	8-12m corridor use, ceiling mount
SR2-LENS4	D	Open area	2-4m, open area space
SR2-LENS5	E	Open area	4-8m, open area space
SR2-LENS6	F	Open area	8-12m, open area space
SR2-LENS7	G	Escape route	2-4m corridor use, wall mount

\*Lens included in the box  
See spacing tables on pages 130-131

