



## AQL 02/HF/LED/FLX

Slave 1 watt, 230 Volt surface mount led luminaire, including control module, series Aqualux

### Product Information

Type	AQL 02/HF/LED/FLX
Catalog number	6000053-005
Category_	Escape route signalisation
GTIN	08713812759326
GID	7TCA091140R0282
Serie	Aqualux
Warranty (Year)	5



### Characteristics

Power supply system	Central
Continuous operation	Yes
Mounting Method	Ceiling;Wall
Mounting form	Surface
Material housing	Aluminium / plastic
Colour housing	White / aluminium
Material cover	Plastic, transparent
Material	Aluminium / polycarbonate
Colour	White / aluminium
Length (mm)	381
Width (mm)	170
Height/depth (mm)	75
Nominal voltage (V)	230
Voltage type	DC
Monitoring equipment	Safety module for monitoring
With lamp	Yes
Lamp Type	Led
Lamp holder	Other
Lamp power (W)	1
Number of lamps	2
Light output in emergency operation (lm)	89
Average lifespan light source (hours)	100.000
Colour of light	White
Colour temperature (K)	6350
CRI	73
Protection class	II
Degree of protection (IP)	65
With remote switch connection	No
Wiring system	Maintained / non-maintained circuit
Type of indicator	Only single-sided
Labelling type	Insert sheet/plate
Recognition distance (m)	25
Circuit	Other
Impact strength (IK)	10
Power consumption maintained mode (W)	3,5
Apparent power consumption maintained mode (VA)	8
Nominal current (mA)	29,6
Inrush Current (A - 0.1ms)	7
Powerfactor	0,45

Temperature range (°C) 0 ~ +35

**Article Details**

Product class Emergency luminaire  
E-code EC001957  
Discount group 30406  
Harmonized code 9405408440  
GLN 8713812000008

**Ordering information**

Orderable Yes  
Order-Unit Pieces  
Minimum order quantity 1  
Order Increment 1

**Supply Information**

Weight (kg) 1,455  
Packaging Cardboard box  
Packaging dimensions (LxWxH) (mm) 426 x 188 x 111