



TYPE APPROVAL CERTIFICATE

Certificate No:
TAE00001AF
Revision No:
4

This is to certify:

That the Contactor

with type designation(s)
AF9 to AF96 3 pole contactors, AF9 to AF80 4 pole contactors

Issued to
ABB France
Chassieu, France

is found to comply with
DNV rules for classification – Ships, offshore units, and high speed and light craft

Application :

Products approved by this certificate are accepted for installation on all vessels classed by DNV.

Type	Rated voltage (V)	Rated current (A)	Frequency (Hz)
AF9 to AF96 3 pole contactors	600 / 690	7 to 57 (AC-3 690 V)	50 / 60
AF9 to AF80 4 pole contactors	600 / 690	25 to 125 (AC-1)	50 / 60

Issued at **Høvik** on **2022-07-05**

for **DNV**

This Certificate is valid until **2026-06-30**.

DNV local station: **France CMC**

Approval Engineer: **Nicolay Horn**

.....
Marta Alonso Pontes
Head of Section

This Certificate is subject to terms and conditions overleaf. Any significant change in design or construction may render this Certificate invalid. The validity date relates to the Type Approval Certificate and not to the approval of equipment/systems installed.

LEGAL DISCLAIMER: Unless otherwise stated in the applicable contract with the holder of this document, or following from mandatory law, the liability of DNV AS, its parent companies and their subsidiaries as well as their officers, directors and employees ("DNV") arising from or in connection with the services rendered for the purpose of the issuance of this document or reliance thereon, whether in contract or in tort (including negligence), shall be limited to direct losses and under any circumstance be limited to 300,000 USD.



Name and place of manufacturer

ABB France Chassieu, France	ABB Xinhui Low voltage Switchgear Co Ltd. Jiangmen City, Jinguzhou Industrial Development Zone Guangdong Province, China
-----------------------------------	--

Product description

AF09 ... AF96 3 pole contactors AC/DC operated – with screw, spring or push-in terminal:

Contactor type	AF(S)9	AF(S)12	AF(S)16	AF(S)26	AF(S)30	AF(S)38
Maximum rated voltage Ue (V AC)	690	690	690	690	690	690
Rated frequency (Hz)	50/60	50/60	50/60	50/60	50/60	50/60
Rated insulation voltage (V)	690*	690*	690*	690*	690*	690*
Main contacts:						
Rated operational current AC-1 40 °C	25 A	28 A	30 A	45 A	50 A	50 A
AC3 Utilization category:						
Rated power AC-3 400 V (kW)	4	5.5	7.5	11	15	18.5
Rated operational current AC-3 400 V	9 A	12 A	18 A	26 A	32 A	38 A
Rated power AC-3 690 V (kW)	5.5	7.5	9	15	18.5	22
Rated operational current AC-3 690 V	7 A	9 A	10.5 A	17 A	21 A	24 A

Contactor type	AF(S)40	AF(S)52	AF(S)65	AF(S)80	AF(S)96
Maximum rated voltage Ue (V AC)	690	690	690	690	690
Rated frequency (Hz)	50/60	50/60	50/60	50/60	50/60
Rated insulation voltage (V)	690*	690*	690*	1000	1000
Main contacts:					
Rated operational current AC-1 40 °C	70 A	100 A	105 A	125 A	130 A
AC3 Utilization category:					
Rated power AC-3 400 V (kW)	18.5	22	30	37	45
Rated operational current AC-3 400 V	40 A	53 A	65 A	80 A	96 A
Rated power AC-3 690 V (kW)	22	30	37	45	55
Rated operational current AC-3 690 V	25 A	35 A	39 A	49 A	57 A

AF09 ... AF80 4 pole contactors AC/DC operated – with screw terminal:

Contactor type	AF09	AF16	AF26	AF38	AF40	AF52	AF80
Maximum rated voltage Ue (V AC)	690	690	690	690	690	690	690
Rated frequency (Hz)	50/60	50/60	50/60	50/60	50/60	50/60	50/60
Rated insulation voltage (V)	690*	690*	690*	690*	690*	690*	1000
Main contacts:							
Rated operational current AC-1 40 °C	25 A	30 A	45 A	55 A	70 A	100 A	125 A

* See Application / limitation

Application/Limitation

With Uimp=6kV the max. rated voltage is 600 V when used in IT (ship) net. It can be used in applications with directly earthed systems with rated voltage of 400/690 V.

Type Approval documentation

Technical info :

«AFS contactors for safety applications» ABB catalogue no. 1SBC100208C0201 issued 2017-11.

“Motor protection and control – Manual motor starters, contactors and overload relays” ABB catalogue issued July 2016.

“AF40... AF96 3-pole contactors”, parts of ABB catalogue “Summary table of electrical data of products”, dated 2011-11-02. Part of CD “AA France Approval DNV Range AF, dated 2011-11-10.

Test reports:

Intertek test report nos. 1621944STO-001 Ed.1 issued 2017-09-28, 2021525STO-001 & 2021526STO-001 issued 2020-09-17, 2021527STO-001 issued 2020-06-16. 1712881STO-001 issued 2017-06-19, 2020464STO-002 issued 2021-06-14, 2020464STO-001 issued 2020-06-29, Intertek Semko AB test report nos 1210336-1 dated 2013-01-31, 1210336-2 dated 2013-01-30, 1210336-3 dated 2013-01-29 & 1210336-5 dated 2013-02-13

Parts of of CD "AA France Approval DNV Range AF, dated 2011-11-10.

Tests carried out

Type tests in accordance with IEC 60947-4-1. Environmental tests in accordance with DNV Standard for Certification No. 2.4 (Vibration, Dry heat, damp heat and cold)

Marking of product

ABB France – Type designation – Ratings

Periodical assessment

The scope of the periodical assessment is to verify that the conditions stipulated for the Type approval are complied with and that no alterations are made to the product design or choice of materials.

The main elements of the assessment are:

- Inspection on factory samples, selected at random from the production line (where practicable)
- Results from Routine tests (RT) checked (if not available tests according to RT to be carried out)
- Review of type approval documentation
- Review of possible change in design, materials and performance
- Ensuring traceability between manufacturer's product type marking and Type Approval Certificate.

Assessment to be performed at 2 and 3.5 year and at renewal.

END OF CERTIFICATE