

---

 TECHNICAL DATA SHEET

# PMA Accessories - BGL - Tube clamps

## One-piece

### PMA



CE

#### Applications:

- In wide range of applications in all industries

#### Features & Benefits:

- Integrated rib provides axial strain relief
- Allows turning of the conduit thus avoiding torsion stresses
- Pre-fixation on the conduit possible
- Allows solid fixation with two screws
- Fits both conduit profiles - fine (T) and coarse (G)
- No corrosion

#### Materials:

- High-grade, specially formulated polyamide 6

#### Compatible with:

- PMAFLEX Pro Conduits
- PMAFLEX Multilayer Conduits
- PMAFLEX Conduits
- PMA Smart Line Conduits

#### Weathering resistance:

- Very good UV resistance and weathering characteristics, particularly in black

#### Colour:

- Black
- Grey

#### Chemical properties:

- Please refer to [www.pma.ch](http://www.pma.ch) (Technical Information / Chemical Resistance)

#### Environmental properties:


- Free from halogens and cadmium
- RoHS and REACH compliant

**Product selection:**

Part no.		Conduit size	Dimensions in mm (nom.)					Weight	Packing unit
black	grey		H	E	A	B	M		
BGL-07	SGL-07	7	13.5	12.5	25.0	13.0	M4	0.2	100
BGL-10	SGL-10	10	16.0	13.5	27.0	13.0	M5	0.2	100
BGL-12	SGL-12	12	19.5	15.5	31.0	13.0	M6	0.3	100
BGL-17	SGL-17	17	25.5	20.0	39.5	16.0	M5	0.4	100
BGL-23	SGL-23	23	34.0	25.0	49.0	16.0	M5	0.6	100
BGL-29	SGL-29	29	40.0	29.0	57.0	19.0	M6	0.9	100

For larger sizes please see GH product range, data sheet No. 60025

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time



Mechanical Properties:	Value:	Test parameters:	Test method:
Tensile modulus	1'200 ... 3'700 N/mm <sup>2</sup>		ISO 527
Tensile strength	45 ... 65 N/mm <sup>2</sup>		ISO 527
Notched bar impact test	4 ... 20 kJ/m <sup>2</sup>		ISO 180/1C

Thermal properties:	Value:	Test parameters:	Test method:
Continuous application temperature	-50 ... +105°C		PMA DO 9.21-4510
Upper application temperature	+120°C	(20'000 h)	PMA DO 9.21-4360
Short-term	+160°C	(168 h)	PMA DO 9.21-4360

ABB Switzerland Ltd,  
PMA Cable Protection  
Aathalstrasse 90  
8610 Uster, Switzerland  
Phone: +41 58 585 00 11  
pma-info@ch.abb.com  
www.pma.ch

Let's write the future.  
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

