
DATA SHEET

AI561

Analog Input Module




1 Ordering Data

Part no.	Description	Product Life Cycle Phase *)
1TNE 968 902 R1101	AI561, analog input module, 4 AI, U/I	Active
1TNE 968 901 R3101	Terminal block TA563-9, 9 pins, screw front, cable side, 6 pieces per unit	Active
1TNE 968 901 R3102	Terminal block TA563-11, 11 pins, screw front, cable side, 6 pieces per unit	Active
1TNE 968 901 R3103	Terminal block TA564-9, 9 pins, screw front, cable front, 6 pieces per unit	Active
1TNE 968 901 R3104	Terminal block TA564-11, 11 pins, screw front, cable front, 6 pieces per unit	Active
1TNE 968 901 R3105	Terminal block TA565-9, 9 pins, spring front, cable front, 6 pieces per unit	Active
1TNE 968 901 R3106	Terminal block TA565-11, 11 pins, spring front, cable front, 6 pieces per unit	Active

*) *For planning and commissioning of new installations use modules in Active status only.*

2 Dimensions



The dimensions are in mm and in brackets in inch.

3 Technical Data

The System Data of AC500-eCo apply ↳ *Chapter 4 "System Data AC500-eCo" on page 4*

Only additional details are therefore documented below.

Parameter		Value
Process supply voltage L+		
	Connections	Terminal 19 for L+ (+24 VDC) and terminal 20 for M (0 V)
	Rated value	24 VDC
	Current consumption via L+ terminal	0.1 A
	Inrush current (at power up)	0.05 A^2s
	Max. ripple	5 %
	Protection against reversed voltage	Yes
	Protection fuse for L+	Recommended
Current consumption from 24 VDC power supply at the terminals UP/L+ and ZP/M of the CPU/bus module		Ca. 10 mA
Galvanic isolation		No
Surge-voltage (max.)		35 VDC for 0.5 s

Parameter	Value
Max. power dissipation within the module	2.7 W
Weight	Ca. 120 g
Mounting position	Horizontal or vertical
Cooling	The natural convection cooling must not be hindered by cable ducts or other parts in the switchgear cabinet.

NOTICE!

Attention:

All I/O channels (digital and analog) are protected against reverse polarity, reverse supply, short circuit and continuous overvoltage up to 30 VDC.

3.1 Technical Data of the Analog Inputs

Parameter		Value	
Number of channels per module		4 individually configurable voltage or current inputs	
Distribution of channels into groups		1 (4 channels per group)	
Resolution			
	Unipolar	Voltage: 0 V...+5 V; 0 V...+10 V: 12 bits Current 0 mA...20 mA; 4 mA...20 mA: 12 bits	
	Bipolar	Voltage -2.5 V...+2.5 V; -5 V...+5 V: 11 bits plus sign	
Connection of the signals I0- to I3-		Terminals 3, 6, 9, 12	
Connection of the signals I0+ to I3+		Terminals 2, 5, 8, 11	
Input type		Differential	
Galvanic isolation		No galvanic isolation between the inputs and the I/O bus	
Common mode input range		Signal voltage plus common mode voltage must be within ±12 V	
Indication of the input signals		No	
Channel input resistance		Voltage: > 1 MΩ Current: ca. 250 Ω	
Conversion error of the analog values caused by non-linearity, adjustment error at factory and resolution within the normal range		Typ.	±0.5 % of full scale (voltage) ±0.5 % of full scale (current 0 mA...20 mA) ±0.7 % of full scale (current 4 mA...20 mA) at 25 °C
		Max.	±2 % of full scale (all ranges) at 0 °C...60 °C or EMC disturbance
Time constant of the input filter		Voltage: 300 µs Current: 300 µs	

Parameter		Value
Relationship between input signal and hex code		
Analog to digital conversion time		Typ. 500 µs per channel
Unused inputs		Can be left open and should be configured as "unused"
Input data length		8 bytes
Overvoltage protection		Yes, up to 30 VDC only for voltage input
Max. cable length (conductor cross section > 0,14 mm^2)		
	Unshielded wire	10 m
	Shielded wire	100 m

4 System Data AC500-eCo

4.1 Environmental Conditions

Table 1: Process and Supply Voltages

Parameter		Value
24 VDC		
	Voltage	24 V (-15 %, +20 %)
	Protection against reverse polarity	Yes
100 VAC		
	Voltage	100 V (-15 %, +10 %)
	Frequency	50/60 Hz (-6 %, +4 %)
230 VAC		
	Voltage	230 V (-15 %, +10 %)
	Frequency	50/60 Hz (-6 %, +4 %)
100...240 VAC wide range supply		
	Voltage	100 V...240 V (-15 %, +10 %)
	Frequency	50/60 Hz (-6 %, +4 %)
Allowed interruptions of power supply, according to EN 61131-2		
	DC supply	Interruption < 10 ms, time between 2 interruptions > 1 s, PS2
	AC supply	Interruption < 0.5 periods, time between 2 interruptions > 1 s

NOTICE!
Exceeding the maximum power supply voltage (> 30 VDC) for process or supply voltages could lead to unrecoverable damage of the system. The system could be destroyed.

Parameter		Value
Temperature		
	Operating	0 °C...+60 °C (horizontal mounting of modules) 0 °C...+40 °C (vertical mounting of modules and output load reduced to 50 % per group)
	Storage	-40 °C...+70 °C
	Transport	-40 °C...+70 °C
Humidity		Max. 95 %, without condensation
Air pressure		
	Operating	> 800 hPa / < 2000 m
	Storage	> 660 hPa / < 3500 m

4.2 Creepage Distances and Clearances

The creepage distances and clearances meet the requirements of the overvoltage category II, pollution degree 2.

4.3 Insulation Test Voltages, Routine Test

According to EN 61131-2

Parameter	Value	
200 V...240 V circuits against other circuitry	2500 V	1.2/50 µs
100 V...127 V circuits against other circuitry	1500 V	1.2/50 µs
100 V...240 V circuits against other circuitry	2500 V	1.2/50 µs
24 V circuits (supply, 24 V inputs/outputs, analogue inputs/ outputs), if they are electrically isolated against other circuitry	500 V	1.2/50 µs
COM interfaces, electrically isolated	500 V	1.2/50 µs
COM interfaces, electrically not isolated	Not applicable	Not applicable
FBP interface	500 V	1.2/50 µs
Ethernet	500 V	1.2/50 µs
ARCNET	500 V	1.2/50 µs
200 V... 240 V circuits against other circuitry	1350 V	AC 2 s
100 V circuits against other circuitry	820 V	AC 2 s
100 V...240 V circuits against other circuitry	1350 V	AC 2 s

Parameter	Value	
24 V circuits (supply, 24 V inputs/outputs, analogue inputs/outputs), if they are electrically isolated against other circuitry	350 V	AC 2 s
COM interfaces, electrically isolated	350 V	AC 2 s
COM interfaces, electrically not isolated	Not applicable	Not applicable
FBP interface	350 V	AC 2 s
Ethernet	350 V	AC 2 s
ARCNET	350 V	AC 2 s

4.4 Power Supply Units

For the supply of the modules, power supply units according to PELV specifications must be used.

4.5 Electromagnetic Compatibility

Electromagnetic Compatibility		
Device suitable for:		
	Industrial applications	Yes
	Domestic applications	No
Immunity against electrostatic discharge (ESD):		According to IEC 61000-4-2, zone B, criterion B
	Electrostatic voltage in case of air discharge	8 kV
	Electrostatic voltage in case of contact discharge	4 kV, in a closed switch-gear cabinet 6 kV [1])
	ESD with communication connectors	In order to prevent operating malfunctions, it is recommended, that the operating personnel discharge themselves prior to touching communication connectors or perform other suitable measures to reduce effects of electrostatic discharges.
Immunity against the influence of radiated (CW radiated):		According to IEC 61000-4-3, zone B, criterion A
	Test field strength	10 V/m
Immunity against transient interference voltages (burst):		According to IEC 61000-4-4, zone B, criterion B
	Supply voltage units (DC)	2 kV
	Supply voltage units (AC)	2 kV
	Digital inputs/outputs (24 VDC)	1 kV
	Digital inputs/outputs (120 VAC...2400 VAC)	2 kV
	Analog inputs/outputs	1 kV
	CS31 system bus	1 kV
	Serial RS-485 interfaces (COM)	1 kV

Electromagnetic Compatibility		
	Serial RS-232 interfaces (COM, not for PM55x and PM56x)	1 kV
	ARCNET	1 kV
	FBP	1 kV
	Ethernet	1 kV
	I/O supply, DC-out	1 kV
Immunity against the influence of line-conducted interferences (CW conducted):		According to IEC 61000-4-6, zone B, criterion A
	Test voltage	3 V zone B, 10 V is also met.
	High energy surges	According to IEC 61000-4-5, zone B, criterion B
	Power supply AC	2 kV CM / 1 kV DM [2])
	Power supply DC	1 kV CM / 0.5 kV DM [2])
	DC I/O supply, add. DC-supply-out	0.5 kV CM / 0.5 kV DM [2])
	Buses, shielded	1 kV CM [2])
	AC I/O unshielded	2 kV CM / 1 kV DM [2])
	I/O analog, I/O DC unshielded	1 kV CM / 0.5 kV DM [2])
	Radiation (radio disturbance)	According to IEC 55011, group 1, class A

[1]) High requirement for shipping classes are achieved with additional specific measures (see specific documentation).

[2]) CM = Common Mode, DM = Differential Mode

4.6 Mechanical Data

Parameter	**Value**
Mounting	Horizontal
Degree of protection	IP 20 (if all terminal screws are tightened)
Housing	Classification V-2 according to UL 94
Vibration resistance acc. to EN 61131-2	all three axes (DIN rail mounting) 5 Hz...8.4 Hz, continuous 3.5 mm 8.4 Hz...150 Hz, continuous 1 g
Shock test	All three axes 15 g, 11 ms, half-sinusoidal
Mounting of the modules:	
DIN rail according to DIN EN 50022	35 mm, depth 7.5 mm or 15 mm
Mounting with screws	Screws with a diameter of 4 mm
Fastening torque	1.2 Nm

4.7 Approvals and certifications

Information on approvals and certificates can be found in the corresponding chapter of the *Main catalog, PLC Automation*.

—
ABB Automation Products GmbH
Eppelheimer Str. 82
69123 Heidelberg, Germany
Telephone: +49 (0)6221 701 1444
Fax: +49 (0)6221 701 1382
E-mail: plc.support@de.abb.com
abb.com/plc

—
© Copyright 2017-2018 ABB.

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.