
TECHNICAL DATA SHEET

Terminals, blade

Nylon-insulated, double crimp

Spec-Kon[®]



Nylon-insulated blade terminals for wire termination of copper conductors ranging from 0.5mm² to 6mm²

Certifications / Standards:

Features:

- Easy entry double crimp
- Corrosive resistant plating
- Color coded to wire size range

Maximum rating:

- 105°C Max
- 600 volts
- Copper conductors only

Application tool:

- ERG9004

Conforms to:

- IEC 60352-2

Materials / Finishes:

- Copper terminal
- Electro-Tin plated
- Nylon insulation

Terminals, blade:
Nylon-insulated, double crimp

Product selection

Drawing	Part no:	Wire size range (mm ²)	Color	Dimensions (mm)				Crimping tool
				L	F	W	D	
	B1.5-2820NDC	0.5 - 1.5	Red	19.5	9.0	2.8	4.4	ERG9004
	B1.5-2321NDC	0.5 - 1.5	Red	20.5	10.0	2.3	4.4	
	B1.5-3022NDC	0.5 - 1.5	Red	21.5	11.0	3.0	4.4	
	B1.5-3024NDC	0.5 - 1.5	Red	23.5	13.0	2.4	4.4	
	B1.5-3025NDC	0.5 - 1.5	Red	24.5	14.0	2.4	4.4	
	B1.5-2029NDC	0.5 - 1.5	Red	28.5	18.0	2.0	4.4	
	B1.5-2229NDC	0.5 - 1.5	Red	28.5	18.0	2.2	4.4	
	B2.5-2820NDC	1.5 - 2.5	Blue	19.5	9.0	2.8	5.0	
	B2.5-2421NDC	1.5 - 2.5	Blue	20.5	10.0	2.3	5.0	
	B2.5-2424NDC	1.5 - 2.5	Blue	23.5	13.0	2.4	5.0	
	B2.5-3025NDC	1.5 - 2.5	Blue	24.5	14.0	2.4	5.0	
	B2.5-2029NDC	1.5 - 2.5	Blue	28.5	18.0	2.0	5.0	
	B2.5-2229NDC	1.5 - 2.5	Blue	28.5	18.0	2.2	5.0	
	B6-2823NDC	4.0 - 6.0	Yellow	22.7	10.0	2.8	7.0	
	B6-4027NDC	4.0 - 6.0	Yellow	26.7	14.0	4.0	7.0	
	B6-4527NDC	4.0 - 6.0	Yellow	26.7	14.0	4.5	7.0	
	B6-2031NDC	4.0 - 6.0	Yellow	30.7	18.0	2.0	7.0	
	B6-4531NDC	4.0 - 6.0	Yellow	30.7	18.0	4.5	7.0	

Note: Products must be installed in accordance with applicable national and local electrical codes.