

## TECHNICAL DATA SHEET

**PMA Accessories - ME-M/M - Enlarger**  
Hexagonal, metal metric thread**PMA****Features & Benefits:**

- For enlargement of an existing metric thread

**Materials:**

- Nickel-plated brass

**Compatible with:**

- PMAFIX Pro, PMAFIX, PMA Smart Line fittings

**Temperature range:**

- -60°C ... +200°C

**Conforms to:**

- Thread according to EN 60423

**Environmental properties:**

- Free from halogens and cadmium
- RoHS and REACH compliant

**Product selection:**

Part no.	Thread size		Dimensions in mm (nom.)					Weight	Packing unit
	metric (outside)	metric (inside)	g	g2	L	d1	SW	kg/100 pcs	pcs/PU
M12M16M	M12 x 1.5	M16 x 1.5	5.0	7.0	16.0	8.0	18.0	1.0	100
M16M20M	M16 x 1.5	M20 x 1.5	5.0	7.5	16.5	12.0	22.0	1.4	100
M20M25M	M20 x 1.5	M25 x 1.5	6.0	8.0	18.5	15.0	27.0	2.3	50
M25M32M	M25 x 1.5	M32 x 1.5	7.0	9.0	20.5	21.0	34.0	2.4	25
M32M40M	M32 x 1.5	M40 x 1.5	8.0	10.0	23.5	26.0	42.0	5.1	25
M40M50M	M40 x 1.5	M50 x 1.5	8.0	13.0	30.0	34.0	52.0	9.8	10
M50M63M	M50 x 1.5	M63 x 1.5	9.0	16.0	32.5	44.0	65.0	11.0	10

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time




ABB Switzerland Ltd,  
PMA Cable Protection  
Aathalstrasse 90  
8610 Uster, Switzerland  
Phone: +41 58 585 00 11  
pma-info@ch.abb.com  
www.pma.ch

Let's write the future.  
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

