


Spacingtabellen

SER-(C/D)SI - 5 LUX







Middelpunt object - plafond (C)	Armatuur tot muur (L)
0.5	0.8
1.0	1.2
1.5	1.7
2.0	2.0





Spacingtabel / Spacing tabel

DIB 325/140B/1

DIB B - 0.5 LUX

Hoogte (m)				
2.8	4.1	10.5	3.3	8.2
3.0	4.2	10.7	3.4	8.4
3.5	4.4	11.2	3.5	8.9
4.0	4.4	11.7	3.6	9.4
6.0	4.2	12.6	2.9	10.2
8.0	-	12.4	-	8.8
10.0	-	6.8	-	4.7





DIB B - 1 LUX

Hoogte (m)				
2.8	3.1	8.3	2.6	6.6
3.0	3.2	8.5	2.6	6.8
3.5	3.3	8.7	2.5	7.1
4.0	3.1	8.8	2.2	7.3
6.0	-	8.3	-	5.7





Spacingtabel / Spacing tabel

DIB 325/140A/1

DIB A- 0.5 LUX

Hoogte (m)				
2.8	3.7	9.8	3.3	8.4
3.0	3.8	9.9	3.4	8.6
3.5	3.9	10.2	3.6	9.0
4.0	4.0	10.5	3.7	9.5
6.0	3.4	11.3	3.1	10.6
8.0	0.4	10.2	0.4	9.4
10.0	-	6.3	-	6.4





DIB A - 1 LUX

Hoogte (m)				
2.8	2.8	7.4	2.6	6.7
3.0	2.8	7.5	2.6	6.9
3.5	2.8	7.8	2.6	7.2
4.0	2.5	8.0	2.4	7.4
6.0	-	6.8	-	6.2
8.0	-	0.8	-	0.8





Spacingtabel / Spacing tabel

CIB-TL 325/140/HF

CIB 325/140/HF - 0.5 LUX

Hoogte (m)				
2.8	4.2	10.7	3.4	8.3
3.0	4.3	10.9	3.5	8.5
3.5	4.5	11.4	3.6	9.0
4.0	4.5	12.0	3.7	9.5
6.0	4.4	12.9	3.1	10.6
8.0	-	13.0	-	9.3
10.0	-	7.9	-	5.5





CIB 325/140/HF - 1 LUX

Hoogte (m)				
2.8	3.2	8.4	2.6	6.7
3.0	3.2	8.6	2.6	6.9
3.5	3.2	8.9	2.6	7.2
4.0	3.2	9.1	2.3	7.4
6.0	-	8.9	-	6.1





Spacingtabel / Spacing tabel

CIB-TL 325/140/24

CIB 325/140/24 - 0.5 LUX

Hoogte (m)				
2.8	4.3	11.1	3.4	8.6
3.0	4.4	11.3	3.5	8.8
3.5	4.6	11.8	3.7	9.3
4.0	4.7	12.3	3.8	9.8
6.0	4.8	13.4	3.4	11.0
8.0	2.1	13.9	0.8	10.1
10.0	-	9.9	-	6.7





CIB 325/140/24 - 1 LUX

Hoogte (m)				
2.8	3.3	8.7	2.7	6.9
3.0	3.4	8.9	2.8	7.1
3.5	3.4	9.3	2.7	7.5
4.0	3.5	9.4	2.5	7.7
6.0	-	9.5	-	6.8
8.0	-	4.1	-	1.5





Spacingtabel / Spacing tabel

NBN

NBN - 0.5 LUX

Hoogte (m)				
2.5	3.9	10.9	3.1	7.8
3.0	3.8	11.2	3.4	8.4
3.5	3.9	11.2	3.5	8.9
4.0	4.0	10.7	3.7	9.3
4.5	4.1	10.8	3.7	9.8
5.0	3.9	11.0	3.6	10.0
5.5	3.7	11.1	3.5	10.3





NBN - 1 LUX

Hoogte (m)				
2.5	2.7	7.8	2.5	6.3
3.0	2.8	7.6	2.6	6.8
3.5	2.8	7.7	2.6	7.1
4.0	2.6	7.9	2.4	7.4
4.5	2.3	8.1	2.1	7.4
5.0	1.7	7.8	1.7	7.3
5.5	1.2	7.5	1.2	6.9





Spacingtabel / Spacing tabel

NB

NB - 0.5 LUX

Hoogte (m)				
2.5	4.7	12.5	3.1	7.6
3.0	4.6	13.0	3.3	8.1
3.5	4.3	13.4	3.5	8.6
4.0	4.2	13.6	3.6	9.2
4.5	4.3	12.4	3.5	9.6
5.0	4.4	12.0	3.4	9.9
5.5	4.3	11.9	3.2	10.1





NB - 1 LUX

Hoogte (m)				
2.5	3.0	9.5	2.5	6.1
3.0	3.0	9.2	2.5	6.7
3.5	3.1	8.5	2.4	6.9
4.0	3.0	8.4	2.2	7.2
4.5	2.6	8.6	1.7	7.1
5.0	1.6	8.7	1.2	6.8





Spacingtabel / Spacing tabel

NB 08/24

NB 08/24 - 0.5 LUX

Hoogte (m)				
2.5	4.3	11.5	3.3	8.1
3.0	4.0	11.9	3.5	8.7
3.5	4.1	12.3	3.7	9.3
4.0	4.2	11.6	3.9	9.7
4.5	4.3	11.5	4.0	10.2
5.0	4.3	11.7	3.9	10.6
5.5	4.2	11.8	3.9	10.9





NB 08/24 - 1 LUX

Hoogte (m)				
2.5	2.9	8.7	2.6	6.6
3.0	3.0	8.1	2.8	6.1
3.5	3.1	8.2	2.8	7.5
4.0	2.9	8.4	2.7	7.7
4.5	2.7	8.6	2.5	8.0
5.0	2.3	8.6	2.1	7.9
5.5	1.7	8.4	1.7	7.7





Spacingtabel / Spacing tabel

NB 08/HF

NB 08/HF - 0.5 LUX

Hoogte (m)				
2.5	5.1	11.2	3.2	7.9
3.0	4.9	11.5	3.4	8.5
3.5	4.0	11.6	3.6	9.0
4.0	4.1	10.9	3.8	9.5
4.5	4.1	11.1	3.8	10.0
5.0	4.1	11.2	3.8	10.2
5.5	3.9	11.4	3.6	10.5





NB 08/HF - 1 LUX

Hoogte (m)				
2.5	2.8	8.2	2.6	6.4
3.0	2.9	7.8	2.7	6.9
3.5	2.9	7.9	2.7	7.2
4.0	2.7	8.1	2.5	7.5
4.5	2.4	8.3	2.2	7.6
5.0	1.9	8.1	1.9	7.5
5.5	1.4	7.8	1.4	7.2





Spacingtabel / Spacing tabel

(I/O)LN





(I/O)LN-1 - 0.5 LUX

Hoogte (m)				
2.5	6.4	16.3	2.9	7.2
3.0	6.7	17.4	3.1	7.8
3.5	6.7	18.0	3.3	8.3
4.0	6.7	18.6	3.3	8.8
4.5	6.5	18.9	3.2	9.0
5.0	6.2	19.0	3.1	9.3
5.5	5.8	19.0	2.8	9.3





(I/O)LN - 1 LUX

Hoogte (m)				
2.5	4.7	12.7	2.3	5.9
3.0	4.7	13.3	2.3	6.3
3.5	4.4	13.4	2.2	6.5
4.0	4.0	13.4	1.9	6.6
4.5	1.6	13.1	1.4	6.5
5.0	0.3	12.4	0.1	6.1
5.5	-	11.5	-	5.6

(I/O)LN-1 + PPL - 0.5 LUX

Hoogte (m)				
2.5	6.2	15.5	2.2	5.9
3.0	6.5	16.6	2.2	6.1
3.5	6.7	17.5	2.2	6.2
4.0	6.7	18.2	1.9	6.2
4.5	6.7	18.6	1.5	6.1
5.0	6.6	19.0	0.7	5.9
5.5	6.4	19.2	-	5.5





(I/O)LN-1 + PPL - 1 LUX

Hoogte (m)				
2.5	4.8	12.4	1.5	4.4
3.0	4.7	13.0	1.2	4.4
3.5	4.7	13.5	0.6	4.2
4.0	4.5	13.5	-	3.8
4.5	-	13.3	-	3.0





Spacingtabel / Spacing tabel

(I/O)L

(I/O)L - 0.5 LUX

Hoogte (m)				
2.5	6.5	16.6	3.0	7.3
3.0	6.8	17.8	3.2	7.9
3.5	6.9	18.4	3.3	8.4
4.0	6.9	19.0	3.4	8.9
4.5	6.8	19.4	3.4	9.2
5.0	6.5	19.5	3.2	9.5
5.5	6.1	19.6	3.0	9.6





(I/O)L - 1 LUX

Hoogte (m)				
2.5	4.9	13.0	2.4	6.0
3.0	4.8	13.6	2.4	6.4
3.5	4.6	13.8	2.3	6.7
4.0	4.2	13.9	2.0	6.8
4.5	2.2	13.5	1.6	6.7
5.0	0.9	13.1	0.7	6.4
5.5	-	12.2	-	6.0





Spacingtabel / Spacing tabel

(I/O)L-230HF





(I/O)L-230HF - 0.5 LUX

Hoogte (m)				
2.5	6.7	16.8	3.0	7.5
3.0	7.0	18.2	3.3	8.1
3.5	7.1	18.8	3.4	8.6
4.0	7.1	19.4	3.5	9.1
4.5	7.0	19.9	3.5	9.4
5.0	6.8	20.0	3.4	9.7
5.5	6.4	20.1	3.2	9.9





(I/O)L-230HF - 1 LUX

Hoogte (m)				
2.5	5.0	13.3	2.4	6.1
3.0	5.0	13.9	2.5	6.6
3.5	4.8	14.2	2.4	6.8
4.0	4.4	14.2	2.2	7.0
4.5	2.8	14.0	1.8	6.9
5.0	1.2	13.7	1.1	6.7
5.5	-	12.8	-	6.3

(I/O)L-230HF + PPL-0.5 LUX

Hoogte (m)				
2.5	6.5	16.0	2.3	6.1
3.0	6.8	17.2	2.3	6.4
3.5	7.0	18.2	2.3	6.5
4.0	7.2	19.0	2.1	6.6
4.5	7.1	19.5	1.8	6.6
5.0	7.0	20.0	1.3	6.4
5.5	6.9	20.2	-	6.1





(I/O)L-230HF + PPL- 1 LUX

Hoogte (m)				
2.5	5.0	12.9	1.6	4.6
3.0	5.1	13.6	1.4	4.8
3.5	5.0	14.1	1.0	4.6
4.0	4.9	14.3	-	4.2
4.5	4.6	14.2	-	3.6
5.0	-	14.0	-	2.6





Spacingtabel / Spacing tabel

(I/O)L-24





(I/O)L-24 - 0.5 LUX

Hoogte (m)				
2.5	6.9	17.2	3.1	7.7
3.0	7.2	18.7	3.4	8.3
3.5	7.4	19.4	3.5	8.8
4.0	7.4	20.0	3.6	9.3
4.5	7.4	20.7	3.6	9.7
5.0	7.2	20.9	3.6	10.0
5.5	6.9	21.0	3.4	10.2





(I/O)L-24 - 1 LUX

Hoogte (m)				
2.5	5.2	14.1	2.6	6.6
3.0	5.3	14.4	2.6	6.8
3.5	5.1	14.8	2.5	7.0
4.0	4.8	14.8	2.4	7.3
4.5	4.3	14.8	2.0	7.3
5.0	1.7	14.4	1.5	7.2
5.5	0.6	13.8	0.4	6.8

(I/O)L-24 + PPL - 0.5 LUX

Hoogte (m)				
2.5	6.6	16.4	2.4	6.3
3.0	7.0	17.6	2.4	6.6
3.5	7.3	18.7	2.4	6.8
4.0	7.5	19.6	2.3	6.9
4.5	7.5	20.2	2.0	6.9
5.0	7.4	20.7	1.6	6.8
5.5	7.3	21.0	0.8	6.5





(I/O)L-24 + PPL - 1 LUX

Hoogte (m)				
2.5	5.2	13.3	1.7	4.8
3.0	5.3	14.1	1.5	4.9
3.5	5.2	14.6	1.2	4.8
4.0	5.1	14.9	0.2	4.6
4.5	4.9	14.9	-	4.1
5.0	-	14.7	-	3.3





Spacingtabel / Spacing tabel

FM-1

FM - 0.5 LUX

Hoogte (m)				
2.8	4.1	10.5	3.3	8.2
3.0	4.2	10.7	3.4	8.4
3.5	4.4	11.2	3.5	8.9
4.0	4.4	11.7	3.6	9.4
6.0	4.2	12.6	2.9	10.2
8.0	-	12.4	-	8.8
10.0	-	6.8	-	4.7





FM - 1 LUX

Hoogte (m)				
2.8	3.1	8.3	2.6	6.6
3.0	3.2	8.5	2.6	6.8
3.5	3.3	8.7	2.5	7.1
4.0	3.1	8.8	2.2	7.3
6.0	-	8.3	-	5.7





Spacingtabel / Spacing tabel

FMN-1

FMN - 0.5 LUX

Hoogte (m)				
2.8	3.7	9.8	3.3	8.4
3.0	3.8	9.9	3.4	8.6
3.5	3.9	10.2	3.6	9.0
4.0	4.0	10.5	3.7	9.5
6.0	3.4	11.3	3.1	10.6
8.0	0.4	10.2	0.4	9.4
10.0	-	6.3	-	6.4





FMN - 1 LUX

Hoogte (m)				
2.8	2.8	7.4	2.6	6.7
3.0	2.8	7.5	2.6	6.9
3.5	2.8	7.8	2.6	7.2
4.0	2.5	8.0	2.4	7.4
6.0	-	6.8	-	6.2
8.0	-	0.8	-	0.8





Spacingtabel / Spacing tabel

FM 08/HF

FM 08/HF - 0.5 LUX

Hoogte (m)				
2.8	4.2	10.7	3.4	8.3
3.0	4.3	10.9	3.5	8.5
3.5	4.5	11.4	3.6	9.0
4.0	4.5	12.0	3.7	9.5
6.0	4.4	12.9	3.1	10.6
8.0	-	13.0	-	9.3
10.0	-	7.9	-	5.5





FM 08/HF - 1 LUX

Hoogte (m)				
2.8	3.2	8.4	2.6	6.7
3.0	3.2	8.6	2.6	6.9
3.5	3.3	8.9	2.6	7.2
4.0	3.2	9.1	2.3	7.4
6.0	-	8.9	-	6.1





Spacingtabel / Spacing tabel

FM 08/24

FM 08/24 - 0.5 LUX

Hoogte (m)				
2.8	4.3	11.1	3.4	8.6
3.0	4.4	11.3	3.5	8.8
3.5	4.6	11.8	3.7	9.3
4.0	4.7	12.3	3.8	9.8
6.0	4.8	13.4	3.4	11.0
8.0	2.1	13.9	0.8	10.1
10.0	-	9.9	-	6.7





FM 08/24 - 1 LUX

Hoogte (m)				
2.8	3.3	8.7	2.7	6.9
3.0	3.4	8.9	2.8	7.1
3.5	3.4	9.3	2.7	7.5
4.0	3.5	9.4	2.5	7.7
6.0	-	9.5	-	6.8
8.0	-	4.1	-	1.5





Spacingtabel / Spacing tabel

FIX FOX FCX

F(I/O/C)X - 0.5 LUX

Hoogte (m)				
2.0	2.2	5.2	2.2	4.9
2.5	2.6	5.9	2.6	5.7
3.0	2.8	6.6	2.9	6.5
3.5	3.0	7.2	3.1	7.3
4.0	3.1	7.7	3.1	8.1
4.5	3.1	8.1	2.8	8.5
5.0	2.9	8.5	2.4	8.8





F(I/O/C)X - 1 LUX

Hoogte (m)				
2.0	1.9	4.5	2.0	4.4
2.5	2.1	5.1	2.2	5.2
3.0	2.2	5.6	2.1	5.9
3.5	2.1	6.0	1.7	6.2
4.0	0.4	6.2	0.4	6.1





Spacingtabel / Spacing tabel

SER-(C/D)LI

SER-(C/D)LI - 0.5 LUX

Hoogte (m)				
2.0	4.5	10.2	1.3	3.8
2.5	5.2	11.8	1.3	3.7
3.0	5.9	13.3	1.3	3.7
3.5	6.5	14.7	1.3	3.6
4.0	7.0	16.0	1.3	3.6
4.5	7.5	17.3	1.3	3.6
5.0	8.0	18.4	1.2	3.6





SER-(C/D)LI - 1 LUX

Hoogte (m)				
2.0	4.0	9.0	0.9	2.6
2.5	4.6	10.5	0.9	2.6
3.0	5.2	11.8	0.9	2.6
3.5	5.6	12.9	0.9	2.6
4.0	6.0	14.1	0.8	2.6
4.5	6.4	15.1	0.7	2.5
5.0	6.7	16.0	0.5	2.5





Spacingtabel / Spacing tabel

SER-(C/W)WI

SER-(C/D)WI - 0.5 LUX

Hoogte (m)				
2.0	3.6	8.9	3.7	9.2
2.5	3.9	9.7	4.1	10.1
3.0	4.1	10.4	4.3	10.8
3.5	4.3	11.0	4.5	11.4
4.0	4.5	11.5	4.6	12.0
4.5	4.5	11.9	4.6	12.4
5.0	4.6	12.2	4.5	12.7





SER-(C/D)WI - 1 LUX

Hoogte (m)				
2.0	2.9	7.2	3.0	7.5
2.5	3.1	7.8	3.2	8.1
3.0	3.2	8.2	3.3	8.6
3.5	3.2	8.6	3.2	9.0
4.0	3.1	8.9	3.0	9.2
4.5	2.9	9.1	2.8	9.2
5.0	2.4	9.1	2.2	9.0





Spacingtabel / Spacing tabel

SER-CLO

SER-CLO(/24) - 0.5 LUX

Hoogte (m)				
2.5	5.0	10.7	1.4	3.3
3.0	5.9	12.4	1.6	3.6
3.5	6.7	14.1	1.7	4.0
4.0	7.4	15.8	1.8	4.3
4.5	8.1	17.5	1.9	4.6
5.0	8.9	19.1	2.0	4.9
5.5	9.6	20.5	2.1	5.1





SER-CLO(/24) - 1 LUX

Hoogte (m)				
2.5	4.8	10.0	1.2	2.8
3.0	5.5	11.7	1.3	3.1
3.5	6.2	13.4	1.4	3.4
4.0	6.9	14.8	1.5	3.7
4.5	7.5	16.3	1.5	3.9
5.0	8.1	17.7	1.5	4.1
5.5	8.8	19.1	1.4	4.2





Spacingtabel / Spacing tabel

SER-DLO

SER-DLO - 0.5 LUX

Hoogte (m)				
2.5	5.0	10.7	1.4	3.3
3.0	5.9	12.4	1.6	3.6
3.5	6.7	14.1	1.7	3.9
4.0	7.4	15.8	1.8	4.3
4.5	8.1	17.4	1.9	4.6
5.0	8.8	19.1	2.0	4.8
5.5	9.6	20.5	2.1	5.1





SER-DLO - 1 LUX

Hoogte (m)				
2.5	4.8	10.0	1.2	2.8
3.0	5.5	11.7	1.3	3.1
3.5	6.2	13.4	1.4	3.4
4.0	6.9	14.8	1.5	3.7
4.5	7.5	16.2	1.5	3.9
5.0	8.1	17.7	1.5	4.1
5.5	8.8	19.1	1.4	4.2





Spacingtabel / Spacing tabel

SER-CWO

SER-CWO(/24) - 0.5 LUX

Hoogte (m)				
2.5	3.7	7.9	3.7	7.9
3.0	4.2	9.2	4.2	9.2
3.5	4.7	10.4	4.6	10.4
4.0	5.0	11.5	4.9	11.5
4.5	4.9	12.4	4.2	12.4
5.0	4.0	13.2	3.6	13.2
5.5	3.7	13.9	3.3	13.8





SER-CWO(/24) - 1 LUX

Hoogte (m)				
2.5	3.3	7.4	3.3	7.4
3.0	3.6	8.5	3.5	8.5
3.5	2.8	9.3	2.6	9.3
4.0	2.6	9.9	2.2	9.9
4.5	-	9.8	-	8.4





Spacingtabel / Spacing tabel

SER-DWO

SER-DWO - 0.5 LUX

Hoogte (m)				
2.5	3.7	7.9	3.7	7.9
3.0	4.2	9.2	4.2	9.2
3.5	4.6	10.3	4.6	10.3
4.0	4.9	11.5	4.9	11.5
4.5	4.7	12.4	4.1	12.4
5.0	3.9	13.2	3.5	13.2
5.5	3.7	13.8	3.2	13.7





SER-DWO - 1 LUX

Hoogte (m)				
2.5	3.3	7.4	3.3	7.4
3.0	3.5	8.4	3.5	8.4
3.5	2.8	9.3	2.5	9.3
4.0	2.5	9.9	2.1	9.8
4.5	-	9.4	-	8.1





Spacingtabel / Spacing tabel

AQL 08/HF

AQL 08/HF - 0.5 LUX

Hoogte (m)				
2.5	5.6	13.9	3.5	8.6
3.0	6.1	14.2	3.7	9.2
3.5	6.5	15.3	3.9	9.8
4.0	7.0	16.5	4.1	10.3
4.5	7.3	17.4	4.1	10.9
5.0	7.5	18.2	4.2	11.2
5.5	7.8	19.8	4.1	11.4





AQL 08/HF - 1 LUX

Hoogte (m)				
2.5	4.6	11.3	2.8	7.0
3.0	5.0	12.2	2.9	7.5
3.5	5.3	13.1	3.0	7.9
4.0	5.5	13.9	2.9	8.1
4.5	5.6	14.5	2.7	8.2
5.0	5.5	15.1	2.4	8.4
5.5	5.3	15.6	2.1	8.2





Spacingtabel / Spacing tabel

AQL 08/24

AQL 08/24 - 0.5 LUX

Hoogte (m)				
2.5	5.5	13.3	3.4	8.3
3.0	5.9	14.4	3.6	8.9
3.5	6.4	15.5	3.8	9.5
4.0	6.8	16.4	3.9	10.1
4.5	7.0	17.3	4.0	10.5
5.0	7.3	18.1	4.0	10.8
5.5	7.5	19.0	3.9	11.0





AQL 08/24 - 1 LUX

Hoogte (m)				
2.5	4.5	11.0	2.7	6.8
3.0	4.9	11.9	2.8	7.3
3.5	5.1	12.8	2.8	7.6
4.0	5.3	13.5	2.7	7.8
4.5	5.4	14.1	2.5	7.9
5.0	5.2	14.6	2.2	7.9
5.5	4.8	14.9	1.7	7.8





Spacingtabel / Spacing tabel

AQL 08/1

AQL 08/1 - 0.5 LUX

Hoogte (m)				
2.5	5.1	12.3	3.1	7.7
3.0	5.5	13.4	3.3	8.3
3.5	5.9	14.4	3.4	8.8
4.0	6.2	15.2	3.5	9.2
4.5	6.5	16.1	3.4	9.5
5.0	6.6	16.8	3.3	9.7
5.5	6.7	17.3	3.1	9.8





AQL 08/1 - 1 LUX

Hoogte (m)				
2.5	4.2	10.2	2.4	6.3
3.0	4.5	11.1	2.5	6.6
3.5	4.6	11.8	2.4	6.8
4.0	4.7	12.4	2.1	6.9
4.5	4.5	12.9	1.8	6.9
5.0	4.1	13.1	1.2	6.7
5.5	3.8	13.3	-	6.2





Spacingtabel / Spacing tabel

AQL 08/3

AQL 08/3 - 0.5 LUX

Hoogte (m)				
2.5	4.7	11.3	2.8	7.0
3.0	5.1	12.3	2.9	7.6
3.5	5.4	13.2	3.0	8.0
4.0	5.6	14.0	2.9	8.2
4.5	5.7	14.7	2.8	8.3
5.0	5.7	15.2	2.5	8.5
5.5	5.4	15.7	2.2	8.4





AQL 08/3 - 1 LUX

Hoogte (m)				
2.5	3.8	9.4	2.1	5.7
3.0	4.0	10.2	2.0	5.9
3.5	4.0	10.7	1.8	6.0
4.0	3.7	11.2	1.4	5.9
4.5	3.4	11.4	0.5	5.6
5.0	2.6	11.3	-	5.0





Spacingtabel / Spacing tabel

AQL 02/LED

AQL 02 - 0.5 LUX

Hoogte (m)				
2.5	3.2	8.2	3.2	8.6
3.0	3.3	8.6	3.2	8.8
3.5	3.3	9.0	3.2	8.9
4.0	3.2	9.2	3.0	9.0
4.5	3.1	9.3	2.8	9.0
5.0	2.8	9.3	2.5	8.9
5.5	2.4	9.2	2.0	8.7





AQL 02 - 1 LUX

Hoogte (m)				
2.5	2.3	6.4	2.2	6.3
3.0	2.3	6.6	2.1	6.4
3.5	2.0	6.6	1.8	6.3
4.0	1.6	6.5	1.3	6.1





Spacingtabel / Spacing tabel

AQL 03/HF

AQL 03/HF - 0.5 LUX

Hoogte (m)				
2.5	5.3	12.6	2.7	7.1
3.0	5.9	13.8	2.7	7.5
3.5	6.3	14.9	2.6	7.6
4.0	6.5	16.0	2.4	7.6
4.5	6.3	17.1	2.2	7.5
5.0	5.9	17.8	1.9	7.3
5.5	5.7	18.4	1.4	7.0





AQL 03/HF - 1 LUX

Hoogte (m)				
2.5	4.5	10.6	1.8	5.4
3.0	4.6	11.7	1.6	5.3
3.5	4.2	12.6	1.3	5.2
4.0	4.0	13.1	0.8	4.8





Spacingtabel / Spacing tabel

AQL 03/1

AQL 03/1 - 0.5 LUX

Hoogte (m)				
2.5	5.0	11.8	2.4	6.5
3.0	5.5	13.0	2.3	6.7
3.5	5.8	14.1	2.1	6.7
4.0	5.5	15.1	1.9	6.6
4.5	5.1	15.9	1.6	6.4
5.0	5.0	16.3	1.0	6.0
5.5	4.9	16.0	-	5.6





AQL 03/1 - 1 LUX

Hoogte (m)				
2.5	4.1	10.0	1.5	4.7
3.0	3.7	10.9	1.2	4.6
3.5	3.6	11.5	0.8	4.3
4.0	3.4	11.1	-	3.8





Spacingtabel / Spacing tabel

AQL 11/24





AQL 11/24 - 0.5 LUX

Hoogte (m)				
2.5	6.2	14.9	4.6	10.8
3.0	6.8	16.3	5.0	11.9
3.5	7.3	17.4	5.4	12.9
4.0	7.7	18.6	5.7	13.9
4.5	8.1	19.7	5.9	14.6
5.0	8.5	20.7	6.0	15.2
5.5	8.8	21.6	6.2	15.9





AQL 11/24 - 1 LUX

Hoogte (m)				
2.5	5.2	12.4	3.8	9.2
3.0	5.6	13.5	4.1	10.1
3.5	6.0	14.6	4.3	10.7
4.0	6.3	15.4	4.4	11.3
4.5	6.6	16.3	4.5	11.7
5.0	6.8	17.0	4.5	12.1
5.5	6.9	17.6	4.5	12.4

AQL 11/24 - 1 LUX

Hoogte (m)				
6.0	6.9	18.2	4.4	12.6
6.5	6.6	18.8	4.3	12.8
7.0	6.1	19.2	4.0	12.9
7.5	5.7	19.4	3.7	12.9
8.0	5.1	19.6	3.3	12.7
8.5	4.4	19.4	2.6	12.6
9.0	3.4	18.8	1.6	12.3





AQL 11/24 - 5 LUX

Hoogte (m)				
2.5	3.1	7.9	2.0	5.6
3.0	2.9	8.5	1.9	5.7
3.5	2.4	8.7	1.5	5.7
4.0	1.6	8.5	0.8	5.5





Spacingtabel / Spacing tabel

AQL 11/HF





AQL 11/HF - 0.5 LUX

Hoogte (m)				
2.5	6.6	15.8	4.8	11.2
3.0	7.2	17.2	5.3	12.5
3.5	7.7	18.6	5.7	13.6
4.0	8.2	19.7	6.0	14.6
4.5	8.6	20.9	6.4	15.6
5.0	9.1	22.0	6.5	16.2
5.5	9.5	23.0	6.7	16.9





AQL 11/HF - 1 LUX

Hoogte (m)				
2.5	5.5	13.2	4.1	9.6
3.0	6.0	14.3	4.4	10.7
3.5	6.4	15.5	4.6	11.4
4.0	6.8	16.5	4.8	12.1
4.5	7.1	17.3	4.9	12.7
5.0	7.4	18.1	5.1	13.1
5.5	7.6	18.9	5.1	13.5

AQL 11/HF - 1 LUX

Hoogte (m)				
7.0	7.5	20.7	4.9	14.3
7.5	7.2	21.3	4.6	14.4
8.0	6.7	21.5	4.4	14.4
8.5	6.2	21.7	4.1	14.4
9.0	5.6	21.9	3.6	14.2
9.5	4.9	21.7	2.9	14.1
10.0	4.0	21.1	1.9	13.8





AQL 11/HF - 5 LUX

Hoogte (m)				
2.5	3.4	8.5	2.3	6.0
3.0	3.4	9.1	2.2	6.3
3.5	3.1	9.6	2.0	6.4
4.0	2.6	9.8	1.6	6.4
4.5	1.7	9.4	0.8	6.2





Spacingtabel / Spacing tabel

AQL 11/1





AQL 11/1 - 1 LUX

Hoogte (m)				
2.5	5.7	13.8	4.3	10.0
3.0	6.3	14.9	4.6	11.0
3.5	6.7	16.1	4.6	12.0
4.0	7.1	17.2	5.1	12.7
4.5	7.4	18.1	5.2	13.3
5.0	7.7	18.9	5.4	13.9
5.5	8.0	19.8	5.5	14.2





AQL 11/1 - 1 LUX

Hoogte (m)				
8.0	8.4	21.8	5.4	15.2
8.5	7.9	23.0	5.1	15.6
9.0	7.0	23.4	4.5	15.6
9.5	6.4	23.6	4.2	15.5
10.0	5.8	23.8	3.6	15.3
10.5	5.1	23.3	2.8	15.2
11.0	3.8	22.7	1.5	14.8

AQL 11/1 - 5 LUX

Hoogte (m)				
2.5	3.6	8.9	2.5	6.0
3.0	3.7	9.6	2.5	6.3
3.5	3.6	10.2	2.3	6.4
4.0	3.1	10.5	2.0	6.4
4.5	2.5	10.6	1.6	6.2
5.0	1.3	10.1	0.3	6.5





AQL 11/1 - 10 LUX

Hoogte (m)				
2.5	2.5	7.2	1.6	4.9
3.0	2.0	7.5	1.3	4.9
3.5	1.1	7.2	0.4	4.7





Spacingtabel / Spacing tabel

AQL 11/3

AQL 11/3 - 0.5 LUX

Hoogte (m)				
2.5	5.1	12.2	3.7	9.0
3.0	5.5	13.3	4.0	9.9
3.5	5.9	14.3	4.2	10.5
4.0	6.2	15.1	4.3	11.1
4.5	6.5	16.0	4.4	11.4
5.0	6.6	16.7	4.4	11.8
5.5	6.7	17.3	4.3	12.1





AQL 11/3 - 1 LUX

Hoogte (m)				
2.5	4.2	10.2	2.9	7.5
3.0	4.5	11.0	3.1	8.0
3.5	4.7	11.7	3.1	8.3
4.0	4.8	12.3	3.1	8.6
4.5	4.5	12.9	2.9	8.8
5.0	4.0	13.2	2.6	8.8
5.5	3.4	13.4	2.2	8.7





Spacingtabel / Spacing tabel

DECO 2D28





DECO 2D28 - 0.5 LUX

Hoogte (m)				
2.5	6.3	15.3	6.3	15.3
3.0	6.9	16.5	6.9	16.5
3.5	7.3	17.7	7.3	17.7
4.0	7.7	18.9	7.7	18.9
4.5	8.1	20.1	8.1	20.1
5.0	8.4	20.8	8.4	20.8
5.5	8.7	21.6	8.7	21.6





DECO 2D28 - 1 LUX

Hoogte (m)				
2.5	5.2	12.6	5.2	12.6
3.0	5.6	13.8	5.6	13.8
3.5	5.9	14.7	5.9	14.7
4.0	6.2	15.4	6.2	15.4
4.5	6.4	16.2	6.4	16.2
5.0	6.6	16.8	6.6	16.8
5.5	6.8	17.3	6.8	17.3

DECO 2D28 - 5 LUX

Hoogte (m)				
2.5	3.0	7.8	3.0	7.8
3.0	3.1	8.3	3.1	8.3
3.5	3.1	8.6	3.1	8.6
4.0	3.1	8.9	3.1	8.9
4.5	2.9	8.9	2.9	8.9
5.0	2.7	8.8	2.7	8.8
5.5	2.3	8.7	2.3	8.7





DECO 2D28 - 15 LUX

Hoogte (m)				
2.5	1.7	5.1	1.7	5.1
3.0	1.5	5.1	1.5	5.1
3.5	0.9	4.9	0.9	4.9





Spacingtabel / Spacing tabel

DECO 230





DECO 230 - 0.5 LUX

Hoogte (m)				
2.5	8.3	20.0	8.3	20.0
3.0	9.1	21.7	9.1	21.7
3.5	9.7	23.4	9.7	23.4
4.0	10.3	25.0	10.3	25.0
4.5	10.9	26.4	10.9	26.4
5.0	11.5	27.6	11.5	27.6
5.5	12.0	28.8	12.0	28.8





DECO 230 - 1 LUX

Hoogte (m)				
2.5	6.9	16.6	6.9	16.6
3.0	7.5	18.2	7.5	18.2
3.5	8.1	19.4	8.1	19.4
4.0	8.6	20.6	8.6	20.6
4.5	8.9	21.8	8.9	21.8
5.0	9.3	23.0	9.3	23.0
5.5	9.7	24.0	9.7	24.0

DECO 230 - 5 LUX

Hoogte (m)				
2.5	4.4	10.8	4.4	10.8
3.0	4.6	11.5	4.6	11.5
3.5	4.8	12.3	4.8	12.3
4.0	5.0	12.8	5.0	12.8
4.5	5.2	13.3	5.2	13.3
5.0	5.2	13.8	5.2	13.8
5.5	5.2	14.1	5.2	14.1





DECO 230 - 15 LUX

Hoogte (m)				
2.5	2.9	7.6	2.9	7.6
3.0	3.0	8.6	3.0	8.0
3.5	3.0	8.3	3.0	8.3
4.0	2.9	8.5	2.9	8.5
4.5	2.8	8.5	2.8	8.5
5.0	2.5	8.5	2.5	8.5
5.5	2.0	8.3	2.0	8.3





Spacingtabel / Spacing tabel

FMN-1/11




FMN-1/11 - 0.5 LUX

Hoogte (m)				
2.5	5.6	14.1	4.8	11.8
3.0	5.9	15.0	5.1	12.7
3.5	6.3	15.7	5.4	13.5
4.0	6.7	16.4	5.7	14.2
4.5	7.0	17.2	5.9	14.9
5.0	7.2	18.0	6.0	15.4
5.5	7.4	18.7	6.2	15.9





FMN-1/11 - 1 LUX

Hoogte (m)				
2.5	4.5	11.2	3.9	9.6
3.0	4.9	11.9	4.1	10.3
3.5	5.1	12.6	4.3	10.9
4.0	5.2	13.4	4.4	11.4
4.5	5.3	14.1	4.6	11.8
5.0	5.4	14.5	4.7	12.1
5.5	5.4	14.7	4.8	12.4

FMN-1/11 - 5 LUX

Hoogte (m)				
2.5	2.4	6.6	2.1	5.6
3.0	2.5	6.7	2.1	5.8
3.5	2.4	6.9	2.0	6.0
4.0	1.8	7.0	1.6	6.1
4.5	1.0	7.0	0.9	6.0





FMN-1/11 - 10 LUX

Hoogte (m)				
2.5	1.7	5.1	1.7	5.1
3.0	1.5	5.1	1.5	5.1
3.5	0.9	4.9	0.9	4.9





Spacingtabel / Spacing tabel

FM 11/24





FM 11/24 - 0.5 LUX

Hoogte (m)				
2.5	5.3	13.4	4.6	11.3
3.0	5.7	14.2	4.9	12.1
3.5	6.1	14.9	5.2	12.9
4.0	6.4	15.6	5.4	13.6
4.5	6.6	16.4	5.6	14.1
5.0	6.8	17.2	5.7	14.7
5.5	6.9	17.9	5.9	15.1





FM 11/24 - 1 LUX

Hoogte (m)				
2.5	4.3	10.6	3.7	9.1
3.0	4.6	11.3	3.9	9.8
3.5	4.8	12.1	4.0	10.3
4.0	4.9	12.8	4.2	10.8
4.5	4.9	13.3	4.3	11.1
5.0	5.0	13.6	4.4	11.4
5.5	5.1	13.8	4.5	11.7

FM 11/24 - 5 LUX

Hoogte (m)				
2.5	2.3	6.2	2.0	5.3
3.0	2.3	6.3	1.9	5.5
3.5	2.0	6.4	1.6	5.6
4.0	1.2	6.5	1.1	5.6





FM 11/24 - 10 LUX

Hoogte (m)				
2.5	1.4	4.6	1.1	4.0
3.0	0.6	4.6	0.5	3.9





Spacingtabel / Spacing tabel

FM 11/HF





FM 11/HF - 0.5 LUX

Hoogte (m)				
2.5	5.7	14.4	4.9	12.0
3.0	6.1	15.4	5.3	13.0
3.5	6.4	16.1	5.6	13.8
4.0	6.8	16.8	5.8	14.5
4.5	7.2	17.5	6.0	15.2
5.0	7.4	18.3	6.2	15.8
5.5	7.6	19.1	6.4	16.3





FM 11/HF - 1 LUX

Hoogte (m)				
2.5	4.6	11.4	3.9	9.8
3.0	4.9	12.1	4.2	10.5
3.5	5.2	12.9	4.4	11.1
4.0	5.4	13.7	4.5	11.6
4.5	5.5	14.4	4.7	12.1
5.0	5.5	14.8	4.8	12.4
5.5	5.6	15.2	4.9	12.7

FM 11/HF - 5 LUX

Hoogte (m)				
2.5	2.5	6.8	2.2	5.7
3.0	2.6	6.9	2.2	6.0
3.5	2.5	7.1	2.1	6.2
4.0	2.1	7.2	1.8	6.3
4.5	1.3	7.3	1.2	6.3





FM 11/HF - 10 LUX

Hoogte (m)				
2.5	1.8	5.0	1.5	4.4
3.0	1.2	5.1	1.1	4.5
3.5	0.4	5.0	-	4.2





Spacingtabel / Spacing tabel

DIB 325/140A/CL11




DIB 11 - 0.5 LUX

Hoogte (m)				
2.5	5.6	14.1	4.8	11.8
3.0	5.9	15.0	5.1	12.7
3.5	6.3	15.7	5.4	13.5
4.0	6.7	16.4	5.7	14.2
4.5	7.0	17.2	5.9	14.9
5.0	7.2	18.0	6.0	15.4
5.5	7.4	18.7	6.2	15.9





DIB 11 - 1 LUX

Hoogte (m)				
2.5	4.5	11.2	3.9	9.6
3.0	4.9	11.9	4.1	10.3
3.5	5.1	12.6	4.3	10.9
4.0	5.2	13.4	4.4	11.4
4.5	5.3	14.1	4.6	11.8
5.0	5.4	14.5	4.7	12.1
5.5	5.4	14.7	4.8	12.4

DIB 11 - 5 LUX

Hoogte (m)				
2.5	2.4	6.6	2.1	5.6
3.0	2.5	6.7	2.1	5.8
3.5	2.4	6.9	2.0	6.0
4.0	1.8	7.0	1.6	6.1
4.5	1.0	7.0	0.9	6.0





DIB 11 - 10 LUX

Hoogte (m)				
2.5	1.7	5.1	1.7	5.1
3.0	1.5	5.1	1.5	5.1
3.5	0.9	4.9	0.9	4.9





Spacingtabel / Spacing tabel

CIB-TL 325/140/24/CL11





CIB 11/24 - 0.5 LUX

Hoogte (m)				
2.5	5.3	13.4	4.6	11.3
3.0	5.7	14.2	4.9	12.1
3.5	6.1	14.9	5.2	12.9
4.0	6.4	15.6	5.4	13.6
4.5	6.6	16.4	5.6	14.1
5.0	6.8	17.2	5.7	14.7
5.5	6.9	17.9	5.9	15.1





CIB 11/24 - 1 LUX

Hoogte (m)				
2.5	4.3	10.6	3.7	9.1
3.0	4.6	11.3	3.9	9.8
3.5	4.8	12.1	4.0	10.3
4.0	4.9	12.8	4.2	10.8
4.5	4.9	13.3	4.3	11.1
5.0	5.0	13.6	4.4	11.4
5.5	5.1	13.8	4.5	11.7

CIB 11/24 - 5 LUX

Hoogte (m)				
2.5	2.3	6.2	2.0	5.3
3.0	2.3	6.3	1.9	5.5
3.5	2.0	6.4	1.6	5.6
4.0	1.2	6.5	1.1	5.6





CIB 11/24 - 10 LUX

Hoogte (m)				
2.5	1.4	4.6	1.1	4.0
3.0	0.6	4.6	0.5	3.9





Spacingtabel / Spacing tabel

CIB-TL 325/140/HF/CL11





CIB 11/HF - 0.5 LUX

Hoogte (m)				
2.5	5.7	14.4	4.9	12.0
3.0	6.1	15.4	5.3	13.0
3.5	6.4	16.1	5.6	13.8
4.0	6.8	16.8	5.8	14.5
4.5	7.2	17.5	6.0	15.2
5.0	7.4	18.3	6.2	15.8
5.5	7.6	19.1	6.4	16.3





CIB 11/HF - 1 LUX

Hoogte (m)				
2.5	4.6	11.4	3.9	9.8
3.0	4.9	12.1	4.2	10.5
3.5	5.2	12.9	4.4	11.1
4.0	5.4	13.7	4.5	11.6
4.5	5.5	14.4	4.7	12.1
5.0	5.5	14.8	4.8	12.4
5.5	5.6	15.2	4.9	12.7

CIB 11/HF - 5 LUX

Hoogte (m)				
2.5	2.5	6.8	2.2	5.7
3.0	2.6	6.9	2.2	6.0
3.5	2.5	7.1	2.1	6.2
4.0	2.1	7.2	1.8	6.3
4.5	1.3	7.3	1.2	6.3





CIB 11/HF - 10 LUX

Hoogte (m)				
2.5	1.8	5.0	1.5	4.4
3.0	1.2	5.1	1.1	4.5
3.5	0.4	5.0	-	4.2





Spacingtabel / Spacing tabel

DVA 360A/1

DVA 360A/1 - 0.5 LUX

Hoogte (m)				
2.5	3.9	10.9	3.1	7.8
3.0	3.8	11.2	3.4	8.4
3.5	3.9	11.2	3.5	8.9
4.0	4.0	10.7	3.7	9.3
4.5	4.1	10.8	3.7	9.8
5.0	3.9	11.0	3.6	10.0
5.5	3.7	11.1	3.5	10.3





DVA 360A/1 - 1 LUX

Hoogte (m)				
2.5	2.7	7.8	2.5	6.3
3.0	2.8	7.6	2.6	6.8
3.5	2.8	7.7	2.6	7.1
4.0	2.6	7.9	2.4	7.4
4.5	2.3	8.1	2.1	7.4
5.0	1.7	7.8	1.7	7.3
5.5	1.2	7.5	1.2	6.9





Spacingtabel / Spacing tabel

DVA 360B/1

DVA 360B/1 - 0.5 LUX

Hoogte (m)				
2.5	4.7	12.5	3.1	7.6
3.0	4.6	13.0	3.3	8.1
3.5	4.3	13.4	3.5	8.6
4.0	4.2	13.6	3.6	9.2
4.5	4.3	12.4	3.5	9.6
5.0	4.4	12.0	3.4	9.9
5.5	4.3	11.9	3.2	10.1





DVA 360B/1 - 1 LUX

Hoogte (m)				
2.5	3.0	9.5	2.5	6.1
3.0	3.0	9.2	2.5	6.7
3.5	3.1	8.5	2.4	6.9
4.0	3.0	8.4	2.2	7.2
4.5	2.6	8.6	1.7	7.1
5.0	1.6	8.7	1.2	6.8





Spacingtabel / Spacing tabel

VA-TL 360/24

VA-TL 360/24 - 0.5 LUX

Hoogte (m)				
2.5	4.3	11.5	3.3	8.1
3.0	4.0	11.9	3.5	8.7
3.5	4.1	12.3	3.7	9.3
4.0	4.2	11.6	3.9	9.7
4.5	4.3	11.5	4.0	10.2
5.0	4.3	11.7	3.9	10.6
5.5	4.2	11.8	3.9	10.9





VA-TL 360/24 - 1 LUX

Hoogte (m)				
2.5	2.9	8.7	2.6	6.6
3.0	3.0	8.1	2.8	6.1
3.5	3.1	8.2	2.8	7.5
4.0	2.9	8.4	2.7	7.7
4.5	2.7	8.6	2.5	8.0
5.0	2.3	8.6	2.1	7.9
5.5	1.7	8.4	1.7	1.7





Spacingtabel / Spacing tabel

VA-TL 360/HF

VA-TL 360/HF - 0.5 LUX

Hoogte (m)				
2.5	5.1	11.2	3.2	7.9
3.0	4.9	11.5	3.4	8.5
3.5	4.0	11.6	3.6	9.0
4.0	4.1	10.9	3.8	9.5
4.5	4.1	11.1	3.8	10.0
5.0	4.1	11.2	3.8	10.2
5.5	3.9	11.4	3.6	10.5





VA-TL 360/HF - 1 LUX

Hoogte (m)				
2.5	2.8	8.2	2.6	6.4
3.0	2.9	7.8	2.7	6.9
3.5	2.9	7.9	2.7	7.2
4.0	2.7	8.1	2.5	7.5
4.5	2.4	8.3	2.2	7.6
5.0	1.9	8.1	1.9	7.5
5.5	1.4	7.8	1.4	7.2





Spacingtabel / Spacing tabel

PRE-1

PRE-1 - 0.5 LUX

Hoogte (m)				
2.5	4.7	11.7	2.7	7.0
3.0	4.9	12.5	2.7	7.3
3.5	5.0	13.2	2.6	7.6
4.0	4.9	13.7	2.4	7.6
4.5	4.2	14.1	2.1	7.6
5.0	2.2	14.2	1.5	7.4





PRE-1 - 1 LUX

Hoogte (m)				
2.5	3.6	9.3	1.8	5.3
3.0	3.3	9.8	1.6	5.4
3.5	1.7	10.1	1.1	5.2





Spacingtabel / Spacing tabel

PRE-24

PRE-24 - 0.5 LUX

Hoogte (m)				
2.5	5.5	13.6	3.2	8.1
3.0	5.8	14.6	3.4	8.7
3.5	6.1	15.5	3.4	9.1
4.0	6.3	16.2	3.4	9.4
4.5	6.4	16.8	3.3	9.6
5.0	6.2	17.4	3.1	9.7
5.5	5.8	17.8	2.9	9.7





PRE-24 - 1 LUX

Hoogte (m)				
2.5	4.3	11.0	2.4	6.5
3.0	4.5	11.7	2.4	6.8
3.5	4.4	12.2	2.2	6.9
4.0	3.9	12.7	1.9	6.8
4.5	2.0	12.8	1.4	6.6





Spacingtabel / Spacing tabel

PRE-HF

PRE-HF - 0.5 LUX

Hoogte (m)				
2.5	5.8	14.4	3.5	8.6
3.0	6.2	15.5	3.6	9.2
3.5	6.6	16.5	3.8	9.8
4.0	6.8	17.3	3.8	10.2
4.5	7.0	18.0	3.8	10.4
5.0	7.1	18.6	3.6	10.6
5.5	6.9	19.1	3.5	10.7





PRE-HF - 1 LUX

Hoogte (m)				
2.5	4.7	11.7	2.7	6.9
3.0	4.9	12.5	2.7	7.3
3.5	5.0	13.1	2.6	7.5
4.0	4.8	13.6	2.4	7.6
4.5	3.1	14.0	2.0	7.5
5.0	2.1	14.1	1.4	7.3





Spacingtabel / Spacing tabel

PRE-V

PRE-V - 0.5 LUX

Hoogte (m)				
2.5	5.9	12.9	2.7	6.4
3.0	6.6	14.8	2.9	7.1
3.5	7.0	16.6	3.0	7.6
4.0	6.9	18.0	2.8	8.1
4.5	6.5	19.3	2.4	8.4
5.0	6.3	19.8	2.1	8.4
5.5	4.9	19.6	1.8	8.1





PRE-V - 1 LUX

Hoogte (m)				
2.5	4.9	11.8	2.1	5.4
3.0	4.7	13.2	1.8	5.8
3.5	4.5	14.0	1.5	6.0
4.0	3.3	13.7	1.2	5.5
4.5	2.9	13.1	1.0	4.7
5.0	2.5	12.7	0.7	4.1
5.5	2.0	9.9	0.5	3.5





Spacingtabel / Spacing tabel

PRE-1/R

PRE-1/R - 0.5 LUX

Hoogte (m)				
2.5	4.3	10.0	2.6	6.7
3.0	4.7	11.2	2.6	7.1
3.5	4.9	12.2	2.5	7.2
4.0	4.9	13.0	2.3	7.3
4.5	4.2	13.5	1.9	7.2
5.0	4.0	13.9	1.2	7.0





PRE-1/R - 1 LUX

Hoogte (m)				
2.5	3.5	8.7	1.7	5.1
3.0	3.3	9.4	1.5	5.1
3.5	2.8	9.8	0.9	5.0





Spacingtabel / Spacing tabel

PRE-24/R

PRE-24/R - 0.5 LUX

Hoogte (m)				
2.5	5.0	11.3	3.3	8.4
3.0	5.6	12.7	3.5	9.0
3.5	6.1	14.0	3.6	9.4
4.0	6.4	15.2	3.6	9.8
4.5	6.7	16.2	3.5	10.0
5.0	6.8	17.2	3.4	10.1
5.5	6.8	18.0	3.2	10.2





PRE-24/R - 1 LUX

Hoogte (m)				
2.5	4.3	10.0	2.5	6.7
3.0	4.7	11.1	2.5	7.0
3.5	4.8	12.1	2.4	7.2
4.0	4.8	12.9	2.2	7.2
4.5	4.1	13.4	1.8	7.1
5.0	3.9	13.7	1.1	6.8





Spacingtabel / Spacing tabel

PRE-HF/R

PRE-HF/R - 0.5 LUX

Hoogte (m)				
2.5	5.2	11.8	3.6	9.0
3.0	5.8	13.3	3.8	9.7
3.5	6.4	14.6	4.0	10.2
4.0	6.9	15.9	4.0	10.6
4.5	7.2	17.1	4.0	11.0
5.0	7.5	18.1	4.0	11.2
5.5	7.7	19.2	3.9	11.4





PRE-HF/R - 1 LUX

Hoogte (m)				
2.5	4.5	10.4	2.8	7.2
3.0	5.0	11.7	2.9	7.6
3.5	5.3	12.7	2.8	7.9
4.0	5.4	13.7	2.7	8.1
4.5	5.4	14.5	2.5	8.1
5.0	4.7	15.0	2.1	8.0
5.5	4.4	15.4	1.4	7.8





Spacingtabel / Spacing tabel

PRE R/LED

PRE /R/LED - 0.5 LUX

Hoogte (m)				
2.5	6.4	13.9	2.8	6.6
3.0	7.3	16.0	3.1	7.3
3.5	8.0	17.9	3.2	7.9
4.0	8.6	19.8	3.2	8.4
4.5	8.3	21.7	2.9	8.8
5.0	7.7	22.9	2.5	9.1
5.5	7.5	24.0	2.3	9.2





PRE /R/LED - 1 LUX

Hoogte (m)				
2.5	5.7	12.8	2.3	5.6
3.0	6.0	14.7	2.2	6.1
3.5	5.5	16.1	1.8	6.4
4.0	5.2	17.2	1.5	6.4
4.5	3.8	16.6	1.3	5.8
5.0	3.4	15.4	1.1	5.0
5.5	3.0	15.0	0.9	4.5





Spacingtabel / Spacing tabel

8860-EX-(A/B)

8860-EX-(A/B) - 0.5 LUX

Hoogte (m)				
2.5	4.6	11.8	3.6	9.7
3.0	4.9	12.5	3.9	9.4
3.5	5.0	13.1	4.0	10.1
4.0	5.1	13.6	4.2	10.7
4.5	5.1	13.9	4.2	11.1
5.0	5.1	14.2	4.2	11.5
5.5	5.0	14.4	4.2	11.8





8860-EX- A/B) - 1 LUX

Hoogte (m)				
2.5	3.5	9.3	2.9	7.2
3.0	3.6	9.7	3.0	7.7
3.5	3.6	10.0	3.0	8.1
4.0	3.5	10.2	2.9	8.3
4.5	3.3	10.3	2.8	8.5
5.0	3.0	10.2	2.5	8.5
5.5	2.5	10.0	2.0	8.3





Spacingtabel / Spacing tabel

8860-EX-24

8860-EX-24 - 0.5 LUX

Hoogte (m)				
2.5	4.9	12.3	3.7	9.0
3.0	5.2	13.2	4.1	9.8
3.5	5.3	13.8	4.2	10.5
4.0	5.4	14.3	4.4	11.2
4.5	5.5	14.7	4.5	11.7
5.0	5.5	15.0	4.6	12.1
5.5	5.4	15.3	4.5	12.4





8860-EX-24 - 1 LUX

Hoogte (m)				
2.5	3.8	9.8	3.0	7.5
3.0	3.9	10.3	3.2	8.1
3.5	3.9	10.6	3.2	8.5
4.0	3.8	10.9	3.2	8.9
4.5	3.7	11.0	3.1	9.0
5.0	3.4	11.0	2.9	9.2
5.5	3.1	10.9	2.6	9.1





Spacingtabel / Spacing tabel

8860-EX-HF

8860-EX-HF - 0.5 LUX

Hoogte (m)				
2.5	4.7	12.0	3.6	8.8
3.0	5.0	12.8	3.9	9.6
3.5	5.1	13.3	4.1	10.3
4.0	5.2	13.9	4.3	10.9
4.5	5.3	14.2	4.3	11.3
5.0	5.2	14.5	4.4	11.7
5.5	5.2	14.7	4.3	12.0





8860-EX-HF - 1 LUX

Hoogte (m)				
2.5	3.6	9.5	2.9	7.3
3.0	3.7	9.9	3.0	7.9
3.5	3.7	10.2	3.1	8.2
4.0	3.6	10.4	3.0	8.5
4.5	3.4	10.5	3.9	8.7
5.0	3.2	10.5	2.6	8.8
5.5	2.7	10.3	2.2	8.8





Spacingtabel / Spacing tabel

DVA-TL 360A

DVA 360A/3 - 0.5 LUX

Hoogte (m)				
2.5	3.1	9.1	2.8	6.9
3.0	3.2	8.8	2.9	7.3
3.5	3.3	8.7	3.0	7.8
4.0	3.2	8.8	2.9	8.1
4.5	3.0	9.0	2.8	8.4
5.0	2.7	9.2	2.5	8.5
5.5	2.2	9.1	2.1	8.4





DVA 360A/3 - 1 LUX

Hoogte (m)				
2.5	2.3	6.2	2.1	5.5
3.0	2.2	6.3	2.0	5.8
3.5	1.9	6.5	1.8	6.0
4.0	1.4	6.4	1.4	5.9
4.5	0.8	6.0	0.8	5.5





Spacingtabel / Spacing tabel

DVA-TL 360B

DVA 360B/3 - 0.5 LUX

Hoogte (m)				
2.5	3.6	10.6	2.7	6.6
3.0	3.4	10.9	2.9	7.2
3.5	3.5	10.4	2.9	7.7
4.0	3.5	9.8	2.8	7.9
4.5	3.5	9.6	2.5	8.2
5.0	3.2	9.8	2.1	8.2
5.5	2.4	10.0	1.6	8.0





DVA 360B/3 - 1 LUX

Hoogte (m)				
2.5	2.5	7.3	2.0	5.4
3.0	2.5	6.8	1.9	5.7
3.5	2.3	6.9	1.5	5.8
4.0	1.4	7.1	1.0	5.5





Spacingtabel / Spacing tabel

NRO 11/HF(/W)





NRO 11/HF - 0.5 LUX

Hoogte (m)				
2.5	6.8	16.3	4.9	11.8
3.0	7.2	17.7	5.3	13.0
3.5	7.7	19.1	5.6	13.8
4.0	8.0	20.0	6.9	14.6
4.5	8.3	20.9	6.1	15.4
5.0	8.5	21.8	6.3	16.0
5.5	8.7	22.4	6.4	16.6

NRO 11/HF - 1 LUX

Hoogte (m)				
2.5	5.4	13.5	4.0	9.8
3.0	5.7	14.4	4.3	10.6
3.5	6.0	15.3	4.4	11.3
4.0	6.2	16.0	4.6	11.9
4.5	6.4	16.5	4.7	12.3
5.0	6.5	17.1	4.7	12.6
5.5	6.7	17.5	4.6	12.9





NRO 11/HF - 5 LUX

Hoogte (m)				
2.5	3.0	7.9	2.1	5.8
3.0	3.0	8.2	1.9	5.9
3.5	2.8	8.4	1.7	5.9
4.0	2.4	8.5	1.1	5.7





Spacingtabel / Spacing tabel

NRO 11/24(/W)





NRO 11/24 - 0.5 LUX

Hoogte (m)				
2.5	6.3	15.3	4.6	11.2
3.0	6.7	16.7	5.0	12.2
3.5	7.1	17.7	5.3	13.0
4.0	7.4	18.6	5.5	13.8
4.5	7.7	19.5	5.6	14.3
5.0	7.9	20.1	5.8	14.9
5.5	8.1	20.7	5.9	15.4

NRO 11/24 - 1 LUX

Hoogte (m)				
2.5	5.0	12.6	3.7	9.2
3.0	5.3	13.5	3.9	9.9
3.5	5.5	14.2	4.1	10.5
4.0	5.7	14.8	4.2	11.0
4.5	5.9	15.3	4.2	11.3
5.0	6.0	15.7	4.1	11.5
5.5	6.0	16.1	4.0	11.7





NRO 11/24 - 5 LUX

Hoogte (m)				
2.5	2.7	7.2	1.8	5.3
3.0	2.6	7.5	1.6	5.3
3.5	2.2	7.6	1.1	5.1





Spacingtabel / Spacing tabel

NRO 11(A/B)/1(/W)





NRO 11/1- 0.5 LUX

Hoogte (m)				
2.5	7.1	17.0	5.2	12.3
3.0	7.6	18.5	5.6	13.5
3.5	8.0	19.9	5.9	14.5
4.0	8.5	21.1	6.2	15.3
4.5	8.7	21.9	6.5	16.1
5.0	9.0	22.8	6.7	16.8
5.5	9.3	23.7	6.9	17.4





NRO 11/1- 1 LUX

Hoogte (m)				
2.5	5.7	14.1	4.2	10.3
3.0	6.1	15.2	4.5	11.1
3.5	6.4	16.1	4.7	11.9
4.0	6.6	16.9	4.9	12.5
4.5	6.8	17.5	5.0	13.0
5.0	7.0	18.1	5.1	13.4
5.5	7.1	18.6	5.1	13.7

NRO 11/1- 1 LUX

Hoogte (m)				
6.0	7.2	19.0	5.0	14.0
6.5	7.2	19.4	4.9	14.1
7.0	7.3	19.7	4.8	14.3
7.5	7.2	20.0	4.6	14.3
8.0	7.0	20.2	4.3	14.3
8.5	6.8	20.4	4.0	14.2
9.0	6.5	20.5	4.5	14.0





NRO 11/1 - 5 LUX

Hoogte (m)				
2.5	3.2	8.3	2.3	6.2
3.0	3.2	8.7	2.2	6.4
3.5	2.2	9.0	2.0	6.4
4.0	2.9	9.2	1.6	6.3
4.5	2.3	9.2	0.8	6.0





Spacingtabel / Spacing tabel

NRO 11(A/B)/3(/W)

NRO 11/3 - 0.5 LUX

Hoogte (m)				
2.5	4.9	12.3	3.7	9.0
3.0	5.2	13.2	3.8	9.7
3.5	5.4	13.9	4.0	10.3
4.0	5.6	14.4	4.0	10.7
4.5	5.7	14.9	4.0	11.0
5.0	5.8	15.3	4.0	11.2
5.5	5.8	15.7	3.9	11.4





NRO 11/3 - 1 LUX

Hoogte (m)				
2.5	3.8	9.8	2.8	7.3
3.0	4.0	10.4	2.9	7.7
3.5	4.1	10.8	2.8	7.9
4.0	4.1	11.2	2.7	8.1
4.5	4.0	11.4	2.4	8.1
5.0	3.7	11.5	2.1	7.9
5.5	3.2	11.6	1.4	7.7





Spacingtabel / Spacing tabel

NB-1/WD

NB-1/WD - 0.5 LUX

Hoogte (m)				
2.5	4.3	13.0	3.6	8.9
3.0	4.4	13.1	3.8	9.6
3.5	4.5	12.1	3.9	10.2
4.0	4.5	12.4	3.9	10.6
4.5	4.5	12.6	3.9	10.9
5.0	4.5	12.8	3.9	11.1
5.5	4.4	12.8	3.9	11.1





NB-1/WD - 1 LUX

Hoogte (m)				
2.5	3.2	8.6	2.8	7.2
3.0	3.2	8.8	2.8	7.6
3.5	3.2	9.0	2.8	7.9
4.0	3.1	9.1	2.7	7.9
4.5	2.9	9.1	2.6	7.8
5.0	2.6	9.0	2.3	7.8
5.5	2.1	8.8	1.9	7.8





Spacingtabel / Spacing tabel

NBN-1/WD

NBN-1/WD - 0.5 LUX

Hoogte (m)				
2.5	4.1	10.0	3.6	9.0
3.0	4.4	10.8	3.8	9.6
3.5	4.5	11.5	4.0	10.2
4.0	4.5	12.1	4.0	10.7
4.5	4.5	12.6	4.0	11.0
5.0	4.5	12.8	4.0	11.3
5.5	4.4	12.8	4.0	11.4





NBN-1/WD - 1 LUX

Hoogte (m)				
2.5	3.2	8.2	2.8	7.2
3.0	3.2	8.7	2.8	7.7
3.5	3.2	9.1	2.8	8.0
4.0	3.1	9.1	2.8	8.0
4.5	2.9	9.1	2.7	8.0
5.0	2.7	9.0	2.4	8.0
5.5	2.2	8.8	2.0	7.9





Spacingtabel / Spacing tabel

IND 08/24

IND 08/24 - 0.5 LUX

Hoogte (m)				
2.5	4.6	12.0	3.3	8.2
3.0	4.8	12.6	3.5	8.9
3.5	4.8	13.0	3.7	9.4
4.0	4.8	13.4	3.7	9.8
4.5	4.7	13.5	3.7	10.1
5.0	4.5	13.6	3.7	10.4
5.5	4.3	13.6	3.5	10.5





IND 08/24 - 1 LUX

Hoogte (m)				
2.5	3.4	9.2	2.6	6.7
3.0	3.4	9.5	2.6	7.1
3.5	3.2	9.6	2.6	7.3
4.0	3.0	9.6	2.4	7.4
4.5	2.6	9.4	2.2	7.5
5.0	2.1	9.1	1.7	7.3
5.5	1.1	8.7	1.0	7.0





Spacingtabel / Spacing tabel

IND 08/HF

IND 08/HF - 0.5 LUX

Hoogte (m)				
2.5	4.5	11.7	3.2	8.0
3.0	4.6	12.2	3.4	8.7
3.5	4.6	12.6	3.5	9.1
4.0	4.6	12.9	3.6	9.6
4.5	4.4	13.0	3.5	9.8
5.0	4.3	13.0	3.5	10.0
5.5	4.0	13.0	3.3	10.1





IND 08/HF - 1 LUX

Hoogte (m)				
2.5	3.3	8.9	2.5	6.5
3.0	3.2	9.2	2.5	6.8
3.5	3.0	9.2	2.5	7.1
4.0	2.8	9.1	2.3	7.1
4.5	2.3	8.9	1.9	7.1
5.0	1.7	8.6	1.4	6.9





Spacingtabel / Spacing tabel

IND 08(A/B)1

IND 08/1- 0.5 LUX

Hoogte (m)				
2.5	4.1	10.9	3.1	7.6
3.0	4.2	11.4	3.2	8.2
3.5	4.2	11.7	3.3	8.6
4.0	4.1	11.9	3.3	8.9
4.5	3.9	11.9	3.2	9.1
5.0	3.7	11.9	3.0	9.2
5.5	3.3	11.7	2.7	9.3





IND 08/1 - 1 LUX

Hoogte (m)				
2.5	3.0	8.3	2.8	6.1
3.0	2.8	8.4	2.3	6.4
3.5	2.6	8.4	2.1	6.5
4.0	2.3	8.2	1.9	6.5
4.5	1.7	7.9	1.4	6.4





Spacingtabel / Spacing tabel

IND 18/24





IND 18/24 - 0.5 LUX

Hoogte (m)				
2.5	5.3	13.8	4.7	9.0
3.0	5.6	14.4	4.0	9.8
3.5	5.7	15.0	4.2	10.5
4.0	5.8	15.5	4.3	11.0
4.5	5.8	15.9	4.4	11.5
5.0	5.8	16.1	4.4	11.9
5.5	5.7	16.3	4.4	12.1

IND 18/24 - 1 LUX

Hoogte (m)				
2.5	4.0	10.7	3.0	7.4
3.0	4.1	11.1	3.1	8.0
3.5	4.1	11.4	3.1	8.4
4.0	4.0	11.6	3.1	8.6
4.5	3.8	11.6	3.0	8.8
5.0	3.6	11.6	2.8	8.8
5.5	3.1	11.5	2.5	8.7





IND 18/24 - 5 LUX

Hoogte (m)				
2.5	1.4	5.1	1.1	3.9
3.0	0.1	4.7	0.1	3.6





Spacingtabel / Spacing tabel

IND 18/HF





IND 18/HF - 0.5 LUX

Hoogte (m)				
2.5	10.5	26.0	6.3	14.7
3.0	11.5	27.8	7.0	16.5
3.5	12.1	29.7	7.6	17.8
4.0	12.7	31.5	8.2	19.1
4.5	13.2	33.2	8.6	20.4
5.0	13.8	34.4	9.0	21.8
5.5	14.1	35.5	9.5	22.8





IND 18/HF - 1 LUX

Hoogte (m)				
2.5	8.6	21.1	5.4	12.7
3.0	9.2	22.9	5.9	14.0
3.5	9.7	24.2	6.4	15.3
4.0	10.1	25.4	6.8	16.3
4.5	10.4	26.5	7.1	17.2
5.0	10.7	27.6	7.4	18.1
5.5	10.9	28.3	7.7	18.9

IND 18/HF - 5 LUX

Hoogte (m)				
2.5	4.9	12.7	3.5	8.5
3.0	5.1	13.3	3.7	9.2
3.5	5.2	13.8	3.8	9.8
4.0	5.2	14.2	3.9	10.2
4.5	5.2	14.5	3.9	10.6
5.0	5.1	14.6	3.9	10.9
5.5	5.9	14.7	3.8	11.1





IND 18/HF - 15 LUX

Hoogte (m)				
2.5	3.0	8.3	2.3	6.1
3.0	2.9	8.5	2.2	6.3
3.5	2.7	8.5	2.1	6.4
4.0	2.3	8.4	1.8	6.4
4.5	1.7	8.1	1.3	6.2





Spacingtabel / Spacing tabel

IND 18/(A/B)/1

IND 18/1 - 0.5 LUX

Hoogte (m)				
2.5	5.4	14.0	3.8	9.1
3.0	5.6	14.7	4.0	9.9
3.5	5.8	15.3	4.2	10.6
4.0	5.9	15.7	4.4	11.2
4.5	5.9	16.2	4.5	11.6
5.0	5.9	16.4	4.5	12.0
5.5	5.9	16.6	4.5	12.3





IND 18/1 - 1 LUX

Hoogte (m)				
2.5	4.1	10.8	3.0	7.5
3.0	4.2	11.3	3.1	8.1
3.5	4.2	11.5	3.2	8.5
4.0	4.1	11.8	3.1	8.7
4.5	4.0	11.8	3.0	9.0
5.0	3.7	11.9	2.9	9.0
5.5	3.3	11.7	2.6	8.9





Spacingtabel / Spacing tabel

IND 36/HF





IND 36/HF - 0.5 LUX

Hoogte (m)				
2.5	13.5	31.5	7.7	18.1
3.0	14.4	35.6	8.6	19.9
3.5	15.3	38.1	9.4	21.7
4.0	16.2	39.9	10.1	23.5
4.5	17.1	41.7	10.7	25.3
5.0	17.8	43.6	11.4	26.8
5.5	18.4	45.4	12.0	28.1





IND 36/HF - 1 LUX

Hoogte (m)				
2.5	10.9	27.0	6.7	15.4
3.0	11.8	28.9	7.4	17.2
3.5	12.6	30.7	8.0	18.9
4.0	13.1	32.5	8.7	20.2
4.5	13.7	34.3	9.1	21.5
5.0	14.2	35.7	9.6	22.8
5.5	14.7	36.8	10.0	24.1

IND 36/HF - 5 LUX

Hoogte (m)				
2.5	6.6	16.5	4.5	10.9
3.0	6.9	17.6	4.9	11.8
3.5	7.2	18.6	5.2	12.7
4.0	7.4	19.2	5.5	13.5
4.5	7.5	19.8	5.7	14.2
5.0	7.7	20.3	5.8	14.8
5.5	7.8	20.7	5.9	15.4





IND 36/HF - 15 LUX

Hoogte (m)				
2.5	4.3	11.3	3.2	8.1
3.0	4.4	11.8	3.4	8.7
3.5	4.5	12.2	3.5	9.2
4.0	4.5	12.5	3.5	9.5
4.5	4.4	12.7	3.4	9.7
5.0	4.2	12.7	3.3	9.9
5.5	3.9	12.7	3.1	9.9





Spacingtabel / Spacing tabel

IND 36/(A/B)1





IND 36/1 - 0.5 LUX

Hoogte (m)				
2.5	6.7	16.8	4.6	11.0
3.0	7.0	17.9	5.0	12.0
3.5	7.3	18.9	5.3	12.9
4.0	7.5	19.6	5.6	13.7
4.5	7.7	20.2	5.8	14.4
5.0	7.8	20.7	6.0	15.1
5.5	7.9	21.1	6.1	15.7

IND 36/1 - 1 LUX

Hoogte (m)				
2.5	5.2	13.4	3.8	9.2
3.0	5.4	14.0	4.0	9.9
3.5	5.5	14.6	4.2	10.6
4.0	5.6	15.0	4.3	11.2
4.5	5.6	15.4	4.4	11.6
5.0	5.6	15.6	4.4	11.9
5.5	5.5	15.9	4.3	12.1





IND 36/1 - 5 LUX

Hoogte (m)				
2.5	2.5	7.1	1.9	5.4
3.0	2.2	7.1	1.8	5.5
3.5	1.8	7.0	1.4	5.5
4.0	0.8	6.6	0.7	5.2





Spacingtabel / Spacing tabel

TNAT 1x8W

TNAT 1x8W - 0.5 LUX

Hoogte (m)				
2.5	4.3	13.0	3.6	8.9
3.0	4.4	13.1	3.8	9.6
3.5	4.5	12.1	3.9	10.2
4.0	4.5	12.4	3.9	10.6
4.5	4.5	12.6	3.9	10.9
5.0	4.5	12.8	3.9	11.1
5.5	4.4	12.8	3.9	11.1





TNAT 1x8W - 1 LUX

Hoogte (m)				
2.5	3.2	8.6	2.8	7.2
3.0	3.2	8.8	2.8	7.6
3.5	3.2	9.0	2.8	7.9
4.0	3.1	9.1	2.7	7.9
4.5	2.9	9.1	2.6	7.8
5.0	2.6	9.0	2.3	7.8
5.5	2.1	8.8	1.9	7.8





Spacingtabel / Spacing tabel

TNAT 2x8W

TNAT 2x8W - 0.5 LUX

Hoogte (m)				
2.5	4.1	10.0	3.6	9.0
3.0	4.4	10.8	3.8	9.6
3.5	4.5	11.5	4.0	10.2
4.0	4.5	12.1	4.0	10.7
4.5	4.5	12.6	4.0	11.0
5.0	4.5	12.8	4.0	11.3
5.5	4.4	12.8	4.0	11.4





TNAT 2x8W - 1 LUX

Hoogte (m)				
2.5	3.2	8.2	2.8	7.2
3.0	3.2	8.7	2.8	7.7
3.5	3.2	9.1	2.8	8.0
4.0	3.1	9.1	2.8	8.0
4.5	2.9	9.1	2.7	8.0
5.0	2.7	9.0	2.4	8.0
5.5	2.2	8.8	2.0	7.9





Spacingtabel / Spacing tabel

TNT/24

TNT/24 - 0.5 LUX

Hoogte (m)				
2.5	4.8	13.8	3.8	9.2
3.0	4.7	14.1	4.0	10.0
3.5	4.8	13.6	4.2	10.6
4.0	4.9	13.2	4.2	11.2
4.5	4.9	13.4	4.2	11.5
5.0	4.9	13.7	4.2	11.8
5.5	4.8	13.7	4.2	12.0





TNT/24 - 1 LUX

Hoogte (m)				
2.5	3.4	9.5	2.9	7.5
3.0	3.5	9.4	3.0	8.1
3.5	3.4	9.6	3.0	8.3
4.0	3.4	9.7	3.0	8.5
4.5	3.3	9.8	2.9	8.4
5.0	3.1	9.7	2.7	8.4
5.5	2.7	9.6	2.4	8.4





Spacingtabel / Spacing tabel

TNT/HF

TNT/HF - 0.5 LUX

Hoogte (m)				
2.5	4.5	13.3	3.7	9.0
3.0	4.5	13.6	3.9	9.7
3.5	4.6	12.7	4.0	10.3
4.0	4.7	12.7	4.0	10.9
4.5	4.7	12.9	4.0	11.1
5.0	4.6	13.1	4.0	11.4
5.5	4.6	13.2	4.0	11.4





TNT/HF - 1 LUX

Hoogte (m)				
2.5	3.3	8.9	2.8	7.3
3.0	3.3	9.1	2.9	7.8
3.5	3.3	9.3	2.8	8.0
4.0	3.2	9.3	2.8	8.1
4.5	3.1	9.3	2.7	8.1
5.0	2.8	9.3	2.5	8.1
5.5	2.4	9.1	2.1	8.1





Spacingtabel / Spacing tabel

XION





XN-EX-1/ZT - 0.5 LUX

Hoogte (m)				
3.0	5.3	13.0	5.2	12.2
4.0	5.9	14.7	5.8	14.2
5.0	6.3	16.1	6.3	15.6
6.0	6.6	17.2	6.5	16.8
7.0	6.7	17.9	6.7	17.7
8.0	6.6	18.5	6.6	18.3
9.0	6.4	18.8	6.4	18.7





XN-EX-1/ZT - 1 LUX

Hoogte (m)				
3.0	4.3	10.7	4.2	10.3
4.0	4.6	11.6	4.6	11.6
5.0	4.7	12.7	4.7	12.5
6.0	4.6	13.6	4.6	13.1
7.0	4.2	13.3	4.3	13.3
8.0	3.5	13.6	3.6	13.2
9.0	2.2	12.2	2.2	12.8

XN-EX-1/ZT - 5 LUX

Hoogte (m)				
1.5	2.0	5.0	1.9	4.8
2.0	2.1	5.5	2.1	5.4
2.5	2.1	5.8	2.1	5.8
3.0	1.9	6.0	2.0	6.0
3.5	1.6	5.9	1.7	5.9
4.0	1.0	5.7	1.1	5.7





XN-EX-1/ZT - 10 LUX

Hoogte (m)				
1.5	1.5	4.0	1.5	3.9
2.0	1.4	4.2	1.4	4.2
2.5	1.1	4.2	1.2	4.2
3.0	0.1	3.9	0.1	3.9





Spacingtabel / Spacing tabel

EVA-.-.LI





EVA-.LI - 1 LUX

Hoogte (m)				
2.0	8.0	21.1	2.2	5.6
2.5	7.7	22.9	2.2	6.1
3.0	7.8	23.2	1.5	6.4
3.5	4.8	21.9	1.2	6.0
4.0	4.4	21.5	1.2	5.0
4.5	3.6	18.8	1.1	4.1
5.0	2.8	13.7	1.0	3.6

EVA-.LI-X - 1 LUX

Hoogte (m)				
5.0	8.3	19.9	1.9	4.9
5.5	8.4	21.1	1.9	5.1
6.0	8.5	22.0	1.9	5.3
6.5	8.6	22.8	1.9	5.4
7.0	8.6	23.5	1.9	5.5
7.5	8.6	24.1	1.9	5.6
8.0	8.5	24.5	1.7	5.6





EVA-.LI-X² - 1 LUX

Hoogte (m)				
9.0	8.1	18.8	2.4	6.7
9.5	8.5	19.5	2.4	6.8
10.0	8.7	20.2	2.5	6.9
10.5	8.8	20.8	2.4	6.9
11.0	8.9	21.5	2.1	7.0
11.5	9.0	22.1	1.8	7.0
12.0	9.0	22.7	1.5	7.1





Spacingtabel / Spacing tabel

EVA-.-.WI





EVA-.-WI - 1 LUX

Hoogte (m)				
2.0	3.2	8.0	3.2	8.0
2.5	3.8	9.5	3.8	9.5
3.0	4.2	11.0	4.2	11.0
3.5	4.6	12.4	4.6	12.4
4.0	5.0	13.7	5.0	13.7
4.5	2.0	13.0	2.0	13.0
5.0	2.0	13.0	2.0	13.0

EVA-.-WI-X - 1 LUX

Hoogte (m)				
5.0	4.8	11.3	4.8	11.3
5.5	4.7	12.1	4.7	12.1
6.0	3.7	12.3	3.7	12.3
6.5	3.2	12.1	3.2	12.1
7.0	2.7	12.2	2.7	12.2
7.5	2.5	12.1	2.5	12.1
8.0	1.9	12.1	1.9	12.1





EVA-.-WI-X² - 1 LUX

Hoogte (m)				
9.0	3.5	10.5	3.5	10.5
9.5	3.5	10.8	3.5	10.8
10.0	3.6	11.1	3.6	11.1
10.5	3.6	11.5	3.6	11.5
11.0	3.6	11.8	3.6	11.8
11.5	3.5	12.1	3.5	12.1
12.0	4.6	11.4	4.6	11.4





Spacingtabel / Spacing tabel

EVA-.LO





EVA-.LO - 1 LUX

Hoogte (m)				
2.0	8.0	21.2	2.2	5.6
2.5	7.7	22.9	2.2	6.1
3.0	7.8	23.2	1.5	6.4
3.5	4.8	21.9	1.2	6.0
4.0	4.4	21.5	1.2	5.0
4.5	3.6	18.8	1.1	4.1
5.0	2.8	13.7	1.0	3.6

EVA-.LO-X - 1 LUX

Hoogte (m)				
5.0	8.3	19.9	1.9	4.9
5.5	8.4	21.1	1.9	5.1
6.0	8.5	22.0	1.9	5.3
6.5	8.6	22.8	1.9	5.4
7.0	8.6	23.5	1.9	5.5
7.5	8.6	24.1	1.9	5.6
8.0	8.5	24.5	1.7	5.6





EVA-.LO-X² - 1 LUX

Hoogte (m)				
9.0	8.1	18.8	2.4	6.7
9.5	8.5	19.5	2.4	6.8
10.0	8.7	20.2	2.5	6.9
10.5	8.8	20.8	2.4	6.9
11.0	8.9	21.5	2.1	7.0
11.5	9.0	22.1	1.8	7.0
12.0	9.0	22.7	1.5	7.1





Spacingtabel / Spacing tabel

EVA-.WO





EVA-.WO - 1 LUX

Hoogte (m)				
2.0	3.2	8.0	3.2	8.0
2.5	3.8	9.5	3.8	9.5
3.0	4.2	11.0	4.2	11.0
3.5	4.6	12.4	4.6	12.4
4.0	5.0	13.7	5.0	13.7
4.5	2.0	13.0	2.0	13.0
5.0	2.0	13.0	2.0	13.0

EVA-.WO-X - 1 LUX

Hoogte (m)				
5.0	4.8	11.3	4.8	11.3
5.5	4.7	12.1	4.7	12.1
6.0	3.7	12.3	3.7	12.3
6.5	3.2	12.1	3.2	12.1
7.0	2.7	12.2	2.7	12.2
7.5	2.5	12.1	2.5	12.1
8.0	1.9	12.1	1.9	12.1

EVA-.WO-X² - 1 LUX

Hoogte (m)				
9.0	3.5	10.5	3.5	10.5
9.5	3.5	10.8	3.5	10.8
10.0	3.6	11.1	3.6	11.1
10.5	3.6	11.5	3.6	11.5
11.0	3.6	11.8	3.6	11.8
11.5	3.5	12.1	3.5	12.1
12.0	4.6	11.4	4.6	11.4

Spacingtabel / Spacing tabel

EVA-.SO



EVA-.SO - 1 LUX - 2m breed

Hoogte (m)		
1.5	2.8	6.7
2.0	3.1	7.5
2.5	3.2	8.4
3.0	1.9	8.6
3.5	1.5	8.0
4.0	1.2	4.4
4.5	1.0	3.6
5.0	0.5	3.3

EVA-.SO - 1 LUX - 3m breed

Hoogte (m)		
1.5	3.1	7.1
2.0	3.4	7.5
2.5	3.6	8.4
3.0	3.6	8.9
3.5	3.6	9.2
4.0	3.0	9.2
4.5	1.6	8.5
5.0	1.4	5.8





EVA-.SO - 1 LUX - 4m breed

Hoogte (m)		
1.5	3.5	7.7
2.0	3.7	8.5
2.5	4.0	9.0
3.0	4.1	9.5
3.5	4.1	9.8
4.0	4.1	10.0
4.5	3.7	10.2
5.0	1.3	9.9





Spacingtabel / Spacing tabel

KOMPAS





EKN - 1 LUX

Hoogte (m)				
2.5	3.3	8.7	2.5	6.6
3.0	3.3	9.0	2.6	7.0
3.5	3.2	9.2	2.5	7.2
4.0	2.9	9.4	2.4	7.3
4.5	2.5	9.2	2.1	7.3
5.0	2.4	9.0	1.7	7.1
5.5	1.2	8.5	1.0	6.9

EK-HF - 1 LUX

Hoogte (m)				
2.5	3.5	9.3	2.7	7.0
3.0	3.6	9.7	2.8	7.4
3.5	3.6	10.0	2.8	7.7
4.0	3.4	10.2	2.7	7.9
4.5	3.1	10.2	2.6	8.0
5.0	2.7	10.1	1.3	7.9
5.5	2.2	9.8	1.9	7.8





EK-24 - 1 LUX

Hoogte (m)				
2.5	3.7	9.6	2.8	7.2
3.0	3.8	10.1	2.9	7.7
3.5	3.7	10.4	3.0	8.0
4.0	3.6	10.6	2.9	8.2
4.5	3.4	10.7	2.8	8.3
5.0	3.0	10.6	2.5	8.4
5.5	2.6	10.4	2.2	8.2





Spacingtabel / Spacing tabel

NP





NP 8(N/H) - 1 LUX

Hoogte (m)				
2.5	3.1	7.6	2.9	7.2
3.0	3.2	8.3	3.0	7.7
3.5	3.1	8.7	2.9	8.1
4.0	3.0	8.9	2.8	8.3
4.5	2.7	9.0	2.5	8.3
5.0	2.4	8.9	2.2	8.2
5.5	2.2	8.6	2.0	7.9

NP 230 - 1 LUX

Hoogte (m)				
2.5	3.1	7.7	2.9	7.3
3.0	3.2	8.5	3.0	7.8
3.5	3.2	8.8	3.0	8.3
4.0	3.1	9.1	2.9	8.5
4.5	2.9	9.2	2.6	8.6
5.0	2.5	9.1	2.4	8.5
5.5	2.3	9.0	2.2	8.3





NP 24 - 1 LUX

Hoogte (m)				
2.5	3.2	7.9	3.0	7.4
3.0	3.4	8.7	3.1	8.0
3.5	3.4	9.1	3.2	8.5
4.0	3.3	9.5	3.1	8.8
4.5	3.2	9.6	2.9	9.0
5.0	2.8	9.6	2.6	8.9
5.5	2.5	9.5	2.4	8.8





Spacingtabel / Spacing tabel

NPW





NPW-8N - 1 LUX

Hoogte (m)				
2.5	3.2	8.2	2.8	7.2
3.0	3.2	8.7	2.8	7.7
3.5	3.2	9.1	2.8	8.0
4.0	3.1	9.1	2.8	8.0
4.5	2.9	9.1	2.7	8.0
5.0	2.7	9.0	2.4	8.0
5.5	2.2	8.8	2.0	7.9





NPW-8H - 1 LUX

Hoogte (m)				
2.5	3.2	8.6	2.8	7.2
3.0	3.2	8.8	2.8	7.6
3.5	3.2	9.0	2.8	7.9
4.0	3.1	9.1	2.7	7.9
4.5	2.9	9.1	2.6	7.8
5.0	2.6	9.0	2.3	7.8
5.5	2.1	8.8	1.9	7.8

NPW-HF - 1 LUX

Hoogte (m)				
2.5	3.3	8.9	2.8	7.3
3.0	3.3	9.1	2.9	7.8
3.5	3.3	9.3	2.8	8.0
4.0	3.2	9.3	2.8	8.1
4.5	3.1	9.3	2.7	8.1
5.0	2.8	9.3	2.5	8.1
5.5	2.4	9.1	2.1	8.1





NPW-24 - 1 LUX

Hoogte (m)				
2.5	3.4	9.5	2.9	7.5
3.0	3.5	9.4	3.0	8.1
3.5	3.4	9.6	3.0	8.3
4.0	3.4	9.7	3.0	8.5
4.5	3.3	9.8	2.9	8.4
5.0	3.1	9.7	2.7	8.4
5.5	2.7	9.6	2.4	8.4





Spacingtabel / Spacing tabel

KLI





KLI - 1 LUX

Hoogte (m)				
2.5	2.9	7.7	2.8	7.0
3.0	3.1	8.0	3.0	7.5
3.5	3.1	8.3	3.0	7.9
4.0	3.1	8.6	3.0	8.2
4.5	3.0	8.8	2.8	8.4
5.0	2.7	8.9	2.6	8.5
5.5	2.2	8.8	2.2	8.4

KLI 230 - 1 LUX

Hoogte (m)				
2.5	3.0	7.9	2.9	7.2
3.0	3.1	8.2	3.0	7.6
3.5	3.2	8.5	3.1	8.0
4.0	3.2	8.8	3.1	8.4
4.5	3.1	9.1	2.9	8.6
5.0	2.9	9.1	2.7	8.7
5.5	2.5	9.1	2.4	8.7





KLI 24 - 1 LUX

Hoogte (m)				
2.5	3.1	8.2	2.9	7.3
3.0	3.2	8.5	3.1	7.8
3.5	3.4	8.7	3.2	8.3
4.0	3.4	9.0	3.2	8.6
4.5	3.3	9.3	3.1	9.0
5.0	3.1	9.5	2.9	9.1
5.5	2.8	9.5	2.7	9.2





Spacingtabel / Spacing tabel

HILED





HIL-.LO - 1 LUX

Hoogte (m)				
2.0	1.9	5.4	3.9	8.2
2.5	2.4	6.8	4.9	10.3
3.0	2.9	8.3	6.0	12.5
3.5	3.2	9.4	6.7	14.6
4.0	3.0	9.3	7.3	16.2
4.5	3.0	9.2	8.0	17.8
5.0	3.1	8.9	8.8	19.3





HIL-.LO - 1 LUX

Hoogte (m)				
5.5	3.1	8.7	9.7	20.7
6.0	3.3	8.7	10.2	22.4
6.5	3.3	8.7	11.1	23.9
7.0	3.5	8.7	11.5	25.5
7.5	3.6	8.8	12.3	27.0
8.0	3.9	9.0	13.2	28.4
8.5	3.9	9.3	14.0	29.8

HIL-.LO - 1 LUX

Hoogte (m)				
9.0	4.0	9.5	14.2	31.2
9.5	4.2	9.8	15.0	32.5
10.0	4.4	10.1	15.8	34.1
10.5	4.4	10.5	16.6	35.5
11.0	4.6	10.8	16.8	37.0
12.0	4.8	11.4	18.3	39.9
13.0	4.7	11.9	19.1	42.7





HIL-.LO - 1 LUX

Hoogte (m)				
14.0	4.8	12.5	20.6	45.4
15.0	4.8	12.8	21.3	48.0
16.0	4.6	13.1	22.7	50.5
17.0	4.5	13.5	23.3	52.9
18.0	4.1	13.8	23.8	55.3
19.0	3.3	14.1	24.2	57.5
20.0	2.1	14.4	23.7	59.8





Spacingtabel / Spacing tabel

HILED




HIL-WO - 1 LUX

Hoogte (m)				
2.0	4.0	8.5	4.0	8.5
2.5	4.3	10.1	4.3	10.1
3.0	5.0	11.6	5.0	11.6
3.5	5.6	13.0	5.6	13.0
4.0	6.2	14.2	6.2	14.2
4.5	6.7	15.5	6.7	15.5
5.0	7.0	16.7	7.0	16.7





HIL-WO - 1 LUX

Hoogte (m)				
5.5	7.2	17.8	7.2	17.8
6.0	7.5	18.7	7.5	18.7
6.5	7.7	19.6	7.7	19.6
7.0	7.8	20.4	7.8	20.4
7.5	8.1	21.1	8.1	21.1
8.0	8.2	21.7	8.2	21.7
8.5	8.2	22.4	8.2	22.4

HIL-WO - 1 LUX

Hoogte (m)				
9.0	8.4	22.9	8.4	22.9
9.5	8.6	23.5	8.6	23.5
10.0	8.7	24.1	8.7	24.1
10.5	8.7	24.6	8.7	24.6
11.0	8.7	25.0	8.7	25.0
11.5	8.7	25.5	8.7	25.5
12.0	8.7	25.9	8.7	25.9

HIL-WO - 1 LUX

Hoogte (m)				
12.5	8.6	26.3	8.6	26.3
13.0	8.4	26.6	8.4	26.6
13.5	8.0	26.9	8.0	26.9
14.0	7.3	27.1	7.3	27.1
14.5	3.8	27.4	3.8	27.4
15.0	0.1	28.1	0.1	28.1
15.5	0.3	28.6	0.3	28.6