

TECHNICAL DATA SHEET

PMA Accessories - ME-M/PG - Enlarger
Metal metric / PG thread adapter**PMA****Features & Benefits:**

- For enlarging metric to PG-threaded holes
- Outside thread with O-ring

Materials:

- Nickel-plated brass

Compatible with:

- PMAFIX Pro, PMAFIX, PMA Smart Line fittings

Temperature range:

- -30°C ... +100°C

Conforms to:

- Metric thread according to EN 60423
- PG thread according to DIN 40430

Environmental properties:

- Free from halogens and cadmium
- RoHS and REACH compliant

Product selection:

Part no.	Thread size		Dimensions in mm (nom.)				Weight kg/100 pcs	Packing unit pcs/PU
	metric (outside)	PG (inside)	g	g2	L	d2		
M12PG9M	M12 x 1.5	9	5.0	7.0	16.0	17.0	0.8	100
M16PG11M	M16 x 1.5	11	5.0	7.0	16.5	20.0	1.1	100
M20PG16M	M20 x 1.5	16	6.0	7.5	19.5	24.0	1.7	100
M25PG21M	M25 x 1.5	21	7.0	8.5	21.5	30.0	2.4	50
M32PG29M	M32 x 1.5	29	8.0	9.0	25.0	39.0	4.5	50
M40PG36M	M40 x 1.5	36	8.0	12.0	28.5	50.0	8.4	25
M50PG42M	M50 x 1.5	42	9.0	15.0	32.0	57.0	10.4	10
M50PG48M	M50 x 1.5	48	9.0	17.0	33.0	64.0	15.7	10

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time




ABB Switzerland Ltd,
PMA Cable Protection
Aathalstrasse 90
8610 Uster, Switzerland
Phone: +41 58 585 00 11
pma-info@ch.abb.com
www.pma.ch

Let's write the future.
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

