

LGR-ICOS™ GLA351-N2OCM

N₂O & CO analyzer – EP QC Rackmount



Highly sensitive, accurate and stable analyzer for reliable measurement of N₂O and CO.

Measurement made easy

LGR-ICOS™ GLA351-N2OCM N₂O & CO – Enhanced performance quantum cascade rackmount analyzer

Features and benefits

- Simultaneous measurements of N₂O and CO
- Highest stability, precision and low drift
- Measurement rates selectable up to 10 Hz
- Installed and operational in minutes
- Batch operation via syringe injection option
- Insensitive to cross-interferences
- Extremely high dynamic range
- Unsurpassed reliability
- Real-time diagnostics

Overview

The ABB LGR-ICOS gas analyzers build on the heritage and extensive track record of Los Gatos Research analyzers, using patented Off-Axis Integrated Cavity Output Spectroscopy (OA-ICOS) technology, the latest evolution in tunable diode laser absorption spectroscopy (TDLAS).

Since CO is an excellent tracer of anthropogenic emissions, simultaneous measurements of CO and N₂O can allow scientists to correlate the sources of N₂O emissions. The GLA351-N2OCM enhanced performance quantum cascade (EP QC) rackmount analyzer also simultaneously measures water vapor mole fraction. As a result, the analyzer reports N₂O and CO on a dry mole basis. It accurately corrects for water vapor dilution and absorption line broadening effects without the need for sample drying or empirical corrections.

The GLA351-N2OCM analyzer is designed for many demanding applications including trace-gas air quality monitoring, eddy correlation flux measurements, chamber flux measurements or combustion diagnostics.

... Overview

ABB's enhanced performance (EP) OA-ICOS analyzers incorporate proprietary internal thermal control for ultra-stable measurements with unsurpassed precision, accuracy and drift. Moreover, only ABB's analyzers provide reliable guaranteed measurements at mole fractions more than 20 times ambient levels.

ABB's patented OA-ICOS technology, a fourth-generation cavity enhanced absorption technique, has many advantages over older conventional and delicate cavity ringdown spectroscopy and direct absorption techniques. OA-ICOS analyzers are simpler, easier to operate and more rugged. They exhibit negligible zero and span drift and a significantly reduced need for regular calibration with expensive reference gases. As a result, ABB analyzers provide higher performance and reliability with minimal operational cost.

The GLA351-N2OCM has an internal computer that can store data practically indefinitely (for applications requiring unattended longer term operation), and send real-time recordings to a data logger through its analog and digital (RS232) outputs. The analyzer includes control and analysis software.

Accessories

MIU-16	Multiport Inlet Unit Automated control of up to 16 inlet ports
MIU-8	Multiport Inlet Unit Automated control of up to 8 inlet ports
ACC-DP3H	3-head Diaphragm External Pump
ACC-DP4H	4-head Diaphragm External Pump ~2.5x pumping speed of ACC-DP3H Fast flow option only
ACC-DS10	Dry Scroll External Pump ~9x pumping speed of ACC-DP3H Fast flow option only
ACC-DS35	Dry Scroll External Pump ~25x pumping speed of ACC-DP3H For 10Hz response time Fast flow option only
OPT-DATALOG	Digital Data Logging Capability Multi-channel data logging option records and synchronizes serial (RS-232) outputs from multiple ABB analyzers and other devices (GPS, anemometers)

ABB Inc.
Measurement & Analytics
3400, Rue Pierre-Ardouin
Quebec, Quebec
Canada G1P 0B2
Tel: +1 418 877-2944
Email: icos.sales@ca.abb.com
abb.com/analytical

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB CA does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

Ordering information

- LGR-ICOS™ GLA351-N2OCM
N₂O & CO analyzer – EP QC rackmount

Specifications

Precision (1σ, 1 sec / 10 sec / 100 sec):

N₂O: 0.1 ppb / 0.04 ppb / 0.02 ppb [<500 ppb]
CO: 0.2 ppb / 0.06 ppb / 0.03 ppb [<500 ppb]
H₂O: 50 ppm / 20 ppm / 10 ppm

Maximum Drift (15 min. average, at STP, over 24 hrs):

N₂O: <1 ppb
CO: <1 ppb
> 10x improvement achieved with periodic referencing

Linear measurement ranges (meets all specifications):

N₂O: Up to 4 ppm
CO: Up to 4 ppm
H₂O: Up to 30 000 ppm

Operational ranges:

N₂O: Up to 40 ppm
CO: Up to 40 ppm
H₂O: $<99\%$ RH, non-condensing

Measurement rate:

0.01 – 1 Hz (user selectable)
Up to 10 Hz with fast flow option

Flow response time:

<12 seconds (1/e)
Up to 10 Hz with fast flow option

Sampling conditions:

Operating temperature: 0 – 45 °C
Ambient humidity: $<99\%$ relative humidity non-condensing

Data outputs:

WiFi, Ethernet, USB, Serial (RS-232)

Power requirements:

110/240 VAC, 50/60 Hz
300 watts (steady state)
max 420 watts with ACC-DP3H
max 550 watts with ACC-DP4H

Dimensions:

50 cm (19.5 in.) H x 48 cm (19 in.) W x 86 cm (34 in.) D

Weight:

68 kg (88 pounds)

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB CA. Copyright © 2020 ABB
All rights reserved