

Stanilite®

Platinum exit LED Quickfit® theatre mask DALI



Range

Platinum range

Product group

Exit LED Quickfit



Features



- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- DALI lighting system
- Quickfit unique steel slide connect bracket for quick installation and easy maintenance
- Includes all pictograph diffuser options for single sided installation
- Universal wall/ceiling mounting, can also be rod or wire suspended
- Retrofit capability; fits into any existing Quickfit mounting bracket

Catalogue no.	Description
DALI products	
PQFBDALEDP	Platinum exit LED Quickfit theatre mask DALI single sided includes all pictograph inserts
Accessories	
MQFCL	Cantilever bracket (white)
QFWGCM	Wire guard - ceiling
QFWGWM	Wire guard - wall
PWQFKITPOLY	IP65 kit - polycarbonate for single or double sided installation
PWQFKITACRY	IP65 kit - acrylic for single or double sided installation
21-OPMD056	Diffuser theatre mask without pictograph inserts *
29-PIQFTM	Standard theatre mask pictograph inserts
Note: * For a double sided configuration additional diffuser 21-OPMD056 is required	
Spare parts	
03-01302P	Battery LiFePO4 3.2V 3.2Ah
PQFBDALEDP-LB	Platinum exit LED Quickfit theatre mask DALI less bracket pictograph
PQFBDALEDP-FR	Platinum exit LED Quickfit theatre mask DALI frame only

Note:

- The exit comes complete including pictograph insert pack as single sided exit. For double sided exit add diffuser 21-OPMD056



Dimensions			
	Length	Width	Height (incl. bracket)
	379mm	72mm	214mm
Weight			
Model	Weight		
DALI	1.8kg		

Construction		
	Part	Construction
	Body	UV/FR ABS body
	Diffuser	Acrylic
	Bracket	Black powder coated zinc steel
Light source		
	Model	Light source
	DALI	Multiple LED 1.6W
Power consumption		
	Model	Power consumption
	DALI	3.2W

Note: Preliminary results

Note:

- Designed to comply with AS2293 and meet relevant Australian EMC standards