



# External Hinged Interface

## Type JPH - Hinged Conduit Joiner



### Technical Characteristics

Conforms to	CE Mark to the low voltage directive RoHS Compliant to 2011/65/EU Conforms with end of life vehicle directive (ELV) EU200/53/EC			
Approvals and Standards	 			
Degree of mechanical protection	High			
Degree of protection	IP40 - Hinged fittings			
UV protection	Medium			
Finish	Dark Orange			
Application	One Piece joiner hinged fittings allow a variety of conduit size variations. These fittings are designed to snap together over all types of slit and un-slit conduit thus maintaining maximum conduit bore. Can be used as a reducer or as an enlarger.			
Normal operating temperature range	Minimum Temperature	Maximum Temperature	Long Term Max Temp (30,000 Hrs)	Short Term Max Temp (3000 Hrs)
	- 40°C	+160°C	+185°C	+200°C
For use with - Conduit range	Full Tempguard system protection is achieved using these fittings with HTC conduit. Compatible with all <a href="#">Harnessflex</a> range			
Fire performance	Test Standard	Performance Rating		
	<b>UL94</b>	<b>V2</b>		
	Self Extinguishing and halogen free			
Chemical resistance & Storage data	Click or See page <a href="#">3</a>			
Type of material	High Temperature Polyamide (Nylon) - Low smoke and halogen free			

Image



# External Hinged Interface

## Type JPH - Hinged Conduit Joiner




### Dimensional Data & Part Number Configuration

Part Number * Stocked Items	Conduit Sizes				Nominal Dimensions (mm)			
	(NC)		(NW)		C	D	E	F
	A	B	A	B				
JPH1208	12	8	10	7.5	38	16	10	10
JPH1212	12	12	10	10	36	16	10	10
JPH1612	16	12	13	10	36	21	10	10
JPH1616	16	16	13	13	36	21	10	10
JPH2008	20	8	17	7.5	38	26	12	10
JPH2012	20	12	17	10	38	26	12	10
JPH2016	20	16	17	13	38	26	12	10
JPH2020	20	20	17	17	38	26	12	12
<b>Part Number ** MTO Items</b>								
JPH2520	25	20	22	17	39	33	12	12
JPH2525	25	25	22	22	39	33	13	13
JPH2820	28	20	23	17	39	33	13	13
JPH2825	28	25	23	22	39	33	13	13
JPH2828	28	28	23	23	39	33	13	13

Note : Nominal Dimensions are in mm

\* Part numbers listed are stocked items available for immediate order

\*\* Parts numbers listed are available to order but not stocked items, and would therefore be subject to manufacturing leadtime



# External Hinged Interface

## Type JPH - Hinged Conduit Joiner



### Chemical Resistance Chart

<b>Key:</b>  Suitable : <span style="color: green;">●</span> Limited Suitability : <span style="color: yellow;">●</span> Unsuitable : <span style="color: red;">●</span> Not Tested : <span style="color: black;">●</span>	<span style="color: green;">●</span> Astm No.1	<span style="color: green;">●</span> Diesel oil	<span style="color: green;">●</span> Methyl Bromide	<span style="color: green;">●</span> Sulphur Dioxide (Gas)
	<span style="color: green;">●</span> Astm No.2	<span style="color: green;">●</span> Diethylamine	<span style="color: red;">●</span> MEK	<span style="color: red;">●</span> Sulphuric Acid (10%)
	<span style="color: green;">●</span> Astm No.3	<span style="color: green;">●</span> Ethanol	<span style="color: red;">●</span> Nitric Acid (10%)	<span style="color: red;">●</span> Sulphuric Acid (70%)
	<span style="color: green;">●</span> Acetic Acid (10%)	<span style="color: green;">●</span> Ether	<span style="color: red;">●</span> Nitric Acid (70%)	<span style="color: green;">●</span> Toluene
	<span style="color: green;">●</span> Acetone	<span style="color: green;">●</span> Ethylamine	<span style="color: yellow;">●</span> Oxalic Acid	<span style="color: green;">●</span> Transformer Oil
	<span style="color: green;">●</span> Aluminium Chloride	<span style="color: green;">●</span> Ethylene Glycol	<span style="color: red;">●</span> Ozone (Gas)	<span style="color: green;">●</span> 1,1,1-Trichloroethane
	<span style="color: yellow;">●</span> Aniline	<span style="color: yellow;">●</span> Ethyl Ethanoate	<span style="color: green;">●</span> Paraffin oil	<span style="color: yellow;">●</span> Trichloroethylene
	<span style="color: yellow;">●</span> Benzaldehyde	<span style="color: green;">●</span> Freon 32	<span style="color: green;">●</span> Petrol	<span style="color: green;">●</span> Turpentine
	<span style="color: green;">●</span> Benzene	<span style="color: red;">●</span> Hydrochloric Acid (10%)	<span style="color: red;">●</span> Phenol	<span style="color: green;">●</span> Urea
	<span style="color: green;">●</span> Carbon tetrachloride	<span style="color: red;">●</span> Hydrochloric Acid (36%)	<span style="color: green;">●</span> Sea Water	<span style="color: green;">●</span> Uric Acid
	<span style="color: red;">●</span> Chlorine water	<span style="color: red;">●</span> Hydrogen Peroxide (35%)	<span style="color: green;">●</span> Silver Nitrate	<span style="color: green;">●</span> Vegetable Oil
	<span style="color: red;">●</span> Chloroform	<span style="color: red;">●</span> Hydrogen Peroxide (87%)	<span style="color: green;">●</span> Skydrol	<span style="color: yellow;">●</span> Vinyl Acetate
	<span style="color: yellow;">●</span> Citric Acid	<span style="color: green;">●</span> Lactic Acid	<span style="color: green;">●</span> Sodium Chloride	<span style="color: green;">●</span> Water
	<span style="color: green;">●</span> Copper Sulphate	<span style="color: green;">●</span> Lubricating oil	<span style="color: yellow;">●</span> Sodium Hydroxide (10%)	<span style="color: green;">●</span> White Spirit
	<span style="color: red;">●</span> Cresol	<span style="color: yellow;">●</span> Methanol	<span style="color: red;">●</span> Sodium Hydroxide (60%)	<span style="color: yellow;">●</span> Zinc Chloride

The information above is given as a guide only and is based on published technical data and experience.  
 The chemical resistance of the above products is dependant on factors such as chemical exposure, concentration of the chemical and temperature.  
 The above chemicals are valid for a temperature of 23°C.  
 Use of the above table is at the users own discretion and risk.  
 Those using it must satisfy themselves that their application presents no health and safety risks.  
 The end user should assess compatibility with their application and contact Harnessflex for further information.

ADHERENCE TO THE CURRENT WIRING REGULATIONS BS7671 OR NEC WIRING REGULATIONS (FOR USA) IS STRONGLY ADVISED.  
 MINIMUM BEND RADIUS FOR FLEXING IS DEPENDANT UPON MINIMUM TEMPERATURE, BENDING FREQUENCY AND CHEMICAL ENVIRONMENT.

### Storage Guidelines

To maintain balanced moisture content, Harnessflex recommends storing products under the following conditions:

<b>Storage temp.</b>	<b>Installation temp.</b>	<b>Rel. humidity</b>
18°C to 30°C	>18°C	>30%

If products from an outside environment are brought into a heated processing area, the change in climate may suddenly cause temporary de-moisturisation around the edges. After 24 hours in the processing area a natural balance will be restored.

Observing this storage recommendation ensures optimum process-ability and material properties.

