


On-load tap-changer type UCGL./III, VUCGL./III, UCLL./III, UC DL./III, VUCLR./III,
 10 tap positions, linear switching.
 Min. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 6,
 the preceding pos. was 5.

Lindningskopplare typ UCGL./III, VUCGL./III, UCLL./III, UC DL./III, VUCLR./III,
 10 lägen, linjär koppling.
 Min antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 6,
 föregående läge var 5.

Pos. Läge	Tap selector and diverter connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	



The tap-changer is shown in pos. 6,
 the preceding pos. was 5.
 The tap selector is seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 6,
 föregående läge var 5.
 Väljaren sedd uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
 tap-changer. Dashed lines show leads belonging
 to the cleats and leads.

Heldragna linjer visar ledare som ingår i
 lindningskopplaren. Streckade linjer visar
 ledare som tillhör anslutningsdonet.

Sheet	Cont						
	Year	Week					
Form No.	Dept						
	Rev Ind	Revision	Appd	Year	Week		
Design checked by	Accepted by	Accepted for prod by			Description (English)	DATA ORIGINAL	
	Design checked by	R.Yngvesson			CONNECTION DIAGRAM		
	Design checked by	Drawn by	L.Bergman			Description (own language)	File name
	Design checked by	Issued by	Year	Week	KOPPLINGSSCHEMA		0370-2
Asea Brown Boveri	5492 0370-2				Lang	Sheet	
					Rev Ind	Cont	

We reserve all rights in this document and in the
 information contained therein. Reproduction, use or
 disclosure to third parties without express authority
 is strictly forbidden. © ABB '19