


FurseWELD

Bar to bar BB41

Bar to bar BB41 - FurseWELD

	Flat tape conductor size A (mm)	Flat tape conductor size B (mm)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
	20 x 3	20 x 3	BB41-4-203203	7TCA083910R0254	65P10	HCPK4
	25 x 3	25 x 3	BB41-4-253253	7TCA083910R0256	65P10	HCPK4
	25 x 3	25 x 3	BB41-4-253253-IU	-	65P10	HCPK4
	25 x 4	25 x 4	BB41-4-254254	7TCA083910R0258	90P10	HCPK4
	25 x 6	25 x 6	BB41-4-256256	7TCA083910R0259	115P10	HCPK4
	30 x 3	30 x 3	BB41-4-303303	7TCA083910R0263	115P10	HCPK4
	30 x 4	30 x 4	BB41-4-304304	7TCA083910R0265	115P10	HCPK4
	30 x 5	30 x 5	BB41-4-305305	7TCA083910R0266	115P10	HCPK4
	31 x 6	31 x 6	BB41-4-316316	7TCA083910R0269	115P10	HCPK4
	38 x 5	38 x 5	BB41-4-385385	7TCA083910R0272	150P10	HCPK4
	38 x 6	38 x 6	BB41-4-386386	7TCA083910R0273	200P10	HCPK4
	40 x 3	40 x 3	BB41-4-403403	7TCA083910R0274	200P10	HCPK4
	40 x 4	40 x 4	BB41-4-404404	7TCA083910R0275	200P10	HCPK4
	40 x 5	40 x 5	BB41-4-405405	7TCA083910R0276	200P10	HCPK4
	40 x 6	40 x 6	BB41-4-406406	7TCA083910R0279	200P10	HCPK4
	50 x 3	50 x 3	BB41-5-503503	7TCA083910R0285	200P10	HCPK5
	50 x 4	50 x 4	BB41-5-504504	7TCA083910R0286	200P10	HCPK5
	50 x 5	50 x 5	BB41-5-505505	7TCA083910R0288	200P10	HCPK5
	50 x 6	50 x 6	BB41-5-506506	7TCA083910R0291	200P10	HCPK5

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

Conductors must be installed in the orientation shown to achieve the correct connection