


TYPICAL WIRING DIAGRAM



UL US
LISTED
TERMINATION
BOX
112Y

Use CU/AL Wire

USE ONLY 60 DEG.C (140 DEG.F) CONDUCTORS ON ALL FIELD INSTALLED LINE, LOAD AND NEUTRAL TERMINATIONS.

THE MAXIMUM SHORT CIRCUIT RATING OF THIS DEVICE IS 10,000 RMS SYMMETRICAL AMPERES AT A MAXIMUM OF 240 VAC.

ALUMINUM TERMINATIONS: TO HELP GUARD AGAINST OVERHEATING WHEN CONNECTING ALUMINUM WIRE IN CU/AL LUG, REMOVE OXIDE FILM FROM WIRE AND PROTECT IT WITH OXIDE INHIBITING COMPOUND.

WIRE RANGE

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRD	SOLID	STRD
LINE - 462 NEUTRAL	14-8	14-4	12-8	12-4
LOAD - 462 NEUTRAL	14-8	14-4	12-8	12-4
NEUTRAL - 482 NEUTRAL	14-8	14-4	12-8	12-4
EQUIP. GRD. - 6L3	12-8	12-2	12-8	12-2

RAINFOOF TERMINAL BOX

MODEL NO. **T1206**
60 AMPS 120/240 VOLTS A-C
TYPE 3R ENCLOSURE

WHEN CABINET HAS PROVISIONS FOR A CONDUIT HUB, SELECT FROM THE CHART BELOW.

CONDUIT SIZE	CLOSURE CAP	3/4	1	1 1/4	1 1/2
CAT. NO.	B01	B07	B10	B12	B15

LUG TIGHTENING TORQUE (LB-IN)

SCREW TYPE	WIRE SIZE	TORQUE
SLOT	14-10	32-35
	8	36-40
	6-4	41-45
	3-2/0	45-50

⚡ DANGER

HAZARD OF ELECTRICAL SHOCK OR BURN. TURN OFF POWER BEFORE WORKING INSIDE THIS EQUIPMENT.

⚡ DANGER

RISQUE DE CHOC ÉLECTRIQUE OU DE BRÛLURE FERMER L'ALIMENTATION ÉLECTRIQUE AVANT DE TRAVAILLER À L'INTÉRIEUR DE CET ÉQUIPEMENT.

MIDWEST ELECTRIC PRODUCTS, INC.
 P.O. BOX 910
 MANKATO, MN 56002-0910
 WWW.MIDWESTELECTRIC.COM
 SALTILLO PLANT MADE IN MEXICO

MNP600174

