
 TECHNICAL DATA SHEET

PMAFIX IP68 - BVIVG-U - Fitting

Straight, for MIL-C5015 connector with UN female thread

PMA



IP68, polyamide fitting for flexible non-metallic conduit



Applications:

- For cable protection systems in a wide range of applications

Features & Benefits:

- Easy installation: simple push fit assembly
- Very high impact resistance
- Vibration-proof connection to PMA conduits
- High conduit pull-out strength
- Can be easily re-opened with a screwdriver
- Very good chemical properties
- Fits both conduit profiles - fine (T) and coarse (G)

Ingress protection:

- IP66, IP68 & IP69 (EN/IEC 60529)
- IP69, 100 bar with Water impact protection (WPS-ring)

Materials:

- High-grade, specially formulated polyamide 6

Compatible with:

- PMAFLEX Pro Conduits
- PMAFLEX Multilayer Conduits
- PMAFLEX Conduits
- PMA Smart Line Conduits
- MIL connector series C5015

Conforms to:

- EN 45545-2 HL3 (R22 & R23)
- NFPA 130
- UL 94 (V0)
- UL 1696 (UL file E80294)

Weathering resistance:

- Very good UV resistance and weathering characteristics

Colour:

- Black

Chemical properties:

- Please refer to www.pma.ch (Technical Information / Chemical Resistance)


Environmental properties:

- Free from halogens and cadmium
- RoHS and REACH compliant

Product selection:

Part no.	Thread size	Conduit size	Connector size	Dimensions in mm (nom.)			Weight	Packing unit
				g	L	d2		
black	UN	NW	MIL	g	L	d2	kg/100 pcs	pcs/PU
BVIVG-U152	5/8"-24UNEF	12	10	8.0	36.5	23.5	0.7	50
BVIVG-U187	3/4"-20UNEF	17	14	9.0	46.5	30.5	1.5	50
BVIVG-U210	7/8"-20UNEF	10	16	9.0	37.0	29.0	0.9	50
BVIVG-U212	7/8"-20UNEF	12	16	9.0	38.5	29.0	1.0	50
BVIVG-U217	7/8"-20UNEF	17	16	9.0	46.5	30.5	1.1	50
BVIVG-U242	1"-20UNEF	12	18	9.0	40.5	32.0	1.1	50
BVIVG-U243	1"-20UNEF	23	18	9.0	55.0	32.0	1.9	30
BVIVG-U247	1"-20UNEF	17	18	9.0	47.5	32.0	1.2	50
BVIVG-U292	1 3/16"-18UNEF	12	20	9.0	40.5	35.0	1.3	50
BVIVG-U293	1 3/16"-18UNEF	23	20	9.0	55.0	35.0	1.9	30
BVIVG-U297	1 3/16"-18UNEF	17	20	9.0	47.5	35.0	1.6	50
BVIVG-U299	1 3/16"-18UNEF	29	20	9.0	47.0	44.0	1.8	20
BVIVG-U349	1 3/8"-18UNEF	29	22	9.0	52.0	44.0	2.6	20
BVIVG-U352	1 7/16"-18UNEF	12	24	10.0	39.0	44.0	1.7	50
BVIVG-U353	1 7/16"-18UNEF	23	24	9.0	52.0	44.0	2.0	30
BVIVG-U356	1 7/16"-18UNEF	36	24	9.0	63.0	53.5	2.4	20
BVIVG-U357	1 7/16"-18UNEF	17	24	9.0	46.5	44.0	1.9	50
BVIVG-U359	1 7/16"-18UNEF	29	24	9.0	52.0	44.0	2.1	20
BVIVG-U433	1 3/4"-18UNS	23	32	10.0	52.0	53.0	2.5	30
BVIVG-U436	1 3/4"-18UNS	36	32	10.0	62.5	53.0	3.3	20
BVIVG-U437	1 3/4"-18UNS	17	32	10.0	46.5	53.0	2.3	50
BVIVG-U439	1 3/4"-18UNS	29	32	10.0	51.5	53.0	2.7	20
BVIVG-U503	2"-18UNS	23	36	10.0	51.5	58.0	2.7	30
BVIVG-U506	2"-18UNS	36	36	10.0	62.5	58.0	3.4	20
BVIVG-U508	2"-18UNS	48	36	10.0	64.5	66.0	4.5	10
BVIVG-U509	2"-18UNS	29	36	10.0	55.0	58.0	3.6	20
BVIVG-U563	2 1/4"-16UN	23	40	10.0	51.0	64.0	2.9	30
BVIVG-U566	2 1/4"-16UN	36	40	10.0	62.0	64.0	3.7	20
BVIVG-U568	2 1/4"-16UN	48	40	10.0	64.0	66.0	4.5	10
BVIVG-U569	2 1/4"-16UN	29	40	10.0	51.0	64.0	2.8	20
BVIVG-U628	2 1/2"-16UN	48	-	10.0	64.0	72.0	4.9	10

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time



Mechanical Properties:	Value:	Test parameters:	Test method:
Tensile modulus	1'200 ... 3'700 N/mm ²		ISO 527
Tensile strength	45 ... 65 N/mm ²		ISO 527
Notched bar impact test	4 ... 20 kJ/m ²		ISO 180/1C
Vibration and shock standard	Cat. 2		IEC 61373, IEC 60068-2-27 / -64

Thermal properties:	Value:	Test parameters:	Test method:
Continuous application temperature	-50 ... +105°C		PMA DO 9.21-4510
Upper application temperature	+120°C	(20'000 h)	PMA DO 9.21-4360
Short-term	+160°C	(168 h)	PMA DO 9.21-4360

Fire safety properties:	Value:	Test parameters:	Test method:
Fire performance	non flame-propagating		IEC EN 61386-1
Flame class	V0		UL 94

Fire hazard level	HL3		EN 45545-2 (R22)
Oxygen index	> 32 %		EN ISO 4589-2
Smoke density	< 150 Ds max.		EN ISO 5659-2 (25 kW/m ²)
Toxicity	< 0.75 CIT _{NLP}		NF X 70-100-1/-2: (600°C)

Fire hazard level	HL3		EN 45545-2 (R23)
Oxygen index	> 32 %		EN ISO 4589-2
Smoke density	< 300 Ds max.		EN ISO 5659-2 (25 kW/m ²)
Toxicity	< 1.5 CIT _{NLP}		NF X 70-100-1/-2: (600°C)

Fire performance NFPA 130:			NFPA 130
- Flammability	compliant		ASTM E 162
- Smoke density	compliant		ASTM E 662

Heat and visible smoke	26.00 MJ/kg		ASTM E 1354
Smoke emission toxicity	compliant		Bombardier SMP 800-C
Smoke emission toxicity	compliant		Boeing BSS 7241

Content of delivery:

- Fitting with conduit locking clip (OVN2)
- conduit gasket (NVN3),
- O-ring (OR)

Assembly instructions:

- Please consider the appropriate assembly instructions on www.pma.ch

ABB Switzerland Ltd,
PMA Cable Protection
Aathalstrasse 90
8610 Uster, Switzerland
Phone: +41 58 585 00 11
pma-info@ch.abb.com
www.pma.ch

Let's write the future.
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

