
Technical Data Sheet

Cyberex® SuperSwitch®4 DSTS

800A – 1200A



About This document

Document information

File name	:	ABB_STS_TDS_SS4_800A-1200A
Model	:	800A – 1200A SS4 - UL
Date of issue	:	05-24-2022
Issued by (department)	:	Product Marketing
Checked by (department)	:	R&D Engineering
Article number	:	...
Document number	:	TDS-STS-MK-0183
Revision	:	REV-A
Revision date	:	05-24-2022



Contents

1	Introduction	4
1.1	Key features and benefits	4
1.2	Mechanical characteristics	5
1.3	General specification	6
1.4	Environmental characteristics	6
2	Electrical characteristics	7
2.1	Electrical ratings	7
2.2	Components	7
3	Operational characteristics	8
3.1	Operational specifications	8
3.2	Power quality and metering	8
4	Control and communications	9
4.1	Communications interfaces	9
5	Options	9
5.1	Accessories	9

1 Introduction

ABB Cyberex SuperSwitch4 (SS4) DSTS is a three-phase, semiconductor-based switching device used for sub-cycle transferring of critical loads between two input sources. Designed with state-of-the-art controls, redundant logic, and compartmentalized design, the SS4 provides unrivalled performance and safety in a compact frame.

1.1 Key features and benefits



Peak performance and reliability

- $\leq 1/4$ cycle in-phase transfers.
- $\leq 16\text{ms}$ out of phase transfers regardless of phase difference between sources.
- $\leq 1.2\text{x}$ inrush for out of phase transfers.



Minimize risk of human error

- On-screen software guided bypass operation.
- Dedicated LED indicators coordinate with bypass instructions on HMI to ensure proper bypass sequence.



Improved safety and serviceability

- Sectionalized design for safety and ease of serviceability enables quicker troubleshooting and time to repair.
- Isolation of consumable components allows for easier replacement without need to de-energize equipment.



Comprehensive offering

- Covering wide power range from 100A up to 4000A in 208V through 480V.
- Ultra-dense optimized designs for low power applications.
- Optimized front access only designs for higher power ratings.




Improved sustainability through robust, high efficiency design and minimized usage of consumable components.



Key applications

- Data centers
- Healthcare facilities
- Financial institutions
- Colleges/Universities

1.2 Mechanical characteristics



Dimensions (W x D x H)	46 x 34 x 78 inches / 1168.4 x 863.6 x 1981.2 mm	
Weight	800A:	1600 lbs / 725.7 kg
	1000A:	1700 lbs / 771.1 kg
	1200A:	1750 lbs / 793.8 kg
Floor loading	800A:	$\leq 147.4 \text{ lbs/ft}^2 / \leq 719.3 \text{ kg/m}^2$
	1000A:	$\leq 156.6 \text{ lbs/ft}^2 / \leq 764.2 \text{ kg/m}^2$
	1200A:	$\leq 161.2 \text{ lbs/ft}^2 / \leq 786.7 \text{ kg/m}^2$
Heat output	BTU/Hr at full load	kW
	800A:	12250
	1000A:	15300
	1200A:	22900

1.3 General specification

Standards	ETL listed to UL 1008S
Audible noise level	800A : ≤65dBA at 1 m 1000A : ≤65dBA at 1 m 1200A : ≤75dBA at 1 m
Access requirements	Front only for installation, operation, and maintenance
Degree of protection against hazards and water ingress	IP20
Cooling	Forced air cooling
Ventilation	Front and rear forced air exhaust
Frame color	RAL 9005 (black)
Transport	On pallet Cabinet suitable for handling by forklift
Cable entry/exit	Top and/or bottom

1.4 Environmental characteristics

Ambient operating temperature range	[° F/° C]	32 - 104° F / 0 - 40° C
Ambient non-operating temperature range	[° F/° C]	-13 - 131° F / -25 - 55° C
Relative humidity range	[%]	10 - 95%, non-condensing
Altitude without de-rating	[ft/m]	Up to 6000 ft / 1828 m
Seismic rating		N/A

2 Electrical characteristics

2.1 Electrical ratings

Amp ratings	[A]	800, 1000, 1200
Voltage ratings	[V]	208, 380, 480
Neutral		Unswitched
Voltage window		+/-10%
SCCR ratings	[kAIC]	65
Input/output frequency	[Hz]	60 +/-5% (57 – 63Hz)
Overload capability		125% for 30 min 150% for 1 min 200% for 10 sec 1000% for 3 cycles 1500% for 1 cycle

2.2 Components

Power semiconductors		100% rated SCRs, type II fuseless design
User interface		10.4" color TFT industrial use VGA LED touchscreen GUI
Cooling		Redundant fans
Power supplies		Triple redundant
Surge protection		40kA SPD on each source
Control logic		Dual redundant
Protection		UL 489 molded case switches
Output load switches		Redundant
Power wire & bus bar		Copper

3 Operational characteristics

3.1 Operational specifications

Full load efficiency	Up to 99.4% (480V), 98.7% (208V)
Sense + transfer time (in-phase)	< 4ms patented A9 transfer method
Sense + transfer time (out-of-phase)	< 16ms patented Real Time Flux Control™ for DIR method
Downstream transformer inrush¹	< 1.2x nominal transformer rating
Bypass	System guided via local display
MTBDE	1.5 million hours

¹ Based on DIR transfer

3.2 Power quality and metering

Loss of source detection	2ms, PLL detection per phase
Voltage	Each source and output. True RMS, up to 13 th harmonic
Current	Each source and output. True RMS, up to 13 th harmonic
Peak current detection	Each source, resettable
Source reacquisition	3 cycles

4 Control and communications

4.1 Communications interfaces

Modbus over RTU (via RS485)	Standard
Modbus over TCP (via Ethernet)	Standard
Serial service port (via USB)	Standard
Customer download port (via USB)	Standard
Local EPO	No
Remote EPO - Emergency Power OFF (n/c contact, customer supplied)	Standard
User Interface Board (UIB)	Standard
Alarm relays	16 form "C" relays
Building alarm inputs	10 dry contact inputs

5 Options

5.1 Accessories

-
1. Seismic rated floorstands (12" – 48"H)
-



<https://new.abb.com/ups/static-switches>

—
ABB Inc.
5900 Eastport Boulevard
Richmond, VA 23231
USA



© Copyright 2022 ABB. All rights reserved.

Specifications subject to change without notice.

The information contained in this publication is intended solely for the purposes indicated. The present publication and any other documentation supplied with the STS system is not to be reproduced, either in part or in its entirety, without the prior written consent of ABB.

Changes to the product or to the information contained in this document are reserved; so are errors and omissions. Please reference ABB order confirmations and submittal documentation packages for job specific configurations.