

# Quotation Request for ABB K-Tek Products AT500 Magnetostrictive Level Transmitter

Factory Contact: \_\_\_\_\_

\*All Fields Required

## Seller Information

Name: \_\_\_\_\_  
Phone: \_\_\_\_\_  
Email: \_\_\_\_\_  
Company or LBU: \_\_\_\_\_  
Main Phone: \_\_\_\_\_  
Fax: \_\_\_\_\_

## End User Information

Name: \_\_\_\_\_  
Phone: \_\_\_\_\_  
Email: \_\_\_\_\_  
Company: \_\_\_\_\_  
Country of Final Destination: \_\_\_\_\_

Note: This information will be required before accepting an order

---

## Tag ID #

---

## Process Conditions

Upper Fluid Operating Sp. Gravity: \_\_\_\_\_  
Minimum Specific Gravity: \_\_\_\_\_  
Lower Fluid Second Sp. Gravity: \_\_\_\_\_  
Fluid(s): \_\_\_\_\_

If water, steam service? Yes - No

Operating Temp: \_\_\_\_\_ Max Temp: \_\_\_\_\_  
Operating Pressure: \_\_\_\_\_ Max Pressure: \_\_\_\_\_  
Minimum Ambient Temperature: \_\_\_\_\_  
High Vibration Environment (Compressor Etc.)? Yes - No

---


## Float Selection

Float # \_\_\_\_\_  
Material \_\_\_\_\_  
Length \_\_\_\_\_  
Min ID \_\_\_\_\_  
Max OD \_\_\_\_\_

---

## Probe Material

- 316 SS (std)
- Alloy 20
- Hastelloy C-276
- PFA Jacket



## Approval or Documentation Required

CRN  
 GOST – Russian  
 ABS

PED  
 ASME  
 Lloyds

NACE  
 FM  
 CSA

ATEX  
 Other

---

## Retrofit Information Only

Is this AT unit being retrofitted to an existing ABB MLG? Y or N  
If YES, then specify the serial number: \_\_\_\_\_

Is this AT unit being retrofitted to an existing competitor MLG? Y or N  
If YES, then specify competitor name: \_\_\_\_\_

Specify the MLG (see figure):  
ML (measuring length): \_\_\_\_\_  
X: \_\_\_\_\_  
Y: \_\_\_\_\_

Does the existing MLG have an insulation blanket? Y or N  
Chamber Flange Type (circle one): Slip On or Weld Neck

