


**QQGQ2.E196145**
**Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component**
[Page Bottom](#)
**Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component**
[See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component](#)

ABB STOTZ-KONTAKT GMBH  
HAUPTSTRASSE 14-16  
78132 HORNBERG, GERMANY

E196145

| Model No.            | Rated Input                       |       | SC | Max Output |       |       | OC  | SP      | EP  | FC | GC |
|----------------------|-----------------------------------|-------|----|------------|-------|-------|-----|---------|-----|----|----|
|                      | Volts                             | Hz    |    | V          | A     | VA    |     |         |     |    |    |
| CP-A CM[*r]          | 13 - 30dc                         | -     | 3  | 30dc       | 0.1   | 3     | 3   | 60950-1 | 20B | 0  | 0  |
| CP-A RU              | 10-40dc                           | -     | 3  | 39.4dc     | 40    | 157.6 | 3   | 60950-1 | 20B | 0  | 0  |
| CP-ASI / 2.8         |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 100-120/<br>200-240 115/<br>230ac | 50/60 | 0  | 30.7dc     | 3.1   | 88.5  | 1/3 | 60950   | 15B | 5  | 1  |
| CP-ASI / 4.0[*r]     |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 100-120/<br>220-240Vac,240-300Vdc | 50-60 | 0  | 30.5dc     | 4     | -     | 3   | 60950-1 | 20  | 5  | 1  |
| CP-ASI / 4.0 DC / DC |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 24dc                              | -     | 3  | 30.4dc     | 7.3   | 150.2 | 3   | 60950-1 | -   | 5  | 1  |
| CP-ASI / 8.0         |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 100-120/<br>220-240ac             | 50-60 | 0  | 30.3       | 10.05 | 304.4 | 3   | 60950   | 15B | 5  | 1  |
| CP-C 24 / 10.0[*r]   |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 110-240ac                         | 48-63 | 0  | 24dc       | 10    | 240   | 3   | 60950-1 | -   | 0  | 1  |
| CP-C 24 / 20.0[*r]   |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 110-240ac                         | 48-63 | 0  | 24dc       | 20    | 480   | -   | 60950-1 | 20B | 0  | 1  |
| CP-C 24 / 5.0        |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 110-240ac                         | 48-63 | 0  | 28         | 12    | 225   | 3   | 60950-1 | -   | 0  | 1  |
| CP-D 12 / 0.83       |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 100-240ac                         | 47-63 | 0  | 12.07      | 1.31  | 13.44 | 3   | 60950-1 | 20B | 0  | 2  |
| CP-D 12 / 2.1[*r]    |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 100-240ac                         | 47-63 | 0  | 12         | 2.1   | -     | -   | 60950-1 | 20B | 0  | 2  |
| CP-D 12 / 4.5        |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 100-240ac                         | 47-63 | 0  | 12.05dc    | 6     | 53.4  | 3   | 60950-1 | 20B | 0  | 2  |
| CP-D 12 / 6.0        |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 100-240ac                         | 47-63 | 0  | 12.02      | 9.11  | 90.1  | 3   | 60950-1 | 20B | 0  | 2  |
| CP-D 15 / 0.67       |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 100-240ac                         | 47-63 | 0  | 14.94      | 1.25  | 14.24 | 3   | 60950-1 | 20B | 0  | 2  |
| CP-D 15 / 2.0        |                                   |       |    |            |       |       |     |         |     |    |    |
|                      | 100-240ac                         | 47-63 | 0  | 15.1dc     | 3.67  | 38.05 | 3   | 60950-1 | 20B | 0  | 2  |
| CP-D 15 / 4.0        |                                   |       |    |            |       |       |     |         |     |    |    |
|                      |                                   |       |    |            |       |       |     |         |     |    |    |

|                    |                       |       |   |         |      |        |   |              |     |   |   |
|--------------------|-----------------------|-------|---|---------|------|--------|---|--------------|-----|---|---|
|                    | 100-240ac             | 47-63 | 0 | 15.01dc | 5.6  | 64.87  | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 15 / 5.0      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 15.023  | 8.76 | 98.2   | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 24 / 0.42     |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 23.94   | 0.8  | 15.8   | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 24 / 1.3      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 24.08dc | 3.1  | 37.52  | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 24 / 2.5      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 24.02dc | 3.88 | 72.22  | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 24 / 3.8      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 24      | 3.8  | 91     | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 24 / 4.2      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 24.08   | 7.71 | 122.58 | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 5 / 1.5       |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 4.99    | 2.54 | 10.36  | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 5 / 12.0      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 5.035   | 17.2 | 52.64  | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 5 / 3.0       |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 5.038dc | 7    | 21.8   | 3 | 60950-1      | 20B | 0 | 2 |
| CP-D 5 / 7.0       |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 5.02dc  | 9.9  | 35.43  | 3 | 60950-1      | 20B | 0 | 2 |
| CP-E 12 / 1.5[*r]  |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 12dc    | -    | 18     | 3 | 60950-1, 2nd | 20B | 1 | 0 |
| CP-E 12 / 10.0     |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 115/<br>220/<br>230ac | 47-63 | 0 | 12.02   | 14   | 124.68 | 3 | 60950-1      | 20B | 0 | 1 |
| CP-E 12 / 2.5      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 14.96dc | 4    | 45.88  | 3 | 60950-1      | 20B | 0 | 1 |
| CP-E 12 / 5.0      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 14.76dc | 7    | 87     | 3 | 60950-1      | 20B | 0 | 1 |
| CP-E 15 / 1.2[*r]  |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 15dc    | -    | 18     | 3 | 60950-1, 2nd | 20B | 1 | 0 |
| CP-E 24 / 0.75[*r] |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 24dc    | -    | 18     | 3 | 60950-1, 2nd | 20B | 1 | 0 |
| CP-E 24 / 1.25     |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 120-240ac             | 47-63 | 0 | 24dc    | -    | 30     | 3 | 60950-1      | 20B | 0 | 1 |
| CP-E 24 / 10.0     |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 115/<br>230ac         | 47-63 | 0 | 24dc    | 14.5 | 308.1  | 3 | 60950-1      | 20B | 0 | 1 |
| CP-E 24 / 2.5      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 100-240ac             | 47-63 | 0 | 28.5dc  | 3.48 | 91.45  | 3 | 60950-1      | 20B | 0 | 1 |
| CP-E 24 / 20.0     |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 115/<br>230ac         | 47-63 | 0 | 24.07dc | 27.3 | 567.1  | 3 | 60950-1      | 20B | 0 | 0 |
| CP-E 24 / 5.0      |                       |       |   |         |      |        |   |              |     |   |   |
|                    | 115/<br>220/<br>230ac | 47-63 | 0 | 24.07   | 7.6  | 131.7  | 3 | 60950-1      | 20B | 0 | 1 |

|                         |                                       |       |   |         |      |        |   |              |     |   |   |
|-------------------------|---------------------------------------|-------|---|---------|------|--------|---|--------------|-----|---|---|
| CP-E 48 / 0.62          |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 100-240ac                             | 47-63 | 0 | 56.87dc | 0.93 | 42     | 3 | 60950-1      | 20B | 0 | 1 |
| CP-E 48 / 1.25          |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 100-240ac                             | 47-63 | 0 | 28.5dc  | 3.48 | 91.45  | 3 | 60950-1      | 20B | 0 | 1 |
| CP-E 48 / 10.0          |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 115/<br>230ac                         | 47-63 | 0 | 48.05dc | 13.5 | 583.9  | 3 | 60950-1      | 20B | 0 | 0 |
| CP-E 48 / 5.0[*r]       |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 115/<br>230ac                         | 47-63 | 0 | 48dc    | 5    | 240    | 3 | 60950-1      | 20B | 0 | 1 |
| CP-E 5 / 3.0[*r]        |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 100-240ac                             | 47-63 | 0 | 5dc     | -    | 15     | 3 | 60950-1, 2nd | 20B | 1 | 0 |
| CP-E 5 / 6.0            |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 100-240ac                             | 47-63 | 0 | 5.87dc  | 7.9  | 41.38  | 3 | 60950-1      | 20B | 0 | 1 |
| CP-S 24 / 10.0[*r]      |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 110-120/<br>220-240ac                 | 48-63 | 0 | 24dc    | 10   | 240    | 3 | 60950-1      | -   | 0 | 1 |
| CP-S 24 / 20.0[*r]      |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 110-240ac                             | 48-63 | 0 | 24dc    | 20   | 480    | - | 60950-1      | 20B | 0 | 1 |
| CP-S 24 / 5.0           |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 110-240ac                             | 48-63 | 0 | 24      | 12.5 | 176    | 3 | 60950-1      | -   | 0 | 1 |
| CP-T 24 / 10.0          |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 3PH 400-500Vac                        | 47-63 | 0 | 24.1dc  | 13.7 | 289.92 | 3 | 60950-1      | 20B | 0 | 1 |
| CP-T 24 / 20.0          |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 3PH 400-500ac                         | 47-63 | 0 | 24.1    | 29.6 | 513    | 3 | 60950-1      | 20B | 0 | 1 |
| CP-T 24 / 40.0          |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 3PH 400-500Vac                        | 47-63 | 0 | 24.1dc  | 44.5 | 1038   | 3 | 60950-1      | 20B | 0 | 1 |
| CP-T 24 / 5.0           |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 3PH 400-500Vac                        | 47-63 | 0 | 24.08dc | 6.95 | 152.32 | - | 60950-1      | 20B | 0 | 1 |
| CP-T 48 / 10.0          |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 3PH 400-500ac                         | 47-63 | 0 | 48.2    | 19.7 | 498    | 3 | 60950-1      | 20B | 0 | 1 |
| CP-T 48 / 20.0          |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 3PH 400-500Vac                        | 47-63 | 0 | 48.1dc  | 27.5 | 1176   | 3 | 60950-1      | 20B | 0 | 1 |
| CP-T 48 / 5.0           |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 3PH 400-500Vac                        | 47-63 | 0 | 48.03dc | 6.32 | 279.93 | 3 | 60950-1      | 20B | 0 | 1 |
| Syston PS TSL 24V / 20A |                                       |       |   |         |      |        |   |              |     |   |   |
|                         | 100-120/<br>208-240/<br>115/<br>230ac | 50/60 | 0 | 54      | 21.5 | 516    | 3 | 1950         | -   | 0 | 1 |

[\*r] - Output values are rated.

Marking: Company name or trademark   and catalog designation on the product or on the smallest unit container in which the product is packaged.  
Last Updated on 2012-11-21

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2012 UL LLC".