


Model 653T
Electronic temperature transmitter
(PC programmable)

- **High flexibility and wide rangeability**
- **Single transmitter accepts RTD/THC/mV/ohm**
- **Galvanically isolated from sensor**
- **Primary element and calibration selectable**
- **User-selectable output drive under input failure conditions**
- **Complies with relevant IEC requirements for test procedure and environmental protection**
- **CENELEC Intrinsic Safety / Flameproof and Factory Mutual approvals**
- **Configurable to the actual application by standard PC**



600T Series transmitter
A complete family of process transmitters providing high performance in real operating conditions

FEATURES

Model 653T electronic transmitter is an extension of the Kent-Taylor 2-wire analog product line.

It is designed for factory setting, in order to meet the specific application requirement of measuring low level signals from thermocouples (THC), resistance thermometer (RTD), resistance (ohm) or e.m.f. (mV) sources.

The instrument can be easily reconfigured for actual requirements by simple procedures through a standard PC equipped with a specific software available on request. (Part no. AN0239)

The temperature transmitter can be mounted directly on a thermowell and thermowell extension, or it can be mounted remotely on a pipestand.

The transmitter assures operational security by using non-volatile memory and also handling up/down scale procedure under sensor anomalies.

Compact, rugged, lightweight, easy to install and service, Kent-Taylor transmitters provide consistently reliable and stable performance under all types of process conditions, coupled with minimum maintenance requirements

FUNCTIONAL SPECIFICATIONS

INPUT SOURCE		MEASURING RANGE	MIN SPAN
Standard	Sensor		
IEC 584-1	Thermocouple Type B	+ 400 to + 1820°C (+ 752 to + 3308°F)	200°C (360°F)
	Thermocouple Type E	- 100 to + 1000°C (- 148 to + 1832°F)	50°C (90°F)
	Thermocouple Type J	- 100 to + 1200°C (- 148 to + 2192°F)	50°C (90°F)
	Thermocouple Type K	- 180 to + 1370°C (- 292 to + 2498°F)	50°C (90°F)
	Thermocouple Type R	- 50 to + 1760°C (- 58 to + 3200°F)	200°C (360°F)
	Thermocouple Type S	- 50 to + 1760°C (- 58 to + 3200°F)	200°C (360°F)
	Thermocouple Type T	- 200 to + 400°C (- 328 to + 752°F)	50°C (90°F)
	Thermocouple Type N	- 180 to + 1300°C (- 292 to + 2372°F)	100°C (180°F)
DIN 43710	Thermocouple Type L	- 100 to + 900°C (- 148 to + 1652°F)	50°C (90°F)
	Thermocouple Type U	- 200 to + 600°C (- 328 to + 1112°F)	75°C (135°F)
ASTM E 998	Thermocouple Type W3	+ 400 to + 2300°C (+752 to + 4172°F)	200°C (360°F)
	Thermocouple Type W5	+ 400 to + 2300°C (+752 to + 4172°F)	200°C (360°F)
IEC 751 / DIN43760 ($\alpha = 0.00385$)	Resistance thermometer Pt 100 2 wires	- 200 to + 850°C (- 328 to + 1562°F)	25°C (45°F)
	Resistance thermometer Pt 100 3 wires	- 200 to + 850°C (- 328 to + 1562°F)	25°C (45°F)
	Resistance thermometer Pt 100 4 wires	- 200 to + 850°C (- 328 to + 1562°F)	25°C (45°F)
DIN43760 ($\alpha = 0.00618$)	Resistance thermometer Ni 100 2 wires	- 60 to + 250°C (-76 to + 482°F)	25°C (45°F)
	Resistance thermometer Ni 100 3 wires	- 60 to + 250°C (-76 to + 482°F)	25°C (45°F)
	Resistance thermometer Ni 100 4 wires	- 60 to + 250°C (-76 to + 482°F)	25°C (45°F)
Linear resistance 2 wires		0 to 5000 Ω	30 Ω
Linear resistance 3 wires		0 to 5000 Ω	30 Ω
Linear resistance 4 wires		0 to 5000 Ω	30 Ω
Voltage (millivolt)		-10 to 800 mV	5 mV

Response Time selectable time constant (63%)
1 to 60 sec. as defined.

Update time
0.5 sec. approx.

Loss of input

The analog signal can be programmed up to a minimum value of 3.5 mA or a maximum value of 23 mA.

Isolation voltage

1500 Vac for 60 sec.

Power supply (at transmitter terminals)

The transmitter operates on 7 to 35 Vdc with no load and is protected against reverse polarity connection.

Minimum operating voltages :

- 7 Vdc without options
- 9 Vdc with optional LCD meter

For Ex ia approval power supply must not exceed 28 Vdc.

Output signal

Two-wire 4 to 20 mA dc., linear with ohms and mV or linear with true temperature for THC and RTD.

Optional output meter

LCD : 3 1/2 digit (± 1999 counts) with 10 mm (3/8 in) high, 7-segment characters. Engineering unit labels are provided.

Warm-up time


Operation within specification in less than 5 min.

Max. offset (input)

50% of maximum span value

Load limitations

Total loop resistance including optional remote indicator line : see figure.



Temperature limits

Ambient

-40 and +85°C (-40 and +185°F)
with LCD meter : -20 and +80°C (-4 and +176°F)

Storage

-50 and +120°C (-58 and +248°F)
with LCD meter : -40 and +85°C (-40 and +185°F)

Humidity

0 to 90% RH

PERFORMANCE SPECIFICATIONS

For data where two values are stated the greater one should be considered for the specific case. If not otherwise stated values as % should be considered percent of calibrated span.

COMMON CHARACTERISTICS

Linearity error

< 0.1%

Temperature coefficient

$\pm 0.01\% / ^\circ\text{C}$

Signal/noise ratio

min. 60 dB

Output meter indication accuracy

LCD : $\pm 0.1\%$ of calibrated span ± 1 digit

Supply voltage

Within voltage/load specified limits the total effect is less than 0.005%/V.

Load

Within load/voltage specified limits the total effect is less than 0.01%/100Ω.

EMI/RFI

Meets EN50081 for emission and EN50082 for immunity when instrument is properly installed with or without output meter.

Vibration

IEC 68-2-6 Test FC

Lloyd's specification no. 1 : 4g / 2-100 Hz

Mounting Position

The transmitter may be mounted in any position with no effect on output signal.

THC INPUT

Basic accuracy

- type E, J, K, L, N, T, U : $\pm 1.0^\circ\text{C}$
- type B, R, S, W3, W5 : $\pm 2^\circ\text{C}$
- cold junction compensation (CJC) : $\pm 1.0^\circ\text{C}$

Temperature coefficient

- type E, J, K, L, N, T, U
 - span $< 500^\circ\text{C}$: $\pm 0.05^\circ\text{C}/^\circ\text{C}$
 - span $> 500^\circ\text{C}$: $\pm 0.01\%/^\circ\text{C}$
- type B, R, S, W3, W5 : $0.2^\circ\text{C}/^\circ\text{C}$

VOLTAGE INPUT

Basic accuracy

$\pm 0.01\text{ mV}$ or $\pm 0.1\%$

Temperature coefficient

$\pm 1\text{ }\mu\text{V} / ^\circ\text{C}$ or $\pm 0.01\% / ^\circ\text{C}$

Input resistance

10 MΩ

RTD INPUT

Basic accuracy

$\pm 0.2^\circ\text{C}$

Sensor current

nom. 0.2 mA

Temperature coefficient

- span $< 100^\circ\text{C}$: $\pm 0.01^\circ\text{C}/^\circ\text{C}$
- span $> 100^\circ\text{C}$: $\pm 0.01\%/^\circ\text{C}$

Effect of sensor cable resistance (3/4 wire)

$< 0.002\text{ }\Omega/\Omega$

Max. cable resistance per wire

5 Ω

LINEAR RESISTANCE INPUT

Basic accuracy

$\pm 0.1\text{ }\Omega$ or $\pm 0.1\%$

Temperature coefficient

$\pm 0.01\text{ }\Omega / ^\circ\text{C}$ or $\pm 0.01\% / ^\circ\text{C}$

Sensor current

nom. 0.2 mA

Effect of sensor cable resistance (3/4 wire)

$< 0.002\text{ }\Omega/\Omega$

Max. cable resistance per wire

5 Ω

Configuration

The transmitter is supplied according to ordered configuration option as follows :

Standard configuration

Sensor type, calibration @ 4-20 mA values (specify range when ordering), response time, broken sensor drive and optional LCD meter scale are in accordance with selected options .

Custom configuration

Customer must specify the calibration schedule to which the transmitter is to be calibrated according to the special option, in a Kent-Taylor specified format.

PHYSICAL SPECIFICATIONS

Materials

Housing and covers

Low copper aluminium alloy with baked epoxy finish;
AISI 316 L ss

Covers O-ring

Buna N

Tagging

AISI 316 ss data plate attached to the electronics housing.

Mounting bracket (*)

Zinc plated carbon steel with chrome passivation; AISI 316 L ss

Optional extras

Output meter Plug-in rotatable type, LCD.

Standard LCD meter scale is 0 to 100% linear; special linear scale to specified range and engineering unit is available.

Supplemental customer tag

AISI 316 ss tag fastened to the transmitter with stainless steel wire for customer's tag data up to a maximum of 56 characters and spaces on two lines for tag number and tag name, and up to a maximum of 28 characters and spaces for calibration details.

Configuration kit

Includes 3.5" configuration program disk, a RS232 interface unit, a cable set for transmitter and PC connection providing adaptor and the user manual (order as Part no. AN0239).

Mounting bracket

For 60 mm. (2in) stand pipe or wall mounting.

Environmental protection

Wet and dust-laden atmospheres

The transmitter is dust and sand tight and protected against immersion effects as defined by IEC 529 (1989) to IP67.

Suitable for tropical climate operation as defined in DIN 40.040, application class GQC.

Hazardous atmospheres

With or without output meter

INTRINSIC SAFETY

- CENELEC DEMKO approval; certificate no. 95D.119293

EEx ia IIC T4 (T_{amb} -40 to +85°C)/T6 (T_{amb} -40 to +60°C)

FLAMEPROOF

- CENELEC/CESI Approval; certificate no. Ex-95.D.111

EEx d IIC T5 (T_{amb} -40 to +85°C)/T6 (T_{amb} -40 to +70°C)

FACTORY MUTUAL :

- Explosionproof: Class I, Div. 1, Groups B, C, D

- Dust ignitionproof : Class II, Div. 1, Groups E, F, G

- Suitable for : Class II, Div. 2, Groups F, G; Class III, Div. 1, 2

- Nonincendive: Class I, Div. 2, Groups A, B, C, D

- Intrinsically safe: Class I,II, III, Div. 1, Groups A, B, C, D, E, F, G

Electrical connections

Two 1/2 NPT or M20 x 1.5 or PG 13.5 or 1/2 GK threaded conduit entries, direct on housing, both available for output/supply signal when the sensor is mounted remotely. Alternatively, one 1/2 NPT threaded entry for integrally mounted sensor and one 1/2 NPT or M20 x 1.5 or PG 13.5 or 1/2 GK threaded entry for output/supply signal, direct on housing.

Terminal block

- two terminals for 4-20 mA output/supply signal wiring up to 2.5 mm² (14 AWG) and two jacks compatible with 3 mm dia miniature plugs.

- four terminals for input signal wiring up to 1.5 mm² (16 AWG)

Grounding

Internal and external 6 mm² (10 AWG) ground termination points are provided

Mass

1 kg approx (2 lbs) without sensor and options

Packing

Expanded polythene box

(*) U-bolt material : AISI 400 ss; screws material: high-strength alloy steel or AISI 316ss

ORDERING INFORMATION

Select one character or set of characters from each category and specify complete catalog number.

PRODUCT CODE

	abcde	f	gh	i	j	k	l	mn	o
BASE MODEL			YY					00	
INPUT SENSOR									
ELECTRICAL CERTIFICATION									
HOUSING									
OUTPUT METER									
MOUNTING BRACKET									
CALIBRATION/CERTIFICATE									

abcde	BASE MODEL - 1st to 5th characters	Codice
	Temperature Transmitter	653TY

f	INPUT SENSOR - 6th character	
	Remote	1
	Integrally mounted (NOTE 1) (one 1/2" NPT CONNECTION ENTRY IS PROVIDED)	5

NOTE 1 : quoted separately

gh	7th and 8th characters	
	Use code	YY

i	ELECTRICAL CERTIFICATION - 9th character	
	General Purpose	1
	Intrinsic Safety to CENELEC EN50014/20 DEMKO approval to EEx ia IIC T6/T4	2
	Flameproof to CENELEC EN50014/18 CESI approval to EEx d IIC T6/T5 (NOTE 2)	3
	Intrinsic Safety and Flameproof, as above, CESI approval (NOTE 2)	U
	Factory Mutual (FM) (only available with Remote sensor and 1/2" NPT electrical connections)	7

NOTE 2 : if integral sensor is required this must be supplied by ABB Kent-Taylor Lenno

HOUSING - 10th character

j	Material	Electrical connections	
	Aluminium alloy	1/2" NPT	1
		CM 20	2
		Pg 13.5	3
		1/2" GK	4
	AISI 316 L ss	1/2" NPT	A
		CM 20	C
		Pg 13.5	D
		1/2" GK	F

k	OUTPUT METER - 11th character	
	None	1
	Digital LCD linear 0-100% user scalable	3
	Digital LCD linear scale (specify range and engineering units)	5

l	MOUNTING BRACKET- 12th character	
	None	1
	Carbon steel	2
	AISI 316 L ss	3


mn	13th - 14th character	
	Use code	00

o	CALIBRATION CERTIFICATE - 15th character	
	Not required	1
	For the transmitter only	3
	For the transmitter and the integrally mounted input sensor	4

ELECTRICAL CONNECTIONS

INPUT TYPE	TERMINAL CONNECTION
Thermocouple and voltage	Terminal 5 = positive Terminal 4 = negative
Resistance thermometer and Linear resistance	Terminal 3 and 6 = inputs Terminal 4 = 3rd wire (if any) Terminal 5 = 4th wire (if any)

NOTE: Use terminals 3 and 6 for external CJC of thermocouple (if any by Pt 100)



DIMENSIONS AND MOUNTING DETAILS (Not for construction unless certified)




ABB Instrumentation spa
Via Statale 113
22016 Lenno (Como)
Italia
Tel. (0344) 58111
Facsimile (0344) 56278

ABB Automation Ltd.
Howard Road
St. Neots, Cambs.
England PE19 3EU
Tel. (01480) 475321,
Facsimile (01480) 217948

ABB Automation Inc.
125 East County Line Road
Warminster, Pa.
18974-4995 USA
Tel. (215) 674-6693/6320/6777
Facsimile (215) 674-7184

The Company's policy is one of continuous product improvement and the right is reserved to modify the specifications contained herein without notice.