



**Industrial Solutions**

### Molded Case Circuit Breaker

**Current Ratings**

70, 80, and 90 Amperes

**Voltage Ratings (Max.)**

1-pole – 277 Vac (125 Vdc)

2- and 3- pole – 480 Vac (250 Vdc)

**Frequency Ratings**

60 Hertz

Type TEYD, TEYH, TEYL, 70 - 90 Amperes

Enclosure Compensated

Long-time Delay and Instantaneous Time-current Curves

Curves show enclosure-compensated circuit breaker in open air, 40°C ambient, wired with conductors of corresponding rating, no prior load. For all other ambients, use rating shift index at top of sheet.

## DES081

**Adjustments**

Long-time delay thermal trip: not adjustable.

Instantaneous magnetic trip: not adjustable.

**by ABB**