

HITACHI
Inspire the Next



- "Always-on," high availability architecture
- Reduced CAPEX through hybrid connectivity
- Robust applications for critical utility communications



Hybrid wireless portfolio for utilities

Tropos TRO600 Series

TRO600 Hybrid Wireless Portfolio

No single communication technology meets every operational need.

Some reach long distances yet provide very low bitrate. Others can only deliver broadband speeds at short distances. Large public networks provide non-dedicated capacity.

Dedicated private networks may not be economical to future-proof coverage and capacity.

In utility operating environments, there is a growing range of application requirements. Some are time-critical, others are bandwidth-intensive and everything in between. What is certain is that the number of devices requiring connectivity is growing exponentially. The challenge facing the utility sector is how to maintain high reliability and resiliency for mission-critical operations while expanding the network and adding ever-increasing numbers of devices and applications.

Public cellular networks

Public mobile network operators provide utilities with rapid time to market, ready-to-use infrastructure and a fast track to new generation technologies. Public cellular networks have a superior geographical reach with minimal investments from utility customers, and charge based on usage. In remote locations however, public cellular access may still be subject to geographical coverage challenges. Despite large spectrum utilization, mobile networks are shared and often subject to congestion and sometimes outages, which are unsuitable for mission critical services.

Private cellular networks

Private LTE networks offer fully self-owned and operated, dedicated infrastructure with a forward-looking Industrial IoT approach. They can be deployed in both licensed and unlicensed spectrum, which may present capacity challenges. Private LTE networks in licensed spectrum are CAPEX-intensive due to spectrum cost. As a result, bandwidth is often insufficient to serve the growing number of applications needed in utility operations. Unlicensed LTE spectrum, on the other hand, can be subject to contention and power restrictions, challenging the reliability of the architecture.

Mesh networks

Advanced mesh networks provide robust self-optimizing, self-healing and self-organizing architectures. Fully dedicated and private, mesh networks utilize unlicensed spectrum to deliver high-reliability communications, ensuring critical communication-grade latency and performance. Due to power restrictions and high contention, unlicensed spectrum may present a distance challenge, rendering mesh networks expensive in large geographical deployments.

Hitachi Energy Tropos TRO600 hybrid portfolio for utilities

The TRO600 architecture delivers an “always-on,” high-availability, high-performance wireless network, specifically designed for critical utility operational applications. By leveraging multiple communication technologies, hybrid backhauling endeavors to reap the best of cellular and mesh networks, while mitigating their weaknesses.

The TRO600 series can take advantage of long-haul cellular links, thus reducing intensive CAPEX.


With its signature broadband mesh capability, TRO600 continues delivering a high-bandwidth / low-latency backhaul option, circumventing cellular disruptions to ensure key communications remain reliable and resilient. Where utility assets fall outside cellular coverage, TRO600 can economically provide a localized service extension, leveraging the nearest wired or wireless backhaul interconnect. In addition to the hybrid wireless architecture, the TRO600 series provides a robust mission-critical wired backhaul through a selection of gigabit Ethernet and fiber interfaces.

Hitachi Energy remains committed to backwards compatibility and providing connectivity to legacy devices within a utility network by offering a range of serial and contact interfaces. For harsh environments, TRO600 offers an IP67, IEC61850/IEE1613 certified, corrosion-resistant ruggedized option and an ATEX Zone 2 certification for explosive atmospheres.

To avoid non-essential communication and allow for future distributed compute requirements, the TRO600 family offers an edge compute platform, ready to host third-party applications. By bringing decision making closer to the network edge, the volume of data traversing a network is reduced, thus reducing end-to-end operating costs and contention.

Through Hitachi Energy Wireless' specialized Supros network management system, utility networks can be configured, monitored and managed throughout the deployment and operations lifecycle. Whether a node is purely mesh, purely cellular or carries the more robust hybrid capability, Supros provides deployment support for scalable Hitachi Energy wireless networks.

TRO600 solution overview




TRO670

- Outdoor router, removable antennas
- Highest environmental options
- AC and DC power options
- Optional integrated battery backup
- Dual-band Tropos mesh, LTE and target platform for third-party gateway radio integrations

TRO640

- In-vehicle installations, rolling stock, vibration resistant
- Fast roaming
- Dual-band Tropos mesh and LTE
- Seamless handover mesh <-> LTE (future)



TRO660

- Outdoor router, integrated antennas
- Ease of deployment; lightweight
- Dual-band Tropos mesh, LTE

TRO620

- DIN rail cabinet/indoor installations
- Integrated solutions
- Dual-band Tropos mesh, LTE and target platform for third-party endpoint radio integration
- Richness of interfaces and connectivity
- Adaptable to mobile and outdoor applications with available accessories
- In the US, TRO620 is FirstNet Ready™ and available for utilities to use on FirstNet®.

“ALWAYS-ON” HIGHLY AVAILABLE, HIGH-PERFORMANCE WIRELESS NETWORKS

THE TRO600 SERIES CELLULAR ROUTERS PROVIDE A RELIABLE AND SECURE CONNECTION OVER PUBLIC AND PRIVATE CELLULAR INFRASTRUCTURES. THE TRO600 SERIES SUPPORTS 450MHZ PRIVATE AND DEDICATED NETWORKS ACROSS MULTIPLE BANDS. TO REMAIN ECONOMIC YET FLEXIBLE, ALL PRODUCTS ARE AVAILABLE IN MESH ONLY, CELLULAR ONLY OR HYBRID RADIO VARIANTS.

Hitachi Energy
marketing-update@hitachienergy.com
hitachienergy.com