

---

TECHNICAL DATA SHEET

# Terminals, ring

## Vinyl-insulated, DIN double crimp

### Spec-Kon<sup>®</sup>



---

**Features:**

- Easy entry double crimp
- Corrosive resistant plating
- Color coded to wire size range

---

**Maximum rating:**

- 75°C Max
- 600 volts
- Copper conductors only

---

**Application:**

- ERG9004

Vinyl-insulated DIN ring terminals for wire termination of copper conductors ranging from 0.5mm<sup>2</sup> to 6mm<sup>2</sup>

**Certifications / Standards:**



---

**Conforms to:**

- IEC 60352-2


---

**Materials / Finishes:**

- Copper terminal
- Electro-Tin plated
- Vinyl insulation

**Terminals, ring:**  
Vinyl-insulated, DIN double crimp

**Product selection**

Drawing	Part no:	Wire size range (mm <sup>2</sup> )	Color	Stud hole size	Dimensions (mm)				Crimping tool
					d2	L	F	W	
	R1.5-2VDC-DIN	0.5 - 1.5	Red <span style="color:red">■</span>	19.0	19.0	16.0	6.0	4.3	ERG9004
	R1.5-25VDC-DIN	0.5 - 1.5	Red <span style="color:red">■</span>	19.0	19.0	16.0	6.0	4.3	
	R1.5-3VDC-DIN	0.5 - 1.5	Red <span style="color:red">■</span>	19.0	19.0	16.0	6.0	4.3	
	R1.5-35VDC-DIN	0.5 - 1.5	Red <span style="color:red">■</span>	19.0	19.0	16.0	6.0	4.3	
	R1.5-4VDC-DIN	0.5 - 1.5	Red <span style="color:red">■</span>	21.0	21.0	17.0	8.0	4.3	
	R1.5-5VDC-DIN	0.5 - 1.5	Red <span style="color:red">■</span>	23.0	23.0	18.0	10.0	4.3	
	R1.5-6VDC-DIN	0.5 - 1.5	Red <span style="color:red">■</span>	23.0	23.0	18.0	10.0	4.3	
	R1.5-8VDC-DIN	0.5 - 1.5	Red <span style="color:red">■</span>	29.0	29.0	22.0	14.0	4.3	
	R1.5-10VDC-DIN	0.5 - 1.5	Red <span style="color:red">■</span>	29.0	29.0	22.0	14.0	4.3	
	R2.5-3VDC-DIN	1.5 - 2.5	Blue <span style="color:blue">■</span>	19.0	19.0	16.0	6.0	4.8	
	R2.5-35VDC-DIN	1.5 - 2.5	Blue <span style="color:blue">■</span>	19.0	19.0	16.0	6.0	4.8	
	R2.5-4VDC-DIN	1.5 - 2.5	Blue <span style="color:blue">■</span>	21.0	21.0	17.0	8.0	4.8	
	R2.5-5VDC-DIN	1.5 - 2.5	Blue <span style="color:blue">■</span>	24.0	24.0	19.0	10.0	4.8	
	R2.5-6VDC-DIN	1.5 - 2.5	Blue <span style="color:blue">■</span>	26.5	26.5	21.0	11.0	4.8	
	R2.5-8VDC-DIN	1.5 - 2.5	Blue <span style="color:blue">■</span>	29.0	29.0	22.0	14.0	4.8	
	R2.5-10VDC-DIN	1.5 - 2.5	Blue <span style="color:blue">■</span>	29.5	29.5	22.0	15.0	4.8	
	R2.5-12VDC-DIN	1.5 - 2.5	Blue <span style="color:blue">■</span>	34.0	34.0	25.0	18.0	4.8	
	R6-4VDC-DIN	4 - 6	Yellow <span style="color:yellow">■</span>	25.0	25.0	21.0	8.0	6.7	
	R6-5VDC-DIN	4 - 6	Yellow <span style="color:yellow">■</span>	27.0	27.0	22.0	10.0	6.7	
	R6-6VDC-DIN	4 - 6	Yellow <span style="color:yellow">■</span>	28.0	28.0	22.5	11.0	6.7	
	R6-8VDC-DIN	4 - 6	Yellow <span style="color:yellow">■</span>	33.0	33.0	26.0	14.0	6.7	
	R6-10VDC-DIN	4 - 6	Yellow <span style="color:yellow">■</span>	37.0	37.0	28.0	18.0	6.7	
	R6-12VDC-DIN	4 - 6	Yellow <span style="color:yellow">■</span>	37.0	37.0	28.0	18.0	6.7	

Note: Products must be installed in accordance with applicable national and local electrical codes.