
TECHNICAL DATA SHEET

Terminals, fork

Vinyl-insulated, DIN single crimp

Spec-Kon®



Features:

- Belled opening for wire termination
- Corrosive resistant plating
- Color coded to wire size range

Maximum rating:

- 75°C Max
- 600 volts
- Copper conductors only

Applications:

- ERG9002

Vinyl-insulated DIN fork terminals for wire termination of copper conductors ranging from 0.5mm² to 6mm²

Certifications / Standards:




Conforms to:

- IEC 60352-2

Materials / Finishes:

- Copper terminal
- Brazed seam crimp barrel
- Electro-Tin plated
- Vinyl insulation

Terminals, fork:
Vinyl-insulated, DIN single crimp

Product selection									
Drawing	Part no:	Wire size range (mm ²)	Color	Stud hole size		Dimensions (mm)			Crimping tool
				d2	L	F	W	D	
	F1.5-3VSC-DIN	0.5 - 1.5	Red	M3	19.8	17.2	6.0	4.0	ERG9002
	F1.5-35VSC-DIN	0.5 - 1.5	Red	M3.5	19.8	17.2	6.0	4.0	
	F1.5-4VSC-DIN	0.5 - 1.5	Red	M4	21.8	18.2	6.8	4.0	
	F1.5-5VSC-DIN	0.5 - 1.5	Red	M5	23.8	19.2	10.0	4.0	
	F1.5-6VSC-DIN	0.5 - 1.5	Red	M6	26.4	21.2	11.0	4.0	
	F2.5-3VSC-DIN	1.5 - 2.5	Blue	M3	20.1	19.5	5.5	4.5	
	F2.5-35VSC-DIN	1.5 - 2.5	Blue	M3.5	20.1	17.5	6.0	4.5	
	F2.5-4VSC-DIN	1.5 - 2.5	Blue	M4	22.1	18.5	6.8	4.5	
	F2.5-5VSC-DIN	1.5 - 2.5	Blue	M5	25.1	20.5	10.0	4.5	
	F2.5-6VSC-DIN	1.5 - 2.5	Blue	M6	27.7	22.5	11.0	4.5	
	F6-4VSC-DIN	4 - 6	Yellow	M4	25.4	22.2	8.0	6.3	
	F6-5VSC-DIN	4 - 6	Yellow	M5	27.6	23.2	10.0	6.3	
	F6-6VSC-DIN	4 - 6	Yellow	M6	29.4	24.2	11.0	6.3	
	F6-8VSC-DIN	4 - 6	Yellow	M8	33.8	27.2	14.0	6.3	
	F6-10VSC-DIN	4 - 6	Yellow	M10	36.8	29.2	18.0	6.3	

Note: Products must be installed in accordance with applicable national and local electrical codes.