

T124 | T184

All-in-One Charging at a Small Footprint



High
Performance

180 kW

Peak Output Power

Single/Dual
Connector

400 A

Output Current
with CCS

Small Footprint

< 0.5 m²

For 180 kW
All-in-One Charger

Power Specification

DC Output:	Output Power: T124: 120 kW T184: 180 kW
	Dynamic Power Sharing: T124: 60 kW power granularity T184: 90 kW power granularity
	Output voltage: 150 - 920 V
	Output current (peak): CCS: 400 A; J3400/NACS: 375 A
	Number of outlets: single, dual; (CE): dual + AC socket
	Total system efficiency: (CE): up to 95.6 % (NA): up to 96 %
AC Input:	Nominal voltage: (CE): 400 V ($\pm 10\%$) (NA): 480 Y / 277 V ($\pm 10\%$)
	Nominal input current (RMS): T124: (CE): 187 A / 220 A (NA): 153 A T184: (CE): 280 A / 312 A (NA): 230 A
	Frequency: (CE): 50 Hz ($\pm 10\%$) (NA): 60 Hz ($\pm 10\%$)
	Earthing systems: TN-S, TN-C, TN-C-S, TT (with upstream RCD)
	Inlet cable size per phase: up to 180 mm ²
	Power factor: > 0.99 @ full load
	Total Harmonic Distortion (THD): < 4.5 % @ full load
	Overvoltage category: III
	SPD: Type 2

System Specification

Operating Conditions:	Operating from (CE): -35 °C to 50 °C (NA): -31 °F to 131 °F (with derating)
	Storage / transport from -5 °C to 40 °C (23 °F to 104 °F)
	Altitude: up to 2000 m (6562 ft)
	Humidity: up to 95 %, non-condensing
	Impact resistance: IK10 (HMI: IK08)
	IP rating: IP54
	Noise emission: < 65 dB(A) @ 1 m front door, 25 °C (77 °F), full power
	Intended use: indoor and outdoor
	Mounting options: floor mounted
	Environment pollution degree: Class 3 (outside), Class 2 (inside)
Dimensions:	H x W x D: 1900 x 565 x 880 mm (74.8 x 22.2 x 34.6 in)
	Weight: T124: 445 kg (981 lbs) T184: 475 kg (1047 lbs)
	Accessibility: meets ADA requirements for height, reach, and user interface

Customer Interface

Display:	Type: 7" LCD; Interface: Touchscreen
Lighting:	Gun holder: LED
Languages:	English (others available via software upgrade)
Connector Options:	Patented two-phase cooling technology (CCS1, CCS2), Air-cooled J3400 (NACS); (CE): AC socket
Cable Management System (CMS):	Optional cable retraction CMS
Cable:	(CE): Length: 5 m (16.4 ft); Reach with CMS: 3.5 m (11.5 ft) (NA): Length: 6 m (19.7 ft); Reach with CMS: 5 m (14.4 ft) Further options available, Type: Air-cooled
Authentication Methods:	RFID, Autocharge, Plug and Charge, Option: payment terminal for credit/debit card
RFID System:	Mifare ISO 14443 A/B to part 4 and ISO/IEC 15693. Others available on request (NFC, Calypso, Ultralight, PayPass, and more)
Remote Management:	Access control, configuration, diagnostics, software updates

Standards & Compliance

Safety Standards:	(CE): EN IEC 61851-1: 2019, EN IEC 61851-23: 2014/AC: 2016, EN IEC 62311: 2020 (NA): UL2202
Metering:	(CE): Eichrecht (NA): CTEP/NTEP
EMC:	(CE): Class A according to: IEC 61851-21-2: 2018, EN IEC 61000-6-1: 2007, EN IEC 61000-6-2: 2019, EN 61000-6-3: 2007+A1: 2011, EN 61000-6-4: 2007+A1: 2011, ETSI EN 301 489-1 v2.2.0: 2017 (NA): Class A (90-180 KW), 47CFR FCC Part 15b; ENERGY STAR® certified; ICES 003
Manufactured:	USA & Europe
Network Connections:	Cellular: LTE Cat 4/UMTS/GSM, Ethernet: 10/100 Base-T
Network Communication Protocol:	(CE): OCPP 1.6J (NA): OCPP 1.6J Core and Smart Charging Profiles; OCPP 2.0.1 Core; Autocharge via OCPP
Vehicle Communication Protocol:	DIN 70121, ISO 15118, Autocharge
Short Circuit Current Rating:	(CE): 25 kA (NA): 65 kA
RED Directive:	EN 300 330 V2.1.1: 2017, EN 301 908-13 V13.2.1: 2022, EN 50364: 2020, EN 62311: 2020, EN 301908-2 V11.1.2: 2017
Additional Standards:	T124 T184: IEC 62196-2, IEC 62196-3, OCA 1.6J (Feb 2024) T184: NEVI configuration: FHWA Build America, Buy America

—
©Copyright ABB E-mobility 2024. All rights reserved to copyrights, registered trademarks, and trademarks reside with their respective owners. The information in this document is provided in good faith, is provided for information purposes only and is subject to contract. The information contained herein is subject to change without notice and should not be construed as any commitment by ABB E-mobility B.V. or its affiliates or holding companies (ABB E-mobility). ABB E-mobility assumes no responsibility for any errors that may appear in this document. We reserve all rights with respect to this document, its content and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB E-mobility. No representations are made, express or implied, with respect to the accuracy, reliability, availability or completeness of the information provided, and no liability is accepted for any damage or loss suffered as a result of reliance on any information provided herein.

—
ABB E-mobility B.V.

Heertjeslaan 6
2629 JG Delft
The Netherlands
Phone: +31 88 4404600
E-mail: info.evci@nl.abb.com
e-mobility.abb.com

—
ABB E-mobility Inc.

950 W Elliott Road, Suite 101
Tempe, AZ, 85284
United States
Phone: 800-435-7365
E-mail: US-evci@abb.com
e-mobility.abb.com

—
ABB E-mobility Inc.

800 Hymus Boulevard
Saint-Laurent, QC H4S 0B5
Canada
Phone: 800-435-7365
E-mail: CA-evci@abb.com
e-mobility.abb.com