
 TECHNICAL DATA SHEET

PMA Smart Line - ALAD-P - Fitting

45°elbow, one-piece, IP66, PG thread

PMA



One-piece, IP66 polyamide fitting for flexible non-metallic conduit



Applications:

- In machine building, installation and construction industries

Features & Benefits:

- Economical
- Easy „push-in“ installation
- Re-opening with screwdriver (for security reasons hand opening not possible)
- Space saving due to compact design
- Fits both conduit profiles - fine (T) and coarse (G)

Ingress protection:

- IP66 (EN/IEC 60529)

Materials:

- High-grade, specially formulated polyamide 6

Compatible with:

- PMAFLEX Pro Conduits
- PMAFLEX Multilayer Conduits
- PMAFLEX Conduits
- PMA Smart Line Conduits

Weathering resistance:

- Very good UV resistance and weathering characteristics, particularly in black

Colour:

- Black
- Grey

Chemical properties:

- Please refer to www.pma.ch (Technical Information / Chemical Resistance)


Environmental properties:

- Free from halogens and cadmium
- RoHS and REACH compliant

Product selection:

Part no.		Thread size	Conduit size	Dimensions in mm (nom.)				Weight	Packing unit
black	grey	PG	NW	g	d2	A	B	kg/100 pcs	pcs/PU
ALAD-P090	SLAD-P090	9	10	11.0	21.5	42.5	34.0	0.6	100
ALAD-P112	SLAD-P112	11	12	11.0	25.0	47.5	40.0	0.8	100
ALAD-P132	SLAD-P132	13.5	12	11.0	25.0	47.5	41.5	0.9	100
ALAD-P137	SLAD-P137	13.5	17	11.0	31.0	54.0	46.0	1.3	100
ALAD-P167	SLAD-P167	16	17	11.0	31.0	54.0	47.0	1.3	100
ALAD-P213	SLAD-P213	21	23	12.0	39.0	63.5	57.5	2.1	50
ALAD-P299	SLAD-P299	29	29	12.0	46.0	69.5	65.0	2.8	30
ALAD-P366	SLAD-P366	36	36	13.0	56.0	81.5	80.0	4.8	20
ALAD-P488	SLAD-P488	48	48	13.0	68.0	91.5	93.0	6.9	10

Our customer service dept. or local distribution partner will be pleased to help you concerning product availability and lead time



Mechanical Properties:	Value:	Test parameters:	Test method:
Tensile modulus	1'200 ... 3'700 N/mm ²		ISO 527
Tensile strength	45 ... 65 N/mm ²		ISO 527
Notched bar impact test	4 ... 20 kJ/m ²		ISO 180/1C

Thermal properties:	Value:	Test parameters:	Test method:
Continuous application temperature	- 50 ... + 105 °C		PMA DO 9.21-4510
Upper application temperature	+ 120°C	(20'000 h)	PMA DO 9.21-4360
Short-term	+ 160 °C	(168 h)	PMA DO 9.21-4360

Fire safety properties:	Value:	Test parameters:	Test method:
Fire performance	non flame-propagating		IEC EN 61386-1
Flame class	V2		UL 94

Content of delivery:

- Fitting

Assembly instructions:

- When mounting, push-in conduit completely and then pull back slightly to ensure the locking mechanism is fully engaged
- To Disassembly: reopen with screwdriver and tiwst for easy release
- Please consider the appropriate assembly instructions on www.pma.ch

ABB Switzerland Ltd,
PMA Cable Protection
Aathalstrasse 90
8610 Uster, Switzerland
Phone: +41 58 585 00 11
pma-info@ch.abb.com
www.pma.ch

Let's write the future.
Together. **abb.com**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Installation Products Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright© 2019 ABB Installation Products Inc. All rights reserved

