


FurseWELD

Cable to cable CC14

Cable to cable CC14 - FurseWELD



Stranded/solid circular conductor size A (mm ²)	Stranded/solid circular conductor size B (mm ²)	Mould part no.	Order code	Powder cartridge part no.	Handle clamp part no.
16 *	16 *	CC14-4-1616	7TCA083910R2965	65P10	HCPK4
25	25	CC14-4-2525	7TCA083910R2768	45P10	HCPK4
35	35	CC14-4-3535	7TCA083910R1183	65P10	HCPK4
35	25	CC14-4-3525	7TCA083910R2966	65P10	HCPK4
50	50	CC14-4-5050	7TCA083910R1185	90P10	HCPK4
50	35	CC14-4-5035	7TCA083910R2967	90P10	HCPK4
50	25	CC14-4-5025	7TCA083910R2968	90P10	HCPK4
70	70	CC14-4-7070	7TCA083910R1188	115P10	HCPK4
70	50	CC14-4-7050	7TCA083910R1187	115P10	HCPK4
70	35	CC14-4-7035	7TCA083910R2374	90P10	HCPK4
70	25	CC14-4-7025	7TCA083910R1186	90P10	HCPK4
95	95	CC14-4-9595	7TCA083910R1195	150P10	HCPK4
95	70	CC14-4-9570	7TCA083910R1194	150P10	HCPK4
95	50	CC14-4-9550	7TCA083910R1193	150P10	HCPK4
95	35	CC14-4-9535	7TCA083910R1192	115P10	HCPK4
120	120	CC14-4-120120	7TCA083910R1178	200P10	HCPK4
120	95	CC14-4-12095	7TCA083910R1182	200P10	HCPK4
120	70	CC14-4-12070	7TCA083910R1181	200P10	HCPK4
120	50	CC14-4-12050	7TCA083910R1180	150P10	HCPK4

Special moulds for all FurseWELD products can be manufactured to meet specific customer applications on request

*4 x S103 Sleeve required when joining conductors 16 mm² or smaller

For order codes of powder cartridges and handle clamps, see pages 49-50

FurseWELD moulds should only be used with FurseWELD powders, handle clamps and accessories. If moulds, powders, handle clamps and accessories from other manufacturers are utilized, we cannot guarantee the safe use or the integrity of the completed joint

FurseWELD moulds for use with stranded conductor are designed for use with non-compacted conductor to BS EN 60228. If a mould for compacted conductor is required, please contact your local representative

Conductors must be installed in the orientation shown to achieve the correct connection