RESIDENTIAL SOLUTIONS

ReliaHome™ Single Main Meter Combos



ReliaHome Meter Combos deliver a smart, space-saving solution for single-family metering and power distribution. Combining the meter socket and load center in one outdoor enclosure, they simplify installation, cut costs and help ensure full NEC 2020 compliance with an integrated main service entrance disconnect.

Built with durable, high-quality materials, these units feature an optimized plug-on neutral design for fast, easy setup. Solar-ready options support photovoltaic (PV) systems and meet NEC 705.12 standards, handling up to 120% of bus ampacity with standard back-fed circuit breakers.

Features

- UL listed (panelboards UL 67)
- Single-phase, three-wire, 120/240 VAC
- Galvanized enclosures
- Service barriers included for factory-installed main circuit breaker and main circuit breaker kits (required to meet UL 67 for service entrance applications)
- NEMA 3R outdoor rated
- 22 kAIC rated

See following page for options and models, including EUSERC-compliant versions.

ENGINEERED
TO OUTRUN

Single main, top/bottom

- Ring and ringless versions available
- Horn and lever bypass versions available
- Plug-on neutral options for faster installations
- Up to 200A
- Solar ready options



PAMS2020TRLNCS
top/bottom, no bypass

PAMS0820TRLLCS
top/bottom, lever bypass

The following Single Main Meter Combos meet EUSERC utility specifications:

Single main, top/bottom and side-by-side

- Ring versions available
- Plug-on neutral options for faster installations
- Solar-ready options
- Extra-wide side-by-side options
- Up to 225A

PCMS4020TRNUSR
top/bottom, EUSERC

TSMQ2020CSCU
side-by-side, EUSERC

—
ABB Inc.
305 Gregson Drive
Cary, NC 27511

electrification.us.abb.com

—
We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Inc. Copyright © 2026 ABB
All rights reserved

1TQC1832E001 1.2026