

## ABB MOTION SERVICES

# ABB Ability<sup>™</sup> Digital Powertrain Condition monitoring of rotating equipment fitted with ABB Ability<sup>™</sup> Smart Sensors



The ABB Ability Smart Sensor is a key element of the Digital Powertrain. It turns rotating equipment, such as motors, into smart, wirelessly connected assets. The sensors help detect potential asset disturbances and plan maintenance before reliability, productivity and safety are impacted.

## **ABB Ability Digital Powertrain**

The ABB Ability Digital Powertrain is a suite of digital solutions that enables you to remotely monitor the health and performance of powertrains, including drives, motors and applications, such as pumps.

It combines data collected by the Smart Sensor with data from other connected equipment, such as variable-speed drives. This data can be accessed and analyzed remotely, providing a better understanding of the maintenance needs and energy efficiency of the entire process.

## **ABB Ability Smart Sensor**

The ABB Ability Smart Sensor is a key element of the Digital Powertrain. It enables remote condition monitoring of a powertrain's rotating assets, such as motors and general machinery.

Easily fitted to the asset's surface, the Smart Sensor collects data and transmits it via a smartphone or gateway to a secure cloud service. Advanced algorithms analyze the data, providing deeper insights into the condition and performance of the monitored asset. Potential machine disturbances and energy savings can be detected and actions taken to make operations more efficient, predictable and safe.

## Benefits

- Early detection of potential problems minimizes downtime
- Condition-based maintenance lowers costs
- Process optimizations reduce operating and energy costs
- Remote condition monitoring increases personnel safety
- Compliant with strictest requirements for equipment operating in explosive atmospheres
- Easily retrofitted to ABB or third-party equipment



01

01 ABB Ability Digital Powertrain web portal

02 ABB Ability Digital Powertrain condition monitoring solution: The ABB Ability Smart Sensor transmits the data via a smartphone or gateway to a secure cloud service. Advanced algorithms analyze the data and convert it into meaningful information, which is sent to the user's smartphone and customer portal.

The solution can also be integrated into your own systems.

### Accessing information

Details on the asset's status can be accessed through:

- Web portal dashboard for operators to view condition and performance trends, access historical data, manage user access rights and set alerts and alarm.
- **App** interface to the asset's status for technicians on the factory floor. A 'traffic light' display gives an easy overview of the condition of all monitored assets.
- Other systems the Smart Sensor data can be easily integrated via API into other systems, such as ERP and SCADA systems or the plant level monitoring system ABB Ability<sup>™</sup> Genix.

## **Expert advice**

While the data is always at your disposal, ABB can provide support to analyze the data and define the steps for improving your operations.



#### Smart Sensor features Certified for hazardous areas

The second generation ABB Ability Smart Sensor is designed for hazardous areas and harsh environments. Its enclosure withstands high vibration levels and protects the sensor from total dust ingress (IP66/67). The sensor is certified for ATEX, IECEx and NEC 500.

#### Pinpoint detection accuracy

The Smart Sensor features the latest technology including accelerometers, magnetometer and ultrasonic microphone. Even slight anomalies in the asset's condition can be detected at a very early stage. The sensor's mechanical design allows the transducers to pick up the true vibrations independent of sensor's eigenfrequencies.

#### Long battery life

The Smart Sensor is available with two battery sizes. The lifetime of the high performance sensor is up to 15 years under normal operating conditions and that of the standard performance sensor up to five years.

## Same hardware for different assets

The same sensor can be used for different assets, saving time and reducing stock holding. The asset to be monitored is chosen during commissioning.





## Intended use

The ABB Ability Smart Sensor can be used for industrial motors and general machinery, such as pumps and fans.

#### Motor specifications

- Industrial AC motors, induction or synchronous
- Continuous duty or intermittent duty with duty cycle durations of more than 20 minutes
   Frame sizes
- Frame Sizes
- IEC: 56 500
- NEMA: 42 449, above NEMA: 5000 6800
- Fixed speed or variable speed
- New or existing motors from ABB or other manufacturers

## Monitored motor health parameters

- Overall condition
- Overall vibration (velocity RMS)
- Bearing condition
- Skin temperature (degrees)

#### Monitored motor operating parameters

- Vibration in 3 axis
  - velocity RMS
  - acceleration RMS
  - acceleration peak to peak
- Speed (rpm)
- Total running time
- Total number of starts
- Supply frequency (Hz)
- Output power (hp/kW)
- Regreasing count-down

#### General machinery specifications

• Assets, such as pumps and fans, in which only temperature and vibration need to be measured and monitored

#### Monitored general machinery health parameters

- Overall vibration (velocity RMS)
- Overall acceleration RMS
- Skin temperature (degrees)

#### Monitored general machinery operating parameters

- Vibration in 3 axis
- velocity RMS
- acceleration RMS
- acceleration peak to peak

## ABB Ability Smart Sensor gateway

The gateway automatically collects data from a high number of Smart Sensors and transmits the data to the cloud for processing.

Gateway specifications		
Manufacturer	Cassia, with ABB customization	
Range	30 - 200 m (can vary in an industria environment depending on facility layout	
Power supply	PoE (Power over Ethernet)	
Certifications	1879 FCC, CSA, CE	
Radio frequency	ISM band, 2.402-2.480 GHz	
Data transfer	WiFi, LAN 4G/LTE USB dongle	
IP rating	IP65 with cover caps	
Environment	Operating temperature: -40 °C to +65 °C	

#### ABB ABILITY<sup>™</sup> CONDITION MONITORING FOR ROTATING EQUIPMENT

SPECIFICATIONS	High performance sensor	Standard performance sensor	
Lifetime	up to 15 years operation under standard conditions <sup>1)</sup>	up to 5 years operation under standard conditions <sup>1)</sup>	
	1) ABB indicates a maximum sensor lifetime which varies between sensor types and is base upon standard usage conditions. Standard conditions of operations are as follows: sensor measurement interval of 1 hour; raw data collection once per day; non-condensing environment; measured asset skin temperature: +15 °C to +50 °C		
/ibration measurement			
Acceleration, low frequency (x, y, z direction)			
Amplitude range	0.03 - 157 m/s² (16g)		
Frequency bandwidth		– 3.3 kHz	
Acceleration, high frequency (z direction)	0.4112	- 3.3 KHZ	
Amplitude range	0.1 - 490 m/s² (50g)	N/A	
·	2.4 Hz - 10 kHz	N/A	
Frequency bandwidth  Aagnetic field measurement	2.4 HZ - 10 KHZ	N/A	
Aagnetic field (x, y, z direction) Amplitude range	1 - 1600 uT		
	1 - 1600 μT 0.1 - 280 Hz		
Frequency bandwith Iltrasonic sound measurement	0.1 -		
	·		
Amplitude range		2 20 N /m²	
Amplitude range	0.6 mN/m <sup>2</sup> - 20 N/m <sup>2</sup>		
Frequency bandwidth		2 - 80 kHz	
emperature measurement (asset skin tempe			
leasurement range	-40 °C to +85 °C		
Resolution	0.1 °C		
Accuracy	+/-0.5 °C		
Vireless communication			
Communication standards	Bluetooth® 5.0, Bluetooth® Low Energy or WirelessHART (HART 7.4)	Bluetooth® 5.0, Bluetooth® Low Energy	
Radio standard	IEEE	302.15.4	
Frequency	2.4 GHz, license free ISM band		
Range (nominal)	>200 m @ line of sight		
Security			
Encryption	128-bit AES encryption		
Authentication	IEC 62351 (role-based access control)		
Power			
Battery type	not rej	placeable	
Invironmental			
	Operation: -	40 °C to +85 °C	
emperature	Storage: : <30 °C		
P class	IP66/67 (dust-tight and resistant to powerful water jetting and submersion		
Chemical tolerance	See chemical tolerance sheet fo	r PBT (Polybutylene terephthalate)	
Certifications			
	Ex ia   Ma -40 °C ≤ T	amb ≤ +85 °C (Mining)	
		$C \leq Tamb \leq +85 ^{\circ}C (Gas)$	
lazardous areas		C ≤ Tamb ≤ +85 °C (Dust) A, B, C and D T4	
		r E, F and G T4	
	Cl III, Div 1		
Radio	EN 300 328 v.2.1.1, EN 301 330 v.2.1.1		
	FC	C/IC	
MC			
mmunity	EN/IEC 61000-6-2		
mission	EN/IEC 61000-6-3		
Physical			
Dimensions (W x D x H)	82 mm x 69 mm x 45 mm	75 mm x 58 mm x 33 mm	
		130 g	
Veight	165 Q	Stainless steel/reinforced PBT	
Veight Case material	185 g Stainless stee	_	

For more information, please contact your local ABB representative or visit:

abb.com/smartsensor solutions.abb/digital-powertrain We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Ltd does not accept any responsibility whatsoever for potential errors or possible lack of information in this document. We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB Ltd. Copyright© 2022 ABB All rights reserved