

FIG. 1




FIG. 2

DIMENSION TABLE

| GCAT NO. | FIG. | A | B | C | D | E | G | H | I |
|----------------------------------|------|-------|-------|-------|-------|-------|-------|-------|-------|
| TH2263MDC/THN2263MDC | 1 | 25.35 | 13.41 | 15.25 | 13.13 | 25.07 | 25.60 | 10.50 | 10.12 |
| TH3363M/THN3363M/TH3323M/TH2223M | 1 | 25.35 | 13.41 | 15.25 | 13.13 | 25.07 | 25.60 | 10.50 | 10.12 |
| TH3364M/THN3364M/TH3324M/TH2224M | 2 | 35.13 | 14.44 | 16.28 | 14.13 | 34.82 | 35.38 | 11.50 | 10.12 |
| TH2223MSS/TH3323MSS/TH3363MSS | 2 | 25.35 | 13.41 | 15.25 | 13.28 | 25.22 | 25.60 | 10.50 | 10.36 |
| THN3363MSS | 2 | 25.35 | 13.41 | 15.25 | 13.28 | 25.22 | 25.60 | 10.50 | 10.36 |
| TH3324MSS/TH2224MSS | 2 | 35.13 | 14.44 | 16.28 | 14.28 | 34.97 | 35.38 | 11.50 | 10.36 |
| TH3364MSS/THN3364MSS | 2 | 35.13 | 14.44 | 16.28 | 14.28 | 34.97 | 35.38 | 11.50 | 10.36 |

NOTE:

1. ALL DIMENSIONS ARE IN INCHES.
2. ALL DIMENSIONS HAVE ± 0.125 TOLERANCE.
3. ADDITIONAL BRACKET FOR 200A CATALOGS.



**OUTLINE DRAWING-MILL DUTY SAFETY SWITCH
100 & 200A, NEMA - TYPE 12 ENCLOSURE**

| THIRD ANGLE | SHEET# | DWG NO. | DATE | REV |
|-------------|--------|---------------|-----------|-----|
| | 1 of 1 | 10103091SH128 | Jan-04-24 | G |