

LIGHTWEIGHT CHANGER FOR ROBOTS - BATCH PART


LWR50L-23-00002-A

▶ PRODUCT SPECIFICATIONS




MATCH

▶ Gripping force diagram



▶ Forces and moments

Shows static forces and moments



Mr_L [Nm]	20	Mr [Nm]	7.0
My_L [Nm]	40	Mx [Nm]	7.0
Fa_L [N]	500	My [Nm]	5.5
		Fa [N]	200.0

▶ Technical data

LWR50L-23-00002-A

Order no.

General data

Control	IO-Link
Operating temperature [°C]	5 ... +60
Protection to IEC 60529	IP40
Weight [kg]	0.7300

Tool changer specific data

Electrical energy transfer	integrated
Locking stroke [mm]	1
Repetition accuracy in X, Y [mm]	0.05
Repetition accuracy in Z [mm]	0.05
Tightening force [N]	50
Release force [N]	0
Offset at coupling max. in X,Y [mm]	1.0

Gripper specific data

suitable for series	LWR50F-xx-03/04/05
Positionable	Yes
Integrated position sensing	Using process data
Cable management	external
Type of drive	electrical
Stroke per jaw [mm]	10
Gripping force safety device	mechanical
Gripping force in closing (adjustable) max. [N]	200
Gripping force in opening (adjustable) max. [N]	200
Closing time [s]	0.19
Opening time [s]	0.19
Control time [s]	0.03
Dead weight of mounted gripper finger max. [kg]	0.1
Length of the gripper fingers max. [mm]	80
Repetition accuracy +/- [mm]	0.02
Voltage [V]	24
Current consumption max. [A]	1.0
Minimum positioning path per jaw [mm]	0.5
PWIS-free	Yes
RoHS compliant	Yes

▶ RECOMMENDED ACCESSORIES



CONNECTIONS / OTHER



ALWR1-50-A
Storage station

▶ RECOMMENDED ACCESSORY STORAGE STATION



NJ5-E2SK-01
Inductive Proximity Switch Cable 0,3 m - Connector M8

