

Stanilite®

Platinum exit LED Quickfit® theatre mask

Nexus®



Range

Platinum range

Product group

Exit LED Quickfit



Features

- LED technology 100,000 hours plus lamp life
- Low power consumption and LED light source for reduced operation and maintenance costs
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, either cabled or wireless
- Quickfit unique steel slide connect bracket for quick installation and easy maintenance
- Includes all pictograph diffuser options for single sided installation
- Universal wall/ceiling mounting, can also be rod or wire suspended
- Retrofit capability; fits into any existing Quickfit mounting bracket

| Catalogue no. | Description |
|---|---|
| Nexus products | |
| PQFBNXSLEDP | Platinum exit LED Quickfit theatre mask Nexus LX single sided includes all pictograph inserts |
| PQFBNRFLEDP | Platinum exit LED Quickfit theatre mask Nexus RF single sided includes all pictograph inserts |
| Accessories | |
| MQFCL | Cantilever bracket (white) |
| QFWGCM | Wire guard - ceiling |
| QFWGWM | Wire guard - wall |
| PWQFKITPOLY | IP65 kit - polycarbonate for single or double sided installation |
| PWQFKITACRY | IP65 kit - acrylic for single or double sided installation |
| 21-OPMD056 | Diffuser theatre mask without pictograph inserts * |
| 29-PIQFTM | Standard theatre mask pictograph inserts |
| Note: * For a double sided configuration additional diffuser 21-OPMD056 is required | |
| Spare parts | |
| 03-01302P | Battery LiFePO4 3.2V 3.2Ah |
| PQFBNXSLEDP-LB | Platinum exit LED Quickfit theatre mask Nexus LX less bracket pictograph |
| PQFBNRFLEDP-LB | Platinum exit LED Quickfit theatre mask Nexus RF less bracket pictograph |
| PQFBNXSLEDP-FR | Platinum exit LED Quickfit theatre mask Nexus LX frame only |
| PQFBNRFLEDP-FR | Platinum exit LED Quickfit theatre mask Nexus RF frame only |

Note:

- The exit comes complete including pictograph insert pack as single sided exit. For double sided exit add diffuser 21-OPMD056



| Dimensions | | | |
|--------------------------|---------------|--------------------------------|-------------------------------|
| | Length | Width | Height (incl. bracket) |
| | 379mm | 72mm | 214mm |
| Weight | | | |
| | Model | Weight | |
| | Nexus | 1.8kg | |
| Construction | | | |
| | Part | Construction | |
| | Body | UV/FR ABS body | |
| | Diffuser | Acrylic | |
| | Bracket | Black powder coated zinc steel | |
| Light source | | | |
| | Model | Light source | |
| | Nexus | Multiple LED 1.6W | |
| Power consumption | | | |
| | Model | Power consumption | |
| | Nexus | 3.2W | |
| | | | Note: Preliminary results |

Note:

- Designed to comply with AS2293 and meet relevant Australian EMC standards