



| MVI Fault Interrupter   | CO-8-4 Relay  | 30-900 Ampere                             |
|---|---|---|
| <b>MINIMUM TRIPPING AND TOTAL CLEARING TIME-CURRENT CHARACTERISTIC CURVES</b>   |   |   |
| <b>Notes:</b> <ol style="list-style-type: none"> <li>1. Tested per C37.60</li> <li>2. Accuracy is equal to +/- 10% of the current or time whichever is greater.</li> <li>3. Minimum power up current: 15 Amperes</li> <li>4. Curves are applicable to the operating range of -40°C to +65°C.</li> </ol> | <ol style="list-style-type: none"> <li>5. CT current sensing capability range: 10 -10,000 amperes RMS</li> <li>6. Curves and trips are set using a personal computer or a control panel</li> <li>7. The total clearing time-current characteristics curves represent the total time required to detect and interrupt the fault current</li> <li>8. This curve in its entirety, including the title block, should be printed on a 11"x 17" sheet in order to conform with the C37.41 curve presentation standard (5.6 cm/decade).</li> </ol> | <b>CO-8-4 Relay<br/>30-900<br/>Ampere</b> |
|   | <br>497 Schooley's Mountain Road<br>Hackettstown NJ, 07840<br>Issue Date: December 13, 2022  |   |