

Type LT6GE - general purpose stainless steel 316L, CE Liquid-tight flexible metallic conduit

Stainless steel 316L general purpose, CE certified liquid-tight flexible metallic conduits provide excellent strength, corrosion protection and liquid-tight performance

Features & Benefits:

- Designed to meet UL 360 ID/OD dimension requirements
- Full compliance to IEC/EN 61386-1 requirements, CE certified
- Trade sizes from 3/8" to 4" (12mm to 100mm)
- Coordinated performance with series 5300SST6 stainless steel 316 fittings
- Ingress protection ratings aligned with industrial enclosures
- Smooth extruded jackets provide best performance with fittings

Applications:

- General purpose, industrial grade liquid-tight flexible metallic conduit
- Used extensively in corrosive environments and where flexibility is necessary for motion, vibration and bending
- Typical applications include water/wastewater plants, food & beverage installations, chemical processing plants, marine and salt environments, pulp and paper
- Sunlight resistant jacket material allows this product to be used in outdoor applications
- Liquid-tight applications against water, oils, cutting fluids, mild acids
- For use in electrical circuits up to 1,000 V

Construction / Material / Finish:

- Stainless steel 316L core
- PVC (Polyvinyl Chloride) extruded smooth jacket
- Ink jet printed ratings and technical information
- Full range of trade sizes from 3/8" to 4" (12mm to 150mm) 3/8" to 4", fully interlocked design
- Color: Gray (standard)

Environment ratings:


Working Temperature:

- Gen:
 - Dry: -55 to +105°C (-67 to +221°F)
- IEC/CE:
 - Gen: -45 to +105°C (-49 to +221°F)

Chemical resistance guide:

- See publication TDS000117

T&B Liquidtight Systems™



Certifications / Standards:



Conforms to:

- IEC/EN 61386-1, -23, Conduit Systems for Cable Management
EU DoC: EC-012-17-177
- CE (Conformité Européenne, European Conformity)
- RoHS (Restriction of Hazardous Substances directive)

Standards requirements:

Designed to UL 360 and CSA 22.2, No. 56 standard requirements including:

- ID and OD Dimensions

Meets all IEC/EN 61386-23 standard requirements including:

- Compression strength - Code 4 Heavy; 1250 N/50mm
- Impact strength - Code 4 Heavy; 6 Joules
- Tensile strength - Code 3 Medium; 500 N/2 min.

Ingress protection:

- Provides "Ingress Integrity" between enclosures, fittings, conduits & seal gaskets when using LT6GE conduits and series 5300SST6 liquidtight fittings
- Covers all trade sizes from 3/8" to 4" (12mm to 103mm)

System ingress ratings:

- Products tested and comply with UL 50E and CSA C22.2, No. 94 Type Rating requirements
 - Indoor: Type 4, 12, 13
 - Outdoor: Type 3, 3R, 4
- NEMA 250: Type 3, 3R, 4, 12, 13

IEC system ingress rating:

- IP ingress protection per IEC/EN 60529 requirements
- IEC ingress ratings: IP66, IP67






Type LT6GE – general purpose stainless steel 316L, CE

Product selection and dimensions

Product selection

Trade size			Coil length										Weight	
UL	CSA	ISO BS EN	Carton		Standard reel				Bulk reel				lbs/ft	kg/m
			Part No./GID	Feet	Meter	Part No./GID	Feet	Meter	Part No./GID	Feet	Meter			
3/8	12	16	LT6GES01G-C	100	30	LT6GES01G-K	500	150	LT6GES01G-L	1,000	300	0.23	0.34	
			7TAA012LVOR0000			7TAA012LVOR0010			7TAA012LVOR0017					
1/2	16	20	LT6GES02G-C	100	30	LT6GES02G-K	500	150	LT6GES02G-L	1,000	300	0.28	0.42	
			7TAA012LVOR0001			7TAA012LVOR0011			7TAA012LVOR0018					
3/4	21	25	LT6GES03G-C	100	30	LT6GES03G-K	500	150	LT6GES03G-L	1,000	300	0.38	0.57	
			7TAA012LVOR0002			7TAA012LVOR0012			7TAA012LVOR0019					
1	27	32	LT6GES04G-C	100	30	LT6GES04G-J	400	120	—	—	—	0.62	0.92	
			7TAA012LVOR0003			7TAA012LVOR0013								
1-1/4	35	40	LT6GES05G-B	50	15	LT6GES05G-E	200	60	—	—	—	0.79	1.18	
			7TAA012LVOR0004			7TAA012LVOR0014								
1-1/2	41	50	LT6GES06G-B	50	15	LT6GES06G-D	150	45	—	—	—	1.03	1.53	
			7TAA012LVOR0005			7TAA012LVOR0015								
2	53	63	LT6GES07G-B	50	15	LT6GES07G-C	100	30	—	—	—	1.19	1.77	
			7TAA012LVOR0006			7TAA012LVOR0016								
2-1/2	63	70	LT6GES08G-A	25	8	—	—	—	—	—	—	2.09	3.11	
			7TAA012LVOR0007											
3	78	80	LT6GES09G-A	25	8	—	—	—	—	—	—	2.95	4.39	
			7TAA012LVOR0008											
4	103	100	LT6GES11G-A	25	8	—	—	—	—	—	—	4.10	6.10	
			7TAA012LVOR0009											



Dimensions

Part number	Trade size			Minimum inside bend radius				Inches				Millimeters			
	UL	CSA	ISO BS EN	Static		Dynamic		Inside (ID)		Outside (OD)		Inside (ID)		Outside (OD)	
				Inches	mm	Inches	mm	Min	Max	Min	Max	Min	Max	Min	Max
LT6GES01G-*	3/8	12	16	2.0	51	4.0	102	0.484	0.504	0.690	0.710	12.3	12.8	17.5	18.0
LT6GES02G-*	1/2	16	20	3.0	76	5.0	127	0.622	0.642	0.820	0.840	15.8	16.3	20.8	21.3
LT6GES03G-*	3/4	21	25	4.2	107	6.0	152	0.820	0.840	1.030	1.050	20.8	21.3	26.2	26.7
LT6GES04G-*	1	27	32	5.5	140	12.0	305	1.041	1.066	1.290	1.315	26.4	27.1	32.8	33.4
LT6GES05G-*	1-1/4	35	40	7.0	178	15.0	381	1.380	1.410	1.630	1.660	35.1	35.8	41.4	42.2
LT6GES06G-*	1-1/2	41	50	4.5	114	17.0	432	1.575	1.600	1.865	1.900	40.0	40.6	47.4	48.3
LT6GES07G-*	2	53	63	6.0	152	22.0	559	2.020	2.045	2.340	2.375	51.3	51.9	59.4	60.3
LT6GES08G-*	2-1/2	63	70	8.0	203	29.0	737	2.480	2.505	2.840	2.875	63.0	63.6	72.1	73.0
LT6GES09G-*	3	78	80	10.0	254	36.0	914	3.070	3.100	3.460	3.500	78.0	78.7	87.9	88.8
LT6GES11G-*	4	103	100	12.0	305	52.0	1,321	4.000	4.040	4.460	4.500	101.6	102.6	113.3	114.3

Note: Product must be installed in accordance with applicable national and local electrical codes.

Contact us

ABB Inc.
 Electrification Products
 8155 T&B Boulevard
 Memphis, TN 38125
www.abb.us/lowvoltage

© 2018 ABB Inc. All rights reserved.

